

# TALON

## Outdoor Uni-PAK All-In-One Metering

Catalog Number

**WTG2211, WTG2211RJ, WTG2211RJB,  
WP2211, WP2211RJ, WP2211RJB**

Enclosure

**Type 3R**

Main Bus Rating: 200 Amps  
120/240 V~, 1 Phase, 3 Wire  
208Y/120 V~, 1 Phase, 3 Wire  
(5th jaw may be required)

Meter Socket Rating: 125A Continuous  
Branch Rating: 125A Max.

For installation by Qualified Person in  
accordance with all local electrical codes  
and/or the National Electrical Code®.

**Suitable Only For Use As  
Service Equipment.** Install no more  
than six main disconnecting means.

For overhead or underground service.

**Use 60/75°C Copper or  
Aluminum Conductors** for all  
panel terminals and on circuit breaker  
terminals when breakers are so marked.

General Information:  
Circuit breaker overload trip position is  
indicated by handle position midway  
between ON and OFF. To reset, move  
handle to OFF position, then turn ON.


### Accessories

5th Jaw, 6 or 9 o'Clock Position. . . . . ECMF5  
Insulated 5th Jaw, 6 or 9 o'Clock Pos. . . ECMF5i  
Meter Socket Cover Plate (Ring Type) . . . ECPP  
Meter Socket Cover Plate (Ringless) . . . ECCP3  
Horn By-Pass (Ringless Only) . . . . . ECMFH

### Short Circuit Current Rating

The maximum short circuit current rating of this device is 100,000 RMS symmetrical amperes, 120/240 V~. The actual rating is limited to the lowest interrupting rating of any circuit breaker installed. Use only Siemens type QP, QPH, HQP, HQPH, LQ, MP-T, MP-HT or MP-MT circuit breakers. Use of other circuit breakers in this device will void the warranty.

**Important:** Do not allow petroleum based (hydrocarbon) sprays, chemicals, solvents or any paint to contact interior components. Petroleum based chemicals can cause degradation of electrical insulating materials.



Terminal	Wire Size	Torque
A, B, N1	300 kcmil - #4 AWG	275 LB-IN
G	#2 - 14 AWG	50 LB-IN
N2/Equip GND	#2/0 - 4 AWG	110 LB-IN

### Use HD Type Hubs if required

Trade Size (in)	Catalog No.
3"	H56856-2
3-1/2"	H56857-2
4"	H56858-2
Closure Plate	H56933