

BOX TERMINAL 4 PCS. ACCESSORY FOR: 3VA6 150/250



| Model | |
|---------------------|-------------|
| Product brand name | SETRON |
| Product designation | accessories |

| Connections according IEC | |
|--|---|
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / minimum | 35 mm ² |
| <ul style="list-style-type: none"> • for copper cable / finely stranded / maximum | 150 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / minimum | 25 mm ² |
| <ul style="list-style-type: none"> • for copper cable / stranded / maximum | 185 mm ² |
| Wire stripping length | 19 mm |
| Tightening torque / when using copper cables | |
| <ul style="list-style-type: none"> • stranded | <= 35 mm ² : 6 Nm, >= 50 mm ² : 12 Nm |
| <ul style="list-style-type: none"> • finely stranded | <= 35 mm ² : 6 Nm, >= 50 mm ² : 12 Nm |

| Connections according UL | |
|---|-----------|
| Wire stripping length | 0.75 in |
| Connectable conductor cross-section | |
| <ul style="list-style-type: none"> • for copper cable / stranded / minimum | 4 AWG |
| <ul style="list-style-type: none"> • for copper cable / stranded / maximum | 350 kcmil |

- for copper cable / finely stranded / minimum
- for copper cable / finely stranded / maximum

4 AWG
350 kcmil

Tightening torque / when using copper cables

- stranded
- finely stranded

<= 1 AWG: 70 lb-in, >= 1/0 AWG: 140 lb-in
<= 1 AWG: 70 lb-in, >= 1/0 AWG: 140 lb-in

Certificates

General Product Approval

EMC

Declaration of
Conformity

other



CSA



UL



RCM



EG-Konf.

[Miscellaneous](#)

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=3VA9244-0JA12>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3VA9244-0JA12>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)



http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3VA9244-0JA12

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>



last modified:

11/20/2017