



REVISION	DATE	BY	DATE	BY
		DRAWN	08/01/07	CY
		CHEK'D		
		VERIF'D		

Confidential - Property of Siemens Industry, Inc. Building Technologies Division		
CUSTOMER		
ORDER NO.	DWG. NO.	
	1D1Y015FTP1	SH 1 OF 2

SIEMENS

CATALOG NO. 1D1Y015FTP1
 SERIAL NO. SERIES H
 15 kVA 60 Hz 1 PHASE
 6 % IMP AT 135 °C
 115 °C RISE °C AVG. AMBIENT
 220 °C TEMP CLASS °C MAX. AMBIENT
 PRIMARY (H1 H3 H2 H4) 240X480 V
 SECONDARY(X4 X2 X3 X1) 120/240 V
 WINDING MATERIAL AL
 ENCLOSURE TYPE NEMA-3R WEIGHT 175 LBS
 ENERGY EFFICIENCY NEMA TP 1-2002


SPACINGS BETWEEN ENCLOSURE AND ANY ADJACENT WALL SHALL BE A MINIMUM OF 6 INCHES
 LISTED DISTRIBUTION TRANSFORMER 77US TYPE F
 LR 3902
 E112313
 SUITABLE FOR INDOOR OR OUTDOOR LOCATIONS DO NOT INSTALL IN AREAS ACCESSIBLE TO PUBLIC FOR INSTALLATION SEE INSTRUCTION MANUAL
 NEMA Class ANN Dry Type Transformer Siemens Industry, Inc. Norcross, GA




PRIMARY VOLTS	CONNECTION LINES TO	INTER-CONNECT
480	H1,H4	1-H2,2-H3,H2-H3
456	H1,H4	2-H3,3-H2,H2-H3
432	H1,H4	3-H2,4-H3,H2-H3
240	H1,H4	1-H2,2-H3,H1-H3,H2-H4
216	H1,H4	3-H2,4-H3,H1-H3,H2-H4
SECONDARY VOLTS	CONNECTION LINES TO	INTER-CONNECT
240	X1,X4	X2-X3
120/240	X1,X2,X4	X2-X3
120	X1,X2	X2-X4,X1-X3



FRONT VIEW



SIDE VIEW



All Dimensions in inches

ENCLOSURE COLOR : ANSI 61 GREY – OUTDOOR

CUSTOMER NOTES:

- HV1 TERMINATED AT TOP FRONT
- LV1 TERMINATED AT BOTTOM FRONT

Confidential – Property of
Siemens Industry, Inc.
 Building Technologies Division

REVISION	DATE	BY	DATE	BY
			08/01/07	CY

CUSTOMER	
ORDER NO.	DWG. NO. 1D1Y015FTP1
SH 2 OF 2	

0.1 root 2011/01/11 10:09