



NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED

- NOTES
- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
  - 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
  - 3 FOR TERMINAL DIAGRAM SEE 2434W50003 (A2)
  - 4 DRG SHOWS OPTION B (11 OUTPUTS, 5 INPUTS)

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓  
 For explanation of dimensions, tolerances, notes etc. see B.S.308.  
 Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
 Limits on untoleranced machined dimensions to B.S.4500;  
 i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
 over 6 to 30±0.2; over 120 to 315±0.5;  
 General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_  
 Treatment: \_\_\_\_\_

Title: TYPICAL SCHEME DIAGRAM FOR  
 3 PHASE DIRECTIONAL & E/F DIRECTIONAL OR  
 3 PHASE DIRECTIONAL & E/F NON DIRECTIONAL  
 NUMERIC OVERCURRENT PROTECTION (ARGUS 2) EPSILON

Reyrolle Protection  
 Hebburn.

First used on: \_\_\_\_\_  
 Similar Articles: 2434W10025  
 Supersedes: \_\_\_\_\_  
 Drg. No. 2434W10071