



NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

- NOTES
- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
 - 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
 - 3 APPLICATION SHOWS USE OF HOLMGREEN CONNECTION FOR E/F CIRCUIT. USE OF SEPERATE RING CORE CT IS ALSO POSSIBLE.
 - 4 APPLICATION SHOWS USE OF 5-LIMB STAR CONNECTED VT WITH SEPERATE OPEN DELTA WINDING PROVIDING THE NEUTRAL VOLTAGE
 - 5 FOR TERMINAL DIAGRAM SEE 2434W50006 (A2)
 - 6 DRG SHOWS (7 OUTPUTS, 9 INPUTS)

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____
Treatment: _____

Title: ARGUS 2 DIGITAL DIRECTIONAL RELAY
TYPICAL SCHEME DIAGRAM FOR
3P DIRECTIONAL P/F & 1P DIRECTIONAL E/F RELAY
WITH OPEN DELTA CONNECTED VT

VATECH REYROLLE
AUTOMATION, CONTROL & PROTECTION

Original Scale: NTS

First used on: _____
Similar Articles: 2434W10090
Supersedes: _____
Drg. No. **2434W10091**

1	11/12/02	CHANGE NOTED
ISSUE	DATE	NOTED