



NOTES
 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
 3 METROSIL & SETTING RESISTORS ARE REQUIRED FOR HIGH IMPEDANCE & RESTRICTED EARTH FAULT APPLICATIONS.
 4 FOR TERMINAL DIAGRAM SEE 2716W50003 (A2)
 5 THIS DIAGRAM IS USED FOR BOTH ARGUS 3 & 4

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
 Machine where marked ✓
 For explanation of dimensions, tolerances, notes etc. see B.S.308.
 Limit on untoleranced unmachined dimensions ± _____
 Limits on untoleranced machined dimensions to B.S.4500;
 i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
 over 6 to 30±0.2; over 120 to 315±0.5;
 General unmachined angular tolerance ± _____

Finish: _____
 Treatment: _____

Title:
 TYPICAL SCHEMATIC DIAGRAM 2 PHASE+EARTH+SEF RS485
 NUMERIC OVERCURRENT PROTECTION (ARGUS 3&4) EPSILON

**Reyrolle Protection
 Hebburn.**

Original Scale:
 NTS

First used on:
 Similar Articles: 2716W10009
 Supersedes:
 Drg. No.
2716W10015

Copyright © 2005 Reyrolle Ltd.

1	04/11/05	CHANGE NOTED
ISSUE	DATE	NOTED