


1 IF IN DOUBT ASK
2 DO NOT SCALE

3 4 5 6 7 8



NOTE:
 THE Ø3.6 HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS.
 THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN
 FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER
 PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY Ø4.5) AND RELAYS
 MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS
 (SUPPLIED IN PANEL FIXING KIT).

EU EXPORT CONTROLS **ECCN: N** **AL: N**
This document is not Export Controlled unless sending to Critical Countries.

Copyright © 2019 Siemens PLC. Hebburn

1	08/08/19	CHANGE
ISSUE	DATE	NOTED

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500:

i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;

General unmachined angular tolerance ± _____

Finish: _____

Treatment: _____

Title:
OVERALL DIMENSIONS AND PANEL DRILLING
FOR 7SR5 S6 CASE.

SIEMENS PLC.

Original Scale:
1 : 2

First used on: _____
 Similar Articles: _____
 Supersedes: _____
 Drg. No. **2518X10006**

DRAWN J.BURNETT CHECKED _____ APPROVED N.C. DATE 08/08/19 IE _____ OPS _____ PCP _____ Purch.Spec. TQ _____ EAC _____ CE _____ STD _____ A3