




1 IF IN DOUBT ASK
2 DO NOT SCALE

3 4 5 6 7 8



PANEL CUT-OUT



NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

NOTE:
THE Ø3.6 HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS.
THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN
FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER
PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY Ø4.5) AND RELAYS
MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS
(SUPPLIED IN PANEL FIXING KIT).

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked ✓

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined dimensions ±

Limits on untoleranced machined dimensions to B.S.4500:

i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;

over 6 to 30±0.2; over 120 to 315±0.5;

General unmachined angular tolerance ±

DRAWN J.BURNETT CHECKED

APPROVED N.C

DATE 08/08/19

IE

OPS

PCP

Purch.Spec. TQ

EAC

CE

STD

A3

EU EXPORT CONTROLS ECEN: N AL: N
This document is not Export Controlled unless sending to Critical Countries.

Copyright © 2019 Siemens PLC. Hebburn

Finish:

Title:

OVERALL DIMENSIONS AND PANEL DRILLING
FOR 7SR5 S12 CASE.

Treatment:

Original Scale:

1 : 3

Drq. No.

2518X10012

First used on:
Similar Articles:
Supersedes:

1	08/08/19	CHANGE NOTED	△
ISSUE	DATE	NOTED	