

# Reyrolle 5

## 7SR57 Motor Protection

[siemens.com/reyrolle5](http://siemens.com/reyrolle5)

### Description

The Reyrolle 5 is designed for the electricity networks of the future with enhanced communications and cyber security while maintaining a user-friendly interface and easy product management.

The 7SR57 motor protection devices include a wide range of protection functions with IEC 61850 and Modbus TCP Ethernet communications as standard. To further minimize the product variants the power supply and the binary inputs cover the full operating range with configurable binary input thresholds.

The large LCD, tactile pushbuttons and programmable LEDs provide a user-friendly product interface and the relay element is withdrawable for easy replacement.

Inputs and Outputs	4 CT + 8 BI + 6 BO 4 CT + 13 BI + 8 BO 4 CT + 4 VT + 9 BI + 8 BO 4 CT + 4 VT + 19 BI + 12 BO
Communication	Standard front USB port (for configuration using Reydisp PC based software tool) rear RS485, 2 x RJ45 electrical ports or optional optical ethernet connections.
Housing	Size 6 or 12 withdrawable design.
Display	Backlit 128 x 128 LCD with text and graphical display capabilities suitable for single line mimic diagrams.



### Benefits

- Setting to select display of alternative languages on the front fascia LCD: French, German, Portuguese, Spanish and Turkish
- Compact design and low product life-cycle cost.
- Reliable operation due to powerful, proven protection algorithms
- IEC 61850 Edition 1 & 2 with HSR, PRP and RSTP operation for increased availability
- Simple product ordering
- Combined 1 A and 5 A current transformer inputs
- 28 programmable tri-color LEDs for clear indications

### Applications

- Motor protection functions designed to protect during all motor starting and running sequences
- Thermal algorithm optimized to closely match the thermal characteristics of motors
- Thermal monitoring via plant temperature sensors supported



## Protecting grids with confidence

### Standard Functionality can include

- 14 Locked rotor protection
- 37/37G Undercurrent protection – phase/earth
- 46BC Broken conductor detection
- 46PR Phase-rotation reversal
- 46UB Phase unbalance
- 48 Starting-time supervision
- 49R Rotor thermal overload protection
- 49TS Temperature sensor supervision
- 50/50G/50N Instantaneous overcurrent/earth fault
- 50AFD Arc flash detection
- 50BCL Break capacity limit
- 50BF Circuit-breaker failure protection – 3-pole
- 51/51G/51N Time delayed overcurrent/earth fault
- 52 Circuit-breaker control
- 60CTS CT supervision
- 66 Number of starts
- 74CC/74TC Close-circuit and trip-circuit supervision
- 81B Backspin monitor
- 81HB2 Inrush current detection
- 86 Lockout
- 87GH Restricted earth fault protection – high-impedance

### Optional Functionality can include

- 27/27Vx Undervoltage protection
- 32 Power protection
- 47 Sequence overvoltage protection
- 55 Power factor
- 59/59Vx Overvoltage protection
- 59N Neutral voltage displacement
- 60VTS VT supervision
- 67/67G/67N Directional – phase/earth fault
- 81 Frequency protection – “f>” or “f<”
- 81B-V Backspin monitor – voltage reference

### Monitoring Functions

- Primary, secondary, phase sequence, current and voltage
- Frequency, power, and energy
- Fault data, event and waveform records
- Motor start data log

### Communication

- IEC 60870-5-103, MODBUS-RTU, DNP3 serial, MODBUS-CLIENT for connection to external RTD box, IEC 61850, MODBUS TCP

Siemens AG  
Smart Infrastructure  
Digital Grid  
Humboldtstrasse 59  
90459 Nuremberg,  
Germany

For the U.S published by  
Siemens Industry Inc.

100 Technology Drive  
Alpharetta, GY 30005  
United States

Customer Support: [www.siemens.com/csc](http://www.siemens.com/csc)  
Phone: +49 (0) 911 433 78 78  
E-mail: [support.energy@siemens.com](mailto:support.energy@siemens.com)

© Siemens 2020 Subject to changes and errors

Subject to changes and errors  
The information given in this document only contains general descriptions and / or performance features which may not always specifically reflect those described or which may undergo modification in the course of further development of the products.

The requested performance features are binding only when they are expressly agreed upon in the concluded contract.