



MODULE LABEL KEY	
ANALOGUE MODULE	AN 1 etc
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

ABBREVIATIONS			
CT	CURRENT INPUTS		
VT	VOLTAGE INPUTS		
SI	STATUS INPUTS		
CO	CHANGE OVER OUTPUT CONTACTS		
NO	NORMALLY OPEN OUTPUT CONTACTS		
NC	NORMALLY CLOSED OUTPUT CONTACTS		

MATERIAL:	
Dimensions in millimetres : Surface texture in micrometres. Machine where marked √ For explanation of dimensions, tolerances, notes etc. see B.S.308. Limit on untoleranced unmachined dimensions ± Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5; General unmachined angular tolerance ±	Finish: Treatment:

Title:	
TERMINAL ID & WIRING FOR OH1-XXX-XD (4CT,4VT,27SI,3CO,26NO) IN E16 CASE.	Original Scale: Drg. No. 2615W11005

Copyright © 1999 VATECH REYROLLE ACP Ltd. Hebburn	
First used on: Similar Articles: Supersedes:	Issue DATE NOTED

Title:	
VATECH REYROLLE AUTOMATION, CONTROL & PROTECTION	Original Scale: Drg. No. 2615W11005

Title:	
TERMINAL ID & WIRING FOR OH1-XXX-XD (4CT,4VT,27SI,3CO,26NO) IN E16 CASE.	Original Scale: Drg. No. 2615W11005

Title:	
TERMINAL ID & WIRING FOR OH1-XXX-XD (4CT,4VT,27SI,3CO,26NO) IN E16 CASE.	Original Scale: Drg. No. 2615W11005

NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED