

NOTES

1 TERMINALS RECOMMENDED ARE PRE INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.


SUPPLIER	AMP	CABLE SIZE
AMP	342103	0.25-1.6 SQ MM
AMP	342143	1.0-2.6 SQ MM.

OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.

2 FOR OUTLINE & DRILLING DRG SEE 2995X10016 (A4).

3 IRIG-B & FIBRE OPTIC CONNECTORS MUST BE DISCONNECTED & FIXING NUTS REMOVED BEFORE WITHDRAWING CONTROLLER MODULE.

RELAY VIEWED FROM REAR



MODULE LABEL KEY	
ANALOGUE MODULE	AN 1 etc
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

ABBREVIATIONS	
CT	CURRENT INPUTS
VT	VOLTAGE INPUTS
SI	STATUS INPUTS
CO	CHANGE OVER OUTPUT CONTACTS
NO	NORMALLY OPEN OUTPUT CONTACTS
NC	NORMALLY CLOSED OUTPUT CONTACTS

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked √
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ±
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
Limits on untoleranced machined dimensions to B.S.4500;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ±

Finish: _____ Title: _____
Treatment: _____

TERMINAL ID & WIRING FOR OH1-XXX-XF (4CT,4VT,11SI,3CO,26NO) IN E16 CASE.

VA TECH Reyrolle
AUTOMATION, CONTROL & PROTECTION

Original Scale: NTS Drg. No. 2615W11008

First used on: _____
Similar Articles: _____
Supersedes: _____

NOT SUBJECT TO UPDATE ONCE COPIED / PRINTED OR DOWNLOADED

3 ROW	13/08/03	MNS13/2440 MM
2	27/02/08	MODULE LABEL & POSTIN ADDED MNI1008/279
1	7/4/00	CHANGE
	ISSUE	DATE NOTED

Copyright © 2000 VA TECH Reyrolle Ltd. Hebburn