


1 IF IN DOUBT ASK
DO NOT SCALE

- NOTES
- 1) TERMINALS RECOMMENDED ARE PRE-INSULATED & MUST BE CRIMPED USING APPROVED TOOLING.
 - 2) CONNECTIONS TO THIS COMMUNICATIONS FACILITY IS BY SCREENED, TWISTED PAIR CABLE, ON SITE. WHEN WIRING OTHER FACILITIES ENSURE THAT THESE TERMINALS ARE NOT OBSCURED BY OTHER WIRE RUNS.

SUPPLIER PART NUMBER CABLE SIZE
Dowells (ring type) RS009 2.5mm sq.
Dowells (pin type) CP9/CP1 2.5mm sq./1.5mm sq

OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.




NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

ABBREVIATIONS

I- CURRENT INPUTS
BI- BINARY INPUTS
BO- BINARY OUTPUTS
COM- BINARY OUTPUT COMMON
NO- NORMALLY OPEN BINARY OUTPUT CONTACTS
NC- NORMALLY CLOSED BINARY OUTPUT CONTACTS
L- LINE
N- NEUTRAL
E- EARTH

COMMUNICATIONS IDENTIFICATION	
COM1	RS485 X2
COM2	USB TYPE 'B' PORT (ON RELAY FRONT LABEL)



MATERIAL: MATERIAL.

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500:
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;

General unmachined angular tolerance ± _____

DRAWN AMARN.

CHECKED SHASHANK

APPROVED

N.C

DATE 30/07/15

IE

OPS

PCP

Purch.Spec. TQ

EAC

EAC.

CE

STD

A3

Title:

TERMINAL ID & WIRING DIAGRAM FOR
7SR105 NON RTD

SIEMENS PROTECTION DEVICES LTD.

Original Scale.

NTS

Drq. No.

2437W60004

First used on:

Similar Articles:

Supersedes:

ISSUE.	MOD.DATE.	CHANGE
ISSUE	DATE	NOTED



Copyright © YEAR Siemens Protection Devices Ltd. Hebburn