



**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**

- NOTES
- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
 - 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
 - 3 FOR TERMINAL DIAGRAM SEE 2716W50002 (A2)
 - 4 THIS DIAGRAM IS USED FOR BOTH ARGUS 5 & 6.

2	19/4/02	MN434/2292
1	22/11/99	CHANGE NOTED
ISSUE	DATE	NOTED

MATERIAL: Dimensions in millimetres : Surface texture in micrometres. Machine where marked ✓ For explanation of dimensions, tolerances, notes etc. see B.S.308. Limit on untoleranced unmachined dimensions ± _____ Limits on untoleranced machined dimensions to B.S.4500; i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8; over 6 to 30±0.2; over 120 to 315±0.5; General unmachined angular tolerance ± _____		Finish: _____ Treatment: _____	Title: TYPICAL SCHEME DIAGRAM FOR 3 PHASE DIRECTIONAL & E/F DIRECTIONAL OR 3 PHASE DIRECTIONAL & E/F NON DIRECTIONAL NUMERIC OVERCURRENT PROTECTION (ARGUS 5&6) Reyrolle Protection Hebburn.	First used on: _____ Similar Articles: 2716W10004 Supersedes: _____ Drg. No. 2716W10010
DRAWN M LEASK CHECKED _____ APPROVED R.D.WATSON	DATE 24/07/02 IE _____ OPS _____ PCP _____ Purch.Spec. TQ _____ EAC _____	CE _____ STD _____ A3 _____		