

IF IN DOUBT ASK
DO NOT SCALE

A

B


C

D


E

F


BUSBARS




DCD31x C R6 Case Size






- RELAY 1
- RELAY 2
- RELAY 3
- RELAY 4
- RELAY 5
- RELAY 6
- RELAY 7



D.C Auxilliary Input Volts



STATUS I/P 1



PHASE ROTATION

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____
Treatment: _____

Title:
TYPICAL SCHEMATIC DIAGRAM FOR 2 PHASE + E/F
DCD OVERCURRENT RELAY

**Reyrolle Protection
Hebburn.**

Original Scale.
NTS

First used on:
Similar Articles: 2434W10016
Supersedes:
Drg. No.
2434W10030


DRAWN M LEASK CHECKED APPROVED R.D.WATSON DATE 23/07/02 IE OPS PCP Purch.Spec. TQ EAC CE STD A3

NOTES

- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
- 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
- 3 FOR TERMINAL DIAGRAM SEE 2434W20001 (A2)
- 4 DRG SHOWS OPTION C (7 O/P. 9 I/P).

NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

TERMINAL BLOCKS VIEWED FROM REAR



KEY
1 Short Terminals
2 Long Terminals
3 CT Shorting Links

Copyright © Reyrolle Ltd.

1	16/10/97	CHANGE NOTED
ISSUE	DATE	