



- NOTES**
1. CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
  2. CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
  3. FOR TERMINAL DIAGRAM SEE 2434W50010 (A2).
  4. DRG SHOWS OPTION B (11 OUTPUTS, 5 INPUTS).

**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_  
Treatment: \_\_\_\_\_

Title: TYPICAL SCHEMATIC DIAGRAM 2PH(DIR)+EF(DIR) OR 3PF(DIR)+EF E8  
110/P+5I/P RS485 ARGUS 2 NUMERIC OVERCURRENT PROTECTION

**SIEMENS PROTECTION DEVICES LTD.**

Original Scale: 1:1

First used on: \_\_\_\_\_  
Similar Articles: 2434W10071  
Supersedes: \_\_\_\_\_  
Drg. No. 2434W10127

1	12.02/07	CHANGE NOTED
ISSUE	DATE	NOTED