

IF IN DOUBT ASK  
DO NOT SCALE

A




B

C

D

E

F



**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**

NOTE:  
THE Ø3.6 HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS. THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY Ø4.5) AND RELAYS MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS (SUPPLIED IN PANEL FIXING KIT).

DRAWING OFFICE ONLY NOTE  
ANY CHANGE TO THIS DRG MUST BE REFLECTED  
ON DRG 2995X10018 & CATALOGUE

5 RDW	04/06/07	MN995/2883 (AL)
4 RDW	23/05/03	MN995/2531 MM
3 RDW	27/09/06	MN995/2462(ML/RDW)
2	30/07/01	MN995/2125
1	15/07/99	CHANGE
ISSUE	DATE	NOTED

**MATERIAL:**

Dimensions in millimetres ; Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_  
Treatment: \_\_\_\_\_

Title:  
**OVERALL DIMENSIONS AND PANEL DRILLING  
FOR EPSILON E16 CASE.**

**SIEMENS PROTECTION DEVICES LTD.**

Original Scale:  
**1:4**

First used on:  
Similar Articles:  
Supersedes:  
Drg. No.  
**2995X10016**

DRAWN	T.CARR	CHECKED	A.LAW	APPROVED	RD.WATSON	DATE	11/07/02	IE	OPS	PCP	Purch.Spec.	TQ	EAC	CE	STD	A3
-------	--------	---------	-------	----------	-----------	------	----------	----	-----	-----	-------------	----	-----	----	-----	----

Copyright © 1999 Siemens Protection Devices Ltd. Hebburn