

IF IN DOUBT ASK
DO NOT SCALE

A




B

C

D

E

F



**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**

NOTE:
THE $\phi 3.6$ HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS. THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY $\phi 4.5$) AND RELAYS MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS (SUPPLIED IN PANEL FIXING KIT).

DRAWING OFFICE ONLY NOTE
ANY CHANGE TO THIS DRG MUST BE REFLECTED
ON DRG 2995X10018 & CATALOGUE

| | | |
|-------|----------|--------------------|
| 5 RDW | 04/06/07 | MN995/2883 (AL) |
| 4 RDW | 23/05/03 | MN995/2531 MM |
| 3 RDW | 27/09/06 | MN995/2462(ML/RDW) |
| 2 | 30/07/01 | MN995/2125 |
| 1 | 15/07/99 | CHANGE |
| ISSUE | DATE | NOTED \triangle |

MATERIAL:

Dimensions in millimetres ; Surface texture in micrometres.
Machine where marked \checkmark
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions \pm _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6 ± 0.1 ; over 30 to 120 ± 0.3 ; over 315 ± 0.8 ;
over 6 to 30 ± 0.2 ; over 120 to 315 ± 0.5 ;
General unmachined angular tolerance \pm _____

Finish: _____
Treatment: _____

Title:
**OVERALL DIMENSIONS AND PANEL DRILLING
FOR EPSILON E16 CASE.**

SIEMENS PROTECTION DEVICES LTD.

Original Scale:
1:4

First used on: _____
Similar Articles: _____
Supersedes: _____
Drg. No.
2995X10016