



IEC 61850 Certificate Level A¹

Page 1/2

No. 74102036-MOC/INC 12-01953

Issued to:
Siemens Protection Devices Limited
North Farm Road, Hebburn
Tyne & Wear, NE31 1LX
United Kingdom

For the product:
Reyrolle 7SR224
Directional Overcurrent Protection Relay
Firmware Version: 7b
EN100 V04.08

Issued by:



The product has not shown to be non-conforming to:

IEC 61850-6, 7-1, 7-2, 7-3, 7-4 and 8-1

Communication networks and systems in substations

The conformance test has been performed according to IEC 61850-10, the UCA International Users Group Device Test Procedures version 2.3 with TPCL² version 1.5, the product's protocol, model and technical issue implementation conformance statements: "7SR224 IEC 61850 Protocol Implementation Conformance Statement (PICS), document issue 2012/10", "7SR224 IEC 61850 Model Implementation Conformance Statement (MICS), document issue 2012/09" and the extra information for testing: "7SR224 Protocol Implementation Extra Information for Testing (PIXIT), document issue 2012/10".

The following IEC 61850 conformance blocks have been tested with a positive result (number of relevant and executed test cases / total number of test cases):


| | | | |
|----|-------------------------------------|-----|--------------------------------|
| 1 | Basic Exchange (18/24) | 9a | GOOSE Publish (8/13) |
| 2 | Data Sets (3/6) | 9b | GOOSE Subscribe (10/11) |
| 2+ | Data Set Definition (23/23) | 12a | Direct Control (5/12) |
| 4 | Setting Group Selection (3/3) | 12c | Enhanced Direct Control (5/13) |
| 5 | Unbuffered Reporting (16/19) | 12d | Enhanced SBO Control (10/19) |
| 6 | Buffered Reporting (18/21) | 13 | Time Synchronization (3/5) |
| 6+ | Enhanced buffered reporting (10/12) | 14 | File Transfer (4/7) |

This certificate includes a summary of the test results as carried out at Siemens in United Kingdom with UniCA 61850 Client simulator 3.25.02 with test suite 3.24.02c and UniCA 61850 Analyzer 4.25.00. This document has been issued for information purposes only, and the original paper copy of the KEMA report: No. 74102036-MOC/INC 12-01952 will prevail.

The test has been carried out on one single specimen of the product as referred above and submitted to KEMA by Siemens. The manufacturer's production process has not been assessed. This attestation does not imply that KEMA has approved any product other than the specimen tested.

Arnhem, October 26, 2012


M. Adriaensen
Director Intelligent Networks & Communication


R. Schimmel
Certification Manager

- 1 Level A - Independent test lab with certified ISO 9000 or ISO 17025 quality system
- 2 TPCL - Test procedures change list

Copyright © KEMA Nederland B.V., Arnhem, the Netherlands. All rights reserved. Please note that any electronic version of this KEMA attestation is provided to KEMA's customer for convenience purposes only. It is prohibited to update or change it in any manner whatsoever, including but not limited to dividing it into parts. In case of a conflict between the electronic version and the original version, the original paper version issued by KEMA will prevail.



Applicable Test Procedures from the UCA International Users Group Device Test Procedures version 2.3 with TPCL version 1.5

| Conformance Block | Mandatory | Conditional |
|---------------------------------|--|---------------------------|
| 1: Basic Exchange | Ass1, Ass2, Ass3, AssN2, AssN3, AssN4, AssN5 Srv1, Srv2, Srv3, Srv4, Srv5, SrvN1abcd, SrvN4 | Srv6, Srv7, SrvN1e, SrvN3 |
| 2: Data Sets | Dset1, Dset10a, DsetN1ae | |
| 2+: Data Set Definition | Dset2, Dset3, Dset4, Dset5, Dset6, Dset7, Dset8, Dset9 DsetN1cd, DsetN2, DsetN3, DsetN4, DsetN5, DsetN6, DsetN7, DsetN8, DsetN9, DsetN10, DsetN11, DsetN12, DsetN13, DsetN14, DsetN15 | |
| 4: Setting Group Selection | Sg1, SgN1a | Sg3 |
| 5: Unbuffered Reporting | Rp1, Rp2, Rp3, Rp4, Rp7, Rp10, Rp12 RpN1, RpN2, RpN3, RpN4 | Rp5, Rp6, Rp8, Rp9, RpN5 |
| 6: Buffered Reporting | Br1, Br2, Br3, Br4, Br7, Br8, Br9, Br12, Br14 BrN1, BrN2, BrN3, BrN4, BrN5 | Br5, Br6, Br10, Br11 |
| 6+: Enhanced buffered reporting | BrE1, BrE2, BrE3, BrE6, BrE7, BrE8, BrE9, BrE10, BrE11 | BrE12 |
| 9a: GOOSE publish | Gop2, Gop3, Gop4, Gop7, Gop10a | Gop1, Gop6, GopN1 |
| 9b: GOOSE subscribe | Gos1a, Gos2, Gos3, GosN1, GosN2, GosN3, GosN4, GosN5, GosN6 | Gos1b |
| 12a: Direct control | CtiN3, CtiN8 DOs1, DOs3 | CtiN11 |
| 12c: Enhanced Direct Control | CtiN3, CtiN8 DOes2, DOes5 | CtiN11 |
| 12d: Enhanced SBO control | Cti3, CtiN1, CtiN2, CtiN3, CtiN4, CtiN9 SBOes1, SBOes2, SBOes3 | CtiN11 |
| 13: Time sync | Tm1, Tm2, TmN1 | |
| 14: File transfer | Ft1, Ft2ab, Ft4, FtN1ab | |