




1 IF IN DOUBT ASK  
DO NOT SCALE



**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**



Copyright © 2011 Siemens Protection Devices Ltd. Hebburn

2 RDW	19.07.13	RETAINING SCREW POSITION CHANGED.
30/7/13	19.07.13	MN435/3650, 3J1770, KB
1	25/07/11	CHANGE NOTED

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked  $\nabla$

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined dimensions  $\pm$  \_\_\_\_\_

Limits on untoleranced machined dimensions to B.S.4500:

i.e. up to 6 $\pm$ 0.1; over 30 to 120 $\pm$ 0.3; over 315 $\pm$ 0.8.

General unmachined angular tolerance  $\pm$  \_\_\_\_\_

Finish: \_\_\_\_\_

Treatment: \_\_\_\_\_

Title: 7SR224, E10, TERMINAL ID & WIRING DIAGRAM  
4I,6V,33BI,2C0,11NO,1NC, RS485 & ETHERNET(x2) COMMS

**SIEMENS PROTECTION DEVICES LTD.**

Original Scale: NTS

First used on: \_\_\_\_\_

Similar Articles: \_\_\_\_\_

Supersedes: \_\_\_\_\_

Drq. No. **2435W40075**

DRAWN KB	CHECKED RD.WATSON	APPROVED RD.WATSON	DATE 02/12/2011	IE	OPS	PCP	Purch.Spec.	TQ	EAC	CE	STD	A3
----------	-------------------	--------------------	-----------------	----	-----	-----	-------------	----	-----	----	-----	----