

- NOTES**
- TERMINALS RECOMMENDED ARE PRE INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
  - FOR OUTLINE & DRILLING DRG SEE 2995X10013 (A4).
  - IRIG-B & FIBRE OPTIC CONNECTORS MUST BE DISCONNECTED & FIXING NUTS REMOVED BEFORE WITHDRAWING CONTROLLER MODULE.

<b>SUPPLIER</b>	<b>AMP</b>	<b>CABLE SIZE</b>
AMP	342103	0.25-1.6 SQ MM
AMP	342143	1.0-2.6 SQ MM.

OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.

2 ROW	13/08/03	MKS13/240 MM
1	02/05/02	CHANGE
ISSUE	DATE	NOTED


Copyright © 2002 VATECH REYROLLE ACP Ltd. Hebburn

First used on:  
Similar Articles:  
Supersedes:  
Original Scale:  
Drg. No. **2471W11004**

**VATECH REYROLLE**  
AUTOMATION, CONTROL & PROTECTION

NTS

EAC CE STD A1



**ABBREVIATIONS**

CT	CURRENT INPUTS
VT	VOLTAGE INPUTS
SI	STATUS INPUTS
CO	CHANGE OVER OUTPUT CONTACTS
NO	NORMALLY OPEN OUTPUT CONTACTS
NC	NORMALLY CLOSED OUTPUT CONTACTS

**MATERIAL:**  
Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ±  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ±

**MODULE LABEL KEY**

ANALOGUE MODULE	AN 1 etc
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

**RELAY VIEWED FROM REAR**

**NOT SUBJECT TO UPDATE ONCE COPIED / PRINTED OR DOWNLOADED**