



1 IF IN DOUBT ASK
2 DO NOT SCALE

NOTES

- 1) TERMINALS RECOMMENDED ARE PRE-INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
- SUPPLIER PART NUMBER CABLE SIZE
AMP 342103 0.25-1.6mm²
AMP 342143 1.0-2.6mm²
- OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.
- 2) FOR OUTLINE & PANEL DRILLING, SEE 2995X10004 (A4).
- 3) CONNECTIONS TO THIS COMMUNICATIONS FACILITY IS BY SCREENED, TWISTED PAIR CABLE ON SITE. WHEN WIRING OTHER FACILITIES ENSURE THAT THESE TERMINALS ARE NOT OBSCURED BY OTHER WIRE RUNS.
- 4) CONTACTS SHOWN THUS ARE INTERNAL RELAY CASE ASSEMBLY CONTACTS AND CLOSE WHEN THE RELAY CHASSIS IS WITHDRAWN FROM THE CASE.
- 5) FOR THE RELAY CASE ASSEMBLY SEE 2436G40006



RELAY VIEWED FROM REAR



ABBREVIATIONS

I-CURRENT INPUTS
V-VOLTAGE INPUTS
BI-BINARY INPUTS
BO-BINARY OUTPUTS
CO-CHANGE OVER BINARY OUTPUT CONTACTS
NO-NORMALLY OPEN BINARY OUTPUT CONTACTS
NC-NORMALLY CLOSED BINARY OUTPUT CONTACTS

COMMUNICATIONS IDENTIFICATION

COM1	RS485 (ON BLOCK 'B' TERMINALS 14,16,18 & 20)
COM2	USB TYPE 'B' PORT (ON RELAY FRONT LABEL)

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.

Machine where marked ∇

For explanation of dimensions, tolerances, notes etc. see B.S.308.

Limit on untoleranced unmachined dimensions \pm

Limits on untoleranced machined dimensions to B.S.4500;

ie. up to 6 \pm 0.1; over 30 to 120 \pm 0.3; over 315 \pm 0.8;
over 6 to 30 \pm 0.2; over 120 to 315 \pm 0.5;

General unmachined angular tolerance \pm

Copyright © 2008 Siemens Protection Devices Ltd. Hebburn

3	N.C	27.03.14	TITLE CHANGED TO SHOW 7SR1 INSTEAD OF 7SR12 MN436/3765.320049 JS
2	RDW	12.12.08	TERM. B1,3,5,7 WERE BO 6,7,8 TERM. B9,11,13,15 WERE BI 4,5,6 TERM. A9 WAS BI 4 COM TERM. A11 WAS BI 5 COM MN436/3047 KB
1		05/09/08	CHANGE NOTED ∇

First used on:

Similar Articles:

Supersedes:

Original Scale.

Dwg. No.

NTS

2436W40006

DRAWN K.BURDON CHECKED K.BURDON

APPROVED RD.WATSON

DATE 05/09/08

IE

OPS

PCP

Purch.Spec. TQ

EAC

CE

STD

A3