

SIEMENS

Ingenuity for life

SIPROTEC 7SA82

Distance protection relay

www.siemens.com/siprotec

Description

The SIPROTEC 7SA82 distance protection has been designed particularly for the cost-optimized and compact protection of lines in medium-voltage and high-voltage systems. With its flexibility and the powerful DIGSI 5 engineering tool, the SIPROTEC 7SA82 device offers future-oriented system solutions with high investment security and low operating costs.

Main function	Distance protection for medium-voltage and high voltage applications
Tripping	3-pole, minimum tripping time: 19 ms
Inputs and outputs	4 current transformers, 4 voltage transformers, 11 or 23 binary inputs, 9 or 16 binary outputs
Hardware flexibility	Different hardware quantity structures for binary inputs and outputs are available in the 1/3 base module. Adding 1/6 expansion modules is not possible; available with large or small display.

Applications

- Detection and selective 3-pole tripping of short circuits in electrical equipment of star networks, lines with infeed at one or two ends, parallel lines and open-circuited or closed ring systems of all voltage levels
- Detection of ground faults in isolated or arc-suppression-coilground power systems in star, ring, or meshed arrangement
- Backup protection for differential protection devices of all kind for lines, transformers, generators, motors, and busbars
- Phasor Measurement Unit (PMU)



SIPROTEC 7SA82

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Minimum tripping time: 19 ms
- 6 independent measuring loops (6-system distance protection)
- Several distance-protection functions can be selected: Classic, reactance method (RMD), impedance protection for transformers
- Directional backup protection and various additional functions
- Detection of ground faults of any type in compensated or isolated electrical power systems using the following functions: $3I_0>$, $V_0>$, fleeting contact, $\cos \phi$, $\sin \phi$, harmonic, dir. Detection of intermittent ground faults and admittance
- Ground fault detection using the pulse detection method

Compact and reliable

- Adaptive power-swing blocking
- Detection of current-transformer saturation for fast tripping with high accuracy
- Arc protection
- Automatic frequency relief for underfrequency load shedding, taking changed infeed conditions due to decentralized power generation into consideration
- Power protection, configurable as active or reactive power protection
- Directional reactive power undervoltage protection (QU protection)
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as thermal overload protection) and operational measured values
- Ground fault detection using the pulse detection method
- Control, synchrocheck and switchgear interlocking protection
- Graphical logic editor to create powerful automation functions in the device
- Single-line representation in small or large display
- Integrated electrical Ethernet RJ45 for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- 2 optional, pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Serial protection data communication via optical fibers, two wire connections and communication networks (IEEE C37.94, and others), including automatic switchover between ring and chain topology
- Reliable data transmission via PRP and HSR redundancy protocols
- Extensive cyber security functionality, such as role-based access control (RBAC), protocolling security-related events or signed firmware
- Simple, quick and secure access to device data via a standard Web browser - without additional software
- Phasor measurement unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization using IEEE 1588
- Powerful fault recording (buffer for a max. record time of 80 sec. at 8 kHz or 320 sec. at 2 kHz)
- Auxiliary functions for simple tests and commissioning

Benefits

- Compact and low-cost distance protection
- Safety due to powerful protection functions
- Data security and transparency over the entire lifecycle of the plant, saving time and money
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Increased reliability and quality of the engineering process
- Highest availability even under extreme environmental conditions by “conformal coating “ (coating) of the modular assemblies
- Powerful communication components warrant safe and effective solutions
- Full compatibility between IEC 61850 Editions 1 and 2



Siemens AG

Energy Management Division
Freyeslebenstraße 1
91058 Erlangen, Germany

SIPROTEC 7SA82 Profile E7.8.docx
Printed in Germany | © 09.18 Siemens AG

E-Mail: support.energy@siemens.com
Tel: +49 180 524 70 00

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org), cryptographic software written by Eric Young (eay@cryptsoft.com) and software developed by Bodo Moeller.