

SIEMENS

Ingenuity for life

SIPROTEC 7SA86

Distance protection

www.siemens.com/siprotec

Description

The SIPROTEC 7SA86 distance protection has been designed specifically for the protection of lines. With its modular structure, flexibility and the high-performance DIGSI 5 engineering tool, the SIPROTEC 7SA86 device offers future-oriented solutions for protection, control, automation, monitoring, and Power Quality – Basic.

Main function	Distance Protection Interoperability of SIPROTEC 4 and SIPROTEC 5 line protection devices
Tripping	3-pole, minimum tripping time: 9 ms
Inputs and outputs	12 predefined standard variants with 4/4 or 8/8 current transformers/voltage transformers, 5 to 31 binary inputs, 8 to 46 binary outputs
Hardware quantity structure	Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system
Housing width	1/3 × 19 inch to 2/1 × 19 inch

Applications

- Detection and selective 3-pole tripping of short circuits in electrical equipment of star networks, lines with infeed at one or 2 ends, parallel lines, and open-circuited or closed ring systems of all voltage levels
- Detection of ground faults in isolated or arc-suppression-coilground systems in star, ring, or meshed arrangement
- Serial protection communication with SIPROTEC 5 and SIPROTEC 4 devices over different distances and physical media, such as optical fiber, two-wire connections, and communication networks
- Backup protection for differential protection devices of all kind for lines, transformers, generators, motors, and busbars
- Phasor Measurement Unit (PMU)



SIPROTEC 5 Device with Expansion Module

- Detection and recording of power-quality data in the mediumvoltage and subordinate low-voltage power system

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Minimum tripping time: 9 ms
- 6 independent measuring loops (6-system distance protection)
- Several distance-protection functions can be selected: Classic, reactance method (RMD), impedance protection for transformers
- Directional backup protection and various additional functions
- Detection of ground faults of any type in compensated or isolated electrical power systems using the following functions: $3I_0>$, $V_0>$, transient ground fault, $\cos \phi$, $\sin \phi$, dir. detection of intermittent ground faults, harmonic detection, and admittance measurement
- Ground-fault detection using the pulse-detection method
- Adaptive power-swing blocking, out-of-step protection

Efficient and modular

- Detection of current-transformer saturation for fast tripping with high accuracy
- Fault locator plus for accurate fault location with in-homogenous line sections and targeted automatic overhead line section reclosing (AREC)
- Arc protection
- Automatic frequency relief for underfrequency load shedding, taking changed infeed conditions due to decentralized power generation into consideration
- Power protection, configurable as active or reactive-power protection
- Directional reactive-power undervoltage protection (QU protection)
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as thermal overload protection) and operational measured values
- PQ - Basic: Voltage unbalance; voltage changes: over-voltage, dip, interruption; TDD, THD, and harmonics
- 3-pole automatic reclosing function
- Control, synchrocheck, and switchgear interlocking protection
- Graphical logic editor to create high-performance automation functions in the device
- Single-line representation in the small or large display
- Fixed integrated electrical Ethernet RJ45 interface for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- Up to 4 optional, pluggable communication modules, usable for different and redundant protocols (IEC 61850-8-1, IEC 61850-9-2 Client, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO, PROFINET IO S2 redundancy)
- Virtual network partitioning (IEEE 802.1Q - VLAN)
- Serial protection communication via optical fibers, two-wire connections, and communication networks (IEEE C37.94 and others), including automatic switch-over between ring feeder and chain topology
- Reliable data transmission via PRP and HSR redundancy protocols
- Extensive cybersecurity functionality, such as role-based access control (RBAC), logging of security-related events, signed firmware, or authenticated IEEE 802.1X network access.
- Simple, fast, and secure access to the device via a standard Web browser to display all information and diagnostic data, vector diagrams, single-line and device display pages
- Phasor Measurement Unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization using IEEE 1588
- High-performance fault recording (buffer for a max. record time of 80 s at 8 kHz or 320 s at 2 kHz)
- Auxiliary functions for simple tests and commissioning
- Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system

Benefits

- Safety due to powerful protection functions
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Cybersecurity in accordance with NERC CIP and BDEW Whitepaper requirements
- Highest availability even under extreme environmental conditions by standard coating of the modules
- Full compatibility between IEC 61850 Editions 1, 2.0, and 2.1



Siemens 2020
Smart Infrastructure
Digital Grid
Humboldtstrasse 59
90459 Nuremberg,
Germany

For the U.S. published by
Siemens Industry Inc.

100 Technology Drive
Alpharetta, GA 30005
United States

Customer Support: <http://www.siemens.com/csc>

© Siemens 2020. Subject to changes and errors.
SIPROTEC 7SA86_Profile V1.docx_12.20

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org), cryptographic software written by Eric Young (eay@cryptsoft.com) and software developed by Bodo Moeller.