




IF IN DOUBT ASK  
DO NOT SCALE



PANEL CUT-OUT



25mm MIN. CLEARANCE FOR TERMINAL WIRING



NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED

**DRAWING OFFICE ONLY NOTE**

ANY CHANGE TO THIS DRG MUST BE REFLECTED  
ON DRG 2995X10017 & CATALOGUE

**MATERIAL:**

**NOTE:**

THE  $\phi 3.6$  HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS. THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY  $\phi 4.5$ ) AND RELAYS MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS (SUPPLIED IN PANEL FIXING KIT).

4 RDW	04/06/07	MN95/2883 (AL)
3 RDW	27/09/06	MN95/2462 (ML/RDW)
2	30/7/01	MN95/2125
1	09/07/99	CHANGE
ISSUE	DATE	NOTED

Copyright © 1999 Reyrolle Ltd.

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked   
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions  $\pm$  \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to  $6\pm 0.1$ ; over 30 to  $120\pm 0.3$ ; over 315  $\pm 0.8$ ;  
over 6 to  $30\pm 0.2$ ; over 120 to  $315\pm 0.5$ ;  
General unmachined angular tolerance  $\pm$  \_\_\_\_\_

Finish:   
Treatment:

Title:  
**OVERALL DIMENSIONS AND PANEL DRILLING  
FOR EPSILON E2 CASE.**

**Reyrolle Protection  
Hebburn.**

Original Scale:  
**1:2**

First used on:  
Similar Articles:  
Supersedes:  
Drg.No.  
**2995X10002**

DRAWN: A.LAW	CHECKED:	APPROVED: R.D.WATSON	DATE: 25/01/02	I.E.	OPS.	PCP.	Purch. Spec.	TQ.	EAC	CE.	STD.	A4h
--------------	----------	----------------------	----------------	------	------	------	--------------	-----	-----	-----	------	-----