

SIEMENS

Ingenuity for life

SIPROTEC 7SL87

Combined line differential and distance protection

www.siemens.com/siprotec

Description

The combined SIPROTEC 7SL87 line differential and distance protection has specifically been designed for the protection of lines. With its modular structure, flexibility and the powerful DIGSI 5 engineering tool, SIPROTEC 7SL87 offers future-oriented system solutions with high investment security and low operating costs.

| | |
|----------------------|---|
| Main function | Differential and distance protection |
| Tripping | 1-pole and 3-pole, minimum tripping time: 9 ms |
| Inputs and outputs | 12 predefined standard variants with 4/4 or 8/8 current/voltage transformers, 5 to 31 binary inputs, 8 to 46 binary outputs |
| Hardware flexibility | Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system |
| Housing width | 1/3 x 19" to 2/1 x 19" |

Applications

- Line protection for all voltage levels with 1-pole and 3-pole tripping
- Phase-selective protection of overhead lines and cables with single-ended and multi-ended infeed of all lengths with up to 6 line ends
- Also used in switchgear with breaker-and-a-half configuration
- Transformers and compensating coils in the protection zone
- Phasor measurement unit (PMU)



Combined line differential and distance protection device SIPROTEC 7SL87 (housing width: 1/3 x 19" to 2 x 19")

- Detection of ground faults in isolated or arc-suppression-coilground power systems in star, ring, or meshed arrangement
- Protection data communication over different distances and physical media, such as optical fiber, two-wire connections, and communication networks

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Minimum tripping time: 9 ms
- Main protection function is differential protection with adaptive algorithm for maximum sensitivity and stability even with the most different transformer errors, current-transformer saturation and capacitive charging currents
- 1-/3-pole automatic reclosing function

Efficient and modular

- Several distance-protection functions as backup protection or 2nd main protection for selection: Classic, reactance method (RMD), impedance protection for transformers
- Directional backup protection and various additional functions
- Adaptive power-swing blocking, out-of-step protection
- Detection of current-transformer saturation for fast tripping with high accuracy Arc protection
- Reactive power-undervoltage protection (QU protection)
- Detection of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as thermal overload protection) and operational measured values
- Control, synchrocheck and switchgear interlocking protection
- Graphical logic editor to create powerful automation functions in the device
- Single line representation in small or large display
- Integrated electrical Ethernet RJ45 for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- Up to 4 optional pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Serial protection data communication via optical fibers, two-wire connections and communication networks (IEEE C37.94, and others), including automatic switchover between ring and chain topology
- Redundancy protocols PRP and HSR
- Cyber security in accordance with NERC CIP and BDWE Whitepaper requirements
- Phasor measurement unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization using IEEE 1588
- Powerful fault recording (buffer for a max. record time of 80 s at 8 kHz or 320 s at 2 kHz)
- Auxiliary functions for simple tests and commissioning
- Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system

Benefits

- Compact and cost effective line differential and distance protection device
- High-performance protection features guarantee safety
- Data security and transparency throughout the entire life cycle of the system save time and reduce costs
- Clear and easy-to-use devices and software thanks to user-friendly design
- Increased quality and reliability of the engineering process
- High degree of overall safety and security based on thorough implementation
- High-performance communications components guarantee safe and effective solutions
- Full compatibility with IEC 61850 Edition 1 and 2
- Future proof system solutions provide high investment security and low operation costs



Siemens AG 2016
Energy Management Division
Freyeslebenstraße 1
91058 Erlangen, Germany

SIPROTEC 7SL87 V7 Profile.docx
Printed in Germany | © 07.16 Siemens AG

E-Mail: support.energy@siemens.com
Tel: +49 180 524 70 00

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org) and cryptographic software written by Eric Young (eay@cryptsoft.com).