


1 IF IN DOUBT ASK
2 DO NOT SCALE

NOTES


- 1) TERMINALS RECOMMENDED ARE PRE-INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP P/DG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
- SUPPLIER PART NUMBER CABLE SIZE
AMP 342103 0.25-1.6mm²
AMP 342143 1.0-2.6mm²
- OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.
- 2) CONTACTS SHOWN THUS ARE INTERNAL RELAY CASE ASSEMBLY CONTACTS AND CLOSE WHEN THE RELAY CHASSIS IS WITHDRAWN FROM THE CASE.
- 3) FOR OUTLINE & DRILLING DRG SEE 2995X10006 (A4).



TYPICAL RELAY VIEWED FROM REAR

ABBREVIATIONS

I-CURRENT INPUTS
BI-BINARY INPUTS
BO-BINARY OUTPUTS
COM-COMMON BINARY OUTPUT CONTACTS
NO-NORMALLY OPEN BINARY OUTPUT CONTACTS
NC-NORMALLY CLOSED BINARY OUTPUT CONTACTS



Copyright © 2015 Siemens Protection Devices Ltd. Hebburn

3 N.C	19/05/15	RS485 ADDED 41,42,43,44 BO 7 WAS TERM 16-17 MNS3870-436 JS
2 I.D	27/03/15	BO 8 WAS TERM 37-38 MNS3855-436 JS
1	26/02/15	CHANGE NOTED

MATERIAL:
Dimensions in millimetres : Surface texture in micrometres:
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ±
Limits on untoleranced machined dimensions to B.S.4500:
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ±

Finish:
Treatment:

Title:
TERMINAL ID & WIRING DIAGRAM FOR 7SR1192
4CT+5BI+8BO

Original Scale:

First used on:
Similar Articles:
Supersedes:

Drg. No.
2436W50002

DRAWN J SPOWART
CHECKED J BIRD
APPROVED I.DALZIEL

DATE 04/03/15
IE

OPS
PCP
Purch.Spec. TQ

EAC

OE

STD
A3

SIEMENS PROTECTION DEVICES LTD.

NTS

**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**