






IF IN DOUBT ASK
DO NOT SCALE



MODULE LABEL KEY	
ANALOGUE MODULE	AN 1 etc
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

Controller Module
SEE NOTE 3



RELAY VIEWED FROM REAR

- NOTES
- TERMINALS RECOMMENDED ARE PRE INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
 - FOR OUTLINE & DRILLING DRG SEE 2995X10013 (A4).
 - IRIG-B & FIBRE OPTIC CONNECTORS MUST BE DISCONNECTED & FIXING NUTS REMOVED BEFORE WITHDRAWING CONTROLLER MODULE.

SUPPLIER	AMP	CABLE SIZE
AMP	342103	0.25-1.6 SQ MM
AMP	342143	1.0-2.6 SQ MM.

OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.

ABBREVIATIONS	
CT	CURRENT INPUTS
VT	VOLTAGE INPUTS
SI	STATUS INPUTS
CO	CHANGE OVER OUTPUT CONTACTS
NO	NORMALLY OPEN OUTPUT CONTACTS
NC	NORMALLY CLOSED OUTPUT CONTACTS

MATERIAL:
Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ±
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ±

Finish:	Title: TERMINAL ID & WIRING DIAGRAM FOR FM1-1XX-XH (4CT,27SI,3CO,10NO) IN E12 VERTICAL CASE	First used on:
Treatment:	VA TECH Reyrolle AUTOMATION, CONTROL & PROTECTION	Similar Articles:
Copyright © 2000 VA TECH Reyrolle Ltd. Hebburn	Original Scale: NTS	Supersedes:
DATE 13/6/01	DRG. No. 2471W11002	ISSUE DATE NOTED
EAC	CE	STD

NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

4 ROW	13/08/03	WNS13/2440 MM
3	13/06/01	SEF CT INFORMATION ADDED WNS13/2091 MM
2	27/02/00	MODULE LABEL & POSTIN ADDED MNV1008/2719
1	23/10/00	CHANGE