


RELAY VIEWED FROM REAR



MODULE LABEL KEY	
ANALOGUE MODULE	AN 1 etc
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

ABBREVIATIONS	
CT	CURRENT INPUTS
VT	VOLTAGE INPUTS
SI	STATUS INPUTS
CO	CHANGE OVER OUTPUT CONTACTS
NO	NORMALLY OPEN OUTPUT CONTACTS
NC	NORMALLY CLOSED OUTPUT CONTACTS

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ±  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ±

Finish: \_\_\_\_\_ Title: TERM IDENT & WIRING DIAGRAM FOR MSCDN-MP2B (6CT+4VT,19SI,3CO,18NO) E16 CASE

Treatment: \_\_\_\_\_ Original Scale: NTS

Copyright © 2002 VA TECH Reyrolle Ltd. Hebburn

First used on: \_\_\_\_\_ Drg. No. 2621W11003

Similar Articles: \_\_\_\_\_

Supersedes: \_\_\_\_\_

2 ROW 19/08/03 MNS13/240 MM  
1 19/11/02 CHANGE  
ISSUE DATE NOTED

DRAWN M LEASK CHECKED RD.WATSON APPROVED RD.WATSON DATE 20/11/02 IE OPS PCP Purch.Spec. TQ EAC CE STD A1

NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED