




IF IN DOUBT ASK  
DO NOT SCALE



**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**

- NOTES**
- 1 TYPICAL VT EARTHING.
  - 2 FOR TYPICAL SCHEMATIC DIAGRAM SHOWING PHASE-PHASE CONNECTIONS SEE 2422W10003 (A3)
  - 3 FOR TYPICAL SCHEMATIC DIAGRAM SHOWING PHASE-NEUTRAL CONNECTIONS SEE 2422W10005 (A3)

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_  
Treatment: \_\_\_\_\_

Title:  
TYPICAL SCHEMATIC DIAGRAM 3 PHASE VOLTAGE/FREQUENCY  
RELAY (USED IN SINGLE PHASE MODE) ARGUS 8

**Reyrolle Protection  
Hebburn.**

Original Scale:  
NTS

First used on: \_\_\_\_\_  
Similar Articles: 2422W10005  
Supersedes: \_\_\_\_\_  
Drg. No.  
**2422W10007**

DRAWN M LEASK	CHECKED	APPROVED R.D.WATSON	DATE 22/07/02	IE	OPS	PCP	Purch.Spec. TQ	EAC	CE	STD	A3
---------------	---------	---------------------	---------------	----	-----	-----	----------------	-----	----	-----	----

Copyright © 2000 Reyrolle Ltd.	1	1/8/00	CHANGE NOTED
ISSUE	DATE		△