

NOTES

1 TERMINALS RECOMMENDED ARE PRE INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.



SUPPLIER	AMP	CABLE SIZE
AMP	342103	0.25-1.6 SQ MM
AMP	342143	1.0-2.6 SQ MM.

OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.

2 FOR OUTLINE & DRILLING DRG SEE 2995X10012 (A4).

3 IRIG-B & FIBRE OPTIC CONNECTORS MUST BE DISCONNECTED & FIXING NUTS REMOVED BEFORE WITHDRAWING CONTROLLER MODULE.

RELAY VIEWED FROM REAR



MODULE LABEL KEY	
ANALOGUE MODULE	NOT FITTED
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

ABBREVIATIONS	
CT	CURRENT INPUTS
VT	VOLTAGE INPUTS
SI	STATUS INPUTS
CO	CHANGE OVER OUTPUT CONTACTS
NO	NORMALLY OPEN OUTPUT CONTACTS
NC	NORMALLY CLOSED OUTPUT CONTACTS

MATERIAL:
 Dimensions in millimetres ; Surface texture in micrometres.
 Machine where marked ✓
 For explanation of dimensions, tolerances, notes etc. see B.S.308.
 Limit on untoleranced unmachined dimensions ±
 Limits on untoleranced machined dimensions to B.S.4500;
 i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
 over 6 to 30±0.2; over 120 to 315±0.5;
 General unmachined angular tolerance ±

Finish:	Title:	TERMINAL I.D. & WIRING FOR IOTA COMMON SERVICES RELAY (19SI, 3CO + 18NO) E12 CASE.
Treatment:	VA TECH Reyrolle AUTOMATION, CONTROL & PROTECTION	

Original Scale: NTS
 Drg. No. 2761W11034

Copyright © 2006 VA TECH Reyrolle Ltd. Hebburn

1	01/02/06	CHANGE NOTED
ISSUE	DATE	NOTED

Copyright © 2006 VA TECH Reyrolle Ltd. Hebburn

First used on: Similar Articles: Supersedes: Drg. No. 2761W11034

Drawn: RDW | Checked: RDW | Approved: RD, WATSON | Date: 01/02/06 | IE: DN | OPS | PCP | Purch. Spec. | TQ | EAC | CE | STD | A1

**NOT SUBJECT TO UPDATE
 ONCE COPIED / PRINTED
 OR DOWNLOADED**

IF IN DOUBT ASK
 DO NOT SCALE