


IF IN DOUBT ASK
DO NOT SCALE

A
B
C
D
E
F
G
H
J
K




RELAY VIEWED FROM REAR

NOTES


- 1 TERMINALS RECOMMENDED ARE PRE INSULATED & MUST BE CRIMPED USING APPROVED TOOLING. AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
- 2 FOR OUTLINE & DRILLING DRG SEE 2995X10012 (A4).
- 3 IRIG-B & FIBRE OPTIC CONNECTORS MUST BE DISCONNECTED & FIXING NUTS REMOVED BEFORE WITHDRAWING CONTROLLER MODULE.

| SUPPLIER | AMP | CABLE SIZE |
|----------|--------|----------------|
| AMP | 342103 | 0.25-1.6 SQ MM |
| AMP | 342143 | 1.0-2.6 SQ MM. |


OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.



VIEW ON REAR OF
VERTICALLY MOUNTED RELAY



Controller Module
(SEE NOTE 3)



| MODULE LABEL KEY | |
|---------------------------|-----------|
| ANALOGUE MODULE | AN 1 etc |
| INPUT/OUTPUT MODULE | I/O 1 etc |
| P.S.U. & BASIC I/O MODULE | P.S.U. |

| ABBREVIATIONS | |
|---------------|---------------------------------|
| CT | CURRENT INPUTS |
| VT | VOLTAGE INPUTS |
| SI | STATUS INPUTS |
| CO | CHANGE OVER OUTPUT CONTACTS |
| NO | NORMALLY OPEN OUTPUT CONTACTS |
| NC | NORMALLY CLOSED OUTPUT CONTACTS |

MATERIAL:
Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ±
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ±

| | | |
|--|--|-------------------|
| Finish: | Title: | First used on: |
| Treatment: | TERM IDENT & WIRING DIAGRAM FOR TAU A/R+CHECK SYNC+ DOUBLE ISOLATOR (2VT,27SI,22NO,4NC,3CO) E12 CASE | Similar Articles: |
| <p align="center">VATECH REYROLLE AUTOMATION, CONTROL & PROTECTION</p> | | Supersedes: |
| Original Scale: | | Original Drg. No. |
| NTS | | 2715W11013 |

**NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED**

| 4 | RDW | 18/08/03 | MNS13/2440 MM |
|-------|----------|----------------|---------------|
| 3 | 27/8/02 | MNS13/2370 RDW | |
| 2 | 02/07/01 | MN715/2112 | |
| 1 | 20/3/01 | CHANGE | |
| ISSUE | DATE | NOTED | △ |