



**NOT SUBJECT TO UPDATE  
ONCE COPIED / PRINTED  
OR DOWNLOADED**

- NOTES
- 1 CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
  - 2 CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
  - 3 APPLICATION SHOWS USE OF SEF/REF AS AN SEF INPUT USE OF THE INPUT FOR HIGH IMPEDANCE REF REQUIRES AN ADDITIONAL SETTING RESISTOR & MAY REQUIRE A METROSIL
  - 4 APPLICATION SHOWS USE OF 5-LIMB STAR CONNECTED VT WITH NEUTRAL VOLTAGE DERIVED INTERNALLY.
  - 5 FOR TERMINAL DIAGRAM SEE 2434W50006 (A2)
  - 6 DRG SHOWS (11 OUTPUTS, 5 INPUTS)

**MATERIAL:**

Dimensions in millimetres : Surface texture in micrometres.  
Machine where marked ✓  
For explanation of dimensions, tolerances, notes etc. see B.S.308.  
Limit on untoleranced unmachined dimensions ± \_\_\_\_\_  
Limits on untoleranced machined dimensions to B.S.4500;  
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;  
over 6 to 30±0.2; over 120 to 315±0.5;  
General unmachined angular tolerance ± \_\_\_\_\_

Finish: \_\_\_\_\_

Treatment: \_\_\_\_\_

Title: ARGUS 2 DIGITAL DIRECTIONAL RELAY  
TYPICAL SCHEME DIAGRAM FOR  
2P DIRECTIONAL P/F, 1P DIRECTIONAL E/F & 1P SEF RELAY  
WITH STAR CONNECTED VT

**VATECH REYROLLE  
AUTOMATION, CONTROL & PROTECTION**

Original Scale:  
NTS

First used on: \_\_\_\_\_  
Similar Articles: 2434W10095  
Supersedes: \_\_\_\_\_  
Drg. No. **2434W10094**