



NOTES

1. CT CIRCUITS ARE SHOWN CONNECTED TO RELAY 1 AMP TAP. USE ALTERNATIVE TAP FOR 5AMP RATED CTs.
2. CT & EARTH CONNECTIONS ARE TYPICAL ONLY.
3. APPLICATION SHOWS USE OF HOLMGREEN CONNECTION FOR E/F CIRCUIT. USE OF SEPERATE RING CORE CT IS ALSO POSSIBLE.
4. APPLICATION SHOWS USE OF 5-LIMB STAR CONNECTED VT WITH SEPARATE OPEN DELTA WINDING PROVIDING THE NEUTRAL VOLTAGE.
5. FOR TERMINAL DIAGRAM SEE 2434W50011 (A2).
6. DRG SHOWS OPTION C (7 OUTPUTS, 9 INPUTS).

NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked ✓
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions ± _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6±0.1; over 30 to 120±0.3; over 315±0.8;
over 6 to 30±0.2; over 120 to 315±0.5;
General unmachined angular tolerance ± _____

Finish: _____

Title:
TYPICAL SCHEMATIC DIAGRAM 3 PH(DIR)+EF(DIR) RS485
ARGUS 2 DIGITAL DIR. OPEN DELTA CONNECTED VT EPSILON

First used on:
Similar Articles: 2434W10091
Supersedes:

Treatment: _____

VATECH REYROLLE
AUTOMATION, CONTROL & PROTECTION

Original Scale.
NTS

Drq. No.
2434W10136

1	12/08/04	CHANGE NOTED
ISSUE	DATE	NOTED