




IF IN DOUBT ASK
DO NOT SCALE



PANEL CUT-OUT



25mm MIN. CLEARANCE FOR TERMINAL WIRING



NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

NOTE:
THE $\phi 3.6$ HOLES ARE FOR M4 THREAD FORMING (TRILOBULAR) SCREWS. THESE ARE SUPPLIED AS STANDARD AND ARE SUITABLE FOR USE IN FERROUS/ALUMINIUM PANELS 1.6mm THICK AND ABOVE. FOR OTHER PANELS, HOLES TO BE M4 CLEARANCE (TYPICALLY $\phi 4.5$) AND RELAYS MOUNTED USING M4 MACHINE SCREWS, NUTS AND LOCKWASHERS (SUPPLIED IN PANEL FIXING KIT).

4 RDW	04/06/07	MN95/2883 (AL)
3 RDW	27/09/06	MN95/2462 (ML/RDW)
2	30/7/01	MN95/2125
1	09/07/99	CHANGE
ISSUE	DATE	NOTED

DRAWING OFFICE ONLY NOTE

ANY CHANGE TO THIS DRG MUST BE REFLECTED ON DRG 2995X10017 & CATALOGUE

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
Machine where marked
For explanation of dimensions, tolerances, notes etc. see B.S.308.
Limit on untoleranced unmachined dimensions \pm _____
Limits on untoleranced machined dimensions to B.S.4500;
i.e. up to 6 ± 0.1 ; over 30 to 120 ± 0.3 ; over 315 ± 0.8 ;
over 6 to 30 ± 0.2 ; over 120 to 315 ± 0.5 ;
General unmachined angular tolerance \pm _____

Finish:
Treatment:

Title:
OVERALL DIMENSIONS AND PANEL DRILLING FOR EPSILON E2 CASE.

**Reyrolle Protection
Hebburn.**

Original Scale:
1:2

First used on:
Similar Articles:
Supersedes:
Drg.No.
2995X10002

Copyright © 1999 Reyrolle Ltd.

DRAWN: A.LAW	CHECKED:	APPROVED: R.D.WATSON	DATE: 25/01/02	I.E.	OPS.	PCP.	Purch. Spec.	TQ.	EAC	CE.	STD.	A4h
--------------	----------	----------------------	----------------	------	------	------	--------------	-----	-----	-----	------	-----