



- NOTES
- 1 TERMINALS RECOMMENDED ARE PRE INSULATED & MUST BE CRIMPED USING APPROVED TOOLING.
AMP PIDG OR PLASTI GRIP FUNNEL ENTRY (RING TONGUE) FOR M4 FIXING STUD.
 - 2 FOR OUTLINE & DRILLING DRG SEE 2995X10008 (A4).
 - 3 IRIG-B & FIBRE OPTIC CONNECTORS MUST BE DISCONNECTED & FIXING NUTS REMOVED BEFORE WITHDRAWING CONTROLLER MODULE.
- | SUPPLIER | AMP | CABLE SIZE |
|----------|--------|----------------|
| AMP | 342103 | 0.25-1.6 SQ MM |
| AMP | 342143 | 1.0-2.6 SQ MM. |
- OR ANY OTHER MANUFACTURERS EQUIVALENT TERMINAL.



NOT SUBJECT TO UPDATE
ONCE COPIED / PRINTED
OR DOWNLOADED

MODULE LABEL KEY	
ANALOGUE MODULE	AN 1 etc
INPUT/OUTPUT MODULE	I/O 1 etc
P.S.U. & BASIC I/O MODULE	P.S.U.

MATERIAL:

Dimensions in millimetres : Surface texture in micrometres.
 Machine where marked V
 For explanation of dimensions, tolerances, notes etc. see BS.308.
 Limit on unrounded unnotched dimensions is BS.4500.
 Limits to BS.4013: over 30 to 120±0.3; over 120 to 315±0.5;
 over 315 to 630±0.7; over 630 to 1250±1.0; over 1250 to 3150±1.5.
 General unnotched angular tolerance ±.

ABBREVIATIONS	
CT-CURRENT INPUTS	
VT-VOLTAGE INPUTS	
SI-STATUS INPUTS	
CO-CHANGE OVER OUTPUT CONTACTS	
NO-NORMALLY OPEN OUTPUT CONTACTS	
NC-NORMALLY CLOSED OUTPUT CONTACTS	

Copyright © 2013 Siemens Protection Devices Ltd, Habburn

TERM IDENT & WIRING DIAGRAM FOR DU3-204-XA RELAYS WITH (7CT + 1XREF/SEF CT, 3SI, 0/P=300+2N0) EB CASE

SIEMENS PROTECTION DEVICES LTD.

DRAWN: J. BURNETT CHECKED: RO. WATSON APPROVED: RO. WATSON DATE: 11/02/2013

Original Scale: NTS
 Dwg. No. 2661W11052

ISSUE	DATE	CHANGE
1		