

7SR210 Non-Directional Relay MICS (Model Implementation Conformance Statement)

Description of the IEC61850 device mapping.

The copyright and other intellectual property rights in this document, and in any model or article produced from it (and including any registered or unregistered design rights) are the property of Siemens Protection Devices Limited. No part of this document shall be reproduced or modified or stored in another form, in any data retrieval system, without the permission of Siemens Protection Devices Limited, nor shall any model or article be reproduced from this document unless Siemens Protection Devices Limited consent.

While the information and guidance given in this document is believed to be correct, no liability shall be accepted for any loss or damage caused by any error or omission, whether such error or omission is the result of negligence or any other cause. Any and all such liability is disclaimed.

Document Release History

This document is issue 2016/02. The list of revisions up to and including this issue is: -

2011/05	First issue.
2013/01	Typographical revisions and added data. Updated in line with software release.
2014/06	Typographical revisions and added data. Updated in line with software release.
2015/06	Typographical revisions and added data. Updated in line with software release.
2016/02	Typographical revisions and added data. Updated in line with software release.

Software Revision History

2011/05	2435H85008R7a-7a (7SR210)	First Release
2013/01	2435H85008R7c-7b (7SR210)	Introduced journaling file system. Added 61850 logical nodes for CB Counters, metering, 50BF, 46BC, 81HBL2 and line check. Added Line Check on non-AR devices. Added 74CCS Close Circuit Supervision.
2014/06	2435H85008R7f-7d (7SR210)	Fault data transmission over IEC 60870-5-103. Additional communications data, control features, meters.
2015/06	2435H85008R8a-7f (7SR210)	Arc Flash Detector. Over current TM Setting Range extended.
2016/02	2435H85008R8b-7f (7SR210)	EN100+ Compatibility.

CONTENTS

DOCUMENT RELEASE HISTORY	2
SOFTWARE REVISION HISTORY	ERROR! BOOKMARK NOT DEFINED.
1. REYROLLE 7SR210 – IEC61850	6
1.1 Function – Device	6
1.2 AR Lockout Trip Counters.....	12
1.3 Autoreclose	12
1.4 BROKEN CONDUCTOR MENU	12
1.5 CB E/F Trip Counter	13
1.6 CB FAIL.....	13
1.7 CB Ph A Trip Counter	13
1.8 CB Ph B Trip Counter	13
1.9 CB Ph C Trip Counter	14
1.10 Change Group	14
1.11 CURRENT METERS.....	14
1.12 Delta Trip Counters	15
1.13 DERIVED EARTH FAULT MENU.....	15
1.14 Disturbance Recorder.....	16
1.15 Double Point Controls (Enhanced Security)	17
1.16 Double Point Controls (Normal Security)	17
1.17 Double Point Inputs.....	17
1.18 Double Point Outputs.....	18
1.19 General Trip Information	19
1.20 INRUSH DETECTOR	19
1.21 LINE CHECK.....	19
1.22 MEASURED EARTH FAULT MENU	21
1.23 NEUTRAL OVERVOLTAGE	22
1.24 NPS OVERCURRENT MENU	23
1.25 NPS OVERVOLTAGE	23
1.26 OVERCURRENT MENU.....	24
1.27 PHASE U/O VOLTAGE.....	27
1.28 RESTRICTED EARTH FAULT	29
1.29 SENSITIVE EARTH FAULT MENU	29
1.30 Single Point Controls (Enhanced Security)	31
1.31 Single Point Controls (Normal Security)	31
1.32 Single Point Inputs	31
1.33 Single Point Outputs	33
1.34 THERMAL MENU	35
1.35 U/O FREQUENCY	35
1.36 UNDER CURRENT MENU	37
1.37 VOLTAGE METERS	38
1.38 Vx U/O VOLTAGE	38
2. IEC 61850 -> REYROLLE	39
2.1 PROT	39
2.1.1 A2759PTOV1	39

2.1.2	A2759PTOV2	39
2.1.3	A2759PTOV3	40
2.1.4	A2759PTOV4	40
2.1.5	A2759PTOV5	41
2.1.6	A2759PTUV1	41
2.1.7	A2759PTUV2	41
2.1.8	A2759PTUV3	42
2.1.9	A2759PTUV4	42
2.1.10	A2759PTUV5	43
2.1.11	A37gPTUC1	43
2.1.12	A37gPTUC2	43
2.1.13	A37PTUC1.....	44
2.1.14	A37PTUC2.....	44
2.1.15	A37SefPTUC1	45
2.1.16	A37SefPTUC2	45
2.1.17	A46BcPTOC1.....	45
2.1.18	A46DtPTOC1.....	45
2.1.19	A46ItPTOC1	46
2.1.20	A47PTOV1	46
2.1.21	A47PTOV2	46
2.1.22	A49PTTR1	47
2.1.23	A50BfRBRF1	47
2.1.24	A50gLCPTOC1	47
2.1.25	A50gLCPTOC2	48
2.1.26	A50gPTOC1	48
2.1.27	A50gPTOC2	48
2.1.28	A50gPTOC3	49
2.1.29	A50gPTOC4	49
2.1.30	A50LCPTOC1	49
2.1.31	A50LCPTOC2	50
2.1.32	A50nPTOC1	50
2.1.33	A50nPTOC2	50
2.1.34	A50nPTOC3	51
2.1.35	A50nPTOC4	51
2.1.36	A50PTOC1	51
2.1.37	A50PTOC2	52
2.1.38	A50PTOC3	52
2.1.39	A50PTOC4	53
2.1.40	A50SefLCPTOC1	53
2.1.41	A50SefLCPTOC2	53
2.1.42	A50SefPTOC1	54
2.1.43	A50SefPTOC2	54
2.1.44	A50SefPTOC3	54
2.1.45	A50SefPTOC4	55
2.1.46	A51gPTOC1	55

2.1.47	A51gPTOC2	55
2.1.48	A51gPTOC3	56
2.1.49	A51gPTOC4	56
2.1.50	A51nPTOC1	56
2.1.51	A51nPTOC2	57
2.1.52	A51nPTOC3	57
2.1.53	A51nPTOC4	57
2.1.54	A51PTOC1	58
2.1.55	A51PTOC2	58
2.1.56	A51PTOC3	59
2.1.57	A51PTOC4	59
2.1.58	A51SefPTOC1	60
2.1.59	A51SefPTOC2	60
2.1.60	A51SefPTOC3	60
2.1.61	A51SefPTOC4	61
2.1.62	A59nDtPTOV1	61
2.1.63	A59nItPTOV1	61
2.1.64	A64hPTOC1	62
2.1.65	A81Hb2PHAR1	62
2.1.66	A81PTOF1	62
2.1.67	A81PTOF2	63
2.1.68	A81PTOF3	63
2.1.69	A81PTOF4	63
2.1.70	A81PTOF5	64
2.1.71	A81PTOF6	64
2.1.72	A81PTUF1	64
2.1.73	A81PTUF2	65
2.1.74	A81PTUF3	65
2.1.75	A81PTUF4	65
2.1.76	A81PTUF5	66
2.1.77	A81PTUF6	66
2.1.78	LLNO	66
2.1.79	PTRC1	67
2.2	MEAS	67
2.2.1	I_MSQI1	67
2.2.2	LLNO	67
2.2.3	V_MSQI1	68
2.3	DR	68
2.3.1	LLNO	68
2.3.2	RDRE1	68
2.4	CTRL	69
2.4.1	BI13GGIO1	69

1. REYROLLE 7SR210 – IEC61850

1.1 Function – Device

Reyrolle	DOI	DA Group
LED Reset		
	CTRL.LLN0.LEDRs	stVal
Local Mode		
	CTRL.LLN0.Loc	stVal
	CTRL.CntPhAGGIO1.Loc	stVal
	CTRL.CntPhBGGIO1.Loc	stVal
	CTRL.CntPhCGGIO1.Loc	stVal
	CTRL.CntPhEGGIO1.Loc	stVal
	CTRL.CntDelGGIO1.Loc	stVal
	CTRL.CntLOGGIO1.Loc	stVal
	CTRL.QOCSWI1.Loc	stVal
	CTRL.QOXCBR1.Loc	stVal
	CTRL.SPDOnsGGIO1.Loc	stVal
	CTRL.SPDOnsGGIO2.Loc	stVal
	CTRL.SPDOnsGGIO3.Loc	stVal
	CTRL.SPDOnsGGIO4.Loc	stVal
	CTRL.SPDOesGGIO1.Loc	stVal
	CTRL.SPDOesGGIO2.Loc	stVal
	CTRL.SPDOesGGIO3.Loc	stVal
	CTRL.SPDOesGGIO4.Loc	stVal
	CTRL.DPDOnsGGIO1.Loc	stVal
	CTRL.DPDOnsGGIO2.Loc	stVal
	CTRL.DPDOnsGGIO3.Loc	stVal
	CTRL.DPDOnsGGIO4.Loc	stVal
	CTRL.DPDOesGGIO1.Loc	stVal
	CTRL.DPDOesGGIO2.Loc	stVal
	CTRL.DPDOesGGIO3.Loc	stVal
	CTRL.DPDOesGGIO4.Loc	stVal
Non-Directional		
	PROT.A81Hb2PHAR1.Str	dirGeneral
	PROT.A81Hb2PHAR1.Str	dirPhsA
	PROT.A81Hb2PHAR1.Str	dirPhsB
	PROT.A81Hb2PHAR1.Str	dirPhsC
	PROT.A64hPTOC1.Str	dirGeneral
	PROT.A46DtPTOC1.Str	dirGeneral
	PROT.A37PTUC1.Str	dirGeneral
	PROT.A37PTUC1.Str	dirPhsA
	PROT.A37PTUC1.Str	dirPhsB
	PROT.A37PTUC1.Str	dirPhsC
	PROT.A37PTUC2.Str	dirGeneral
	PROT.A37PTUC2.Str	dirPhsA
	PROT.A37PTUC2.Str	dirPhsB
	PROT.A37PTUC2.Str	dirPhsC
	PROT.A37gPTUC1.Str	dirGeneral
	PROT.A37gPTUC2.Str	dirGeneral
	PROT.A37SefPTUC1.Str	dirGeneral
	PROT.A37SefPTUC2.Str	dirGeneral
	PROT.A49PTTR1.Str	dirGeneral
	PROT.A2759PTOV1.Str	dirGeneral
	PROT.A2759PTOV1.Str	dirPhsA
	PROT.A2759PTOV1.Str	dirPhsB
	PROT.A2759PTOV1.Str	dirPhsC
	PROT.A2759PTUV1.Str	dirGeneral
	PROT.A2759PTUV1.Str	dirPhsA
	PROT.A2759PTUV1.Str	dirPhsB
	PROT.A2759PTUV1.Str	dirPhsC
	PROT.A2759PTOV2.Str	dirGeneral

	PROT.A2759PTOV2.Str	dirPhsA
	PROT.A2759PTOV2.Str	dirPhsB
	PROT.A2759PTOV2.Str	dirPhsC
	PROT.A2759PTUV2.Str	dirGeneral
	PROT.A2759PTUV2.Str	dirPhsA
	PROT.A2759PTUV2.Str	dirPhsB
	PROT.A2759PTUV2.Str	dirPhsC
	PROT.A2759PTOV3.Str	dirGeneral
	PROT.A2759PTOV3.Str	dirPhsA
	PROT.A2759PTOV3.Str	dirPhsB
	PROT.A2759PTOV3.Str	dirPhsC
	PROT.A2759PTUV3.Str	dirGeneral
	PROT.A2759PTUV3.Str	dirPhsA
	PROT.A2759PTUV3.Str	dirPhsB
	PROT.A2759PTUV3.Str	dirPhsC
	PROT.A2759PTOV4.Str	dirGeneral
	PROT.A2759PTOV4.Str	dirPhsA
	PROT.A2759PTOV4.Str	dirPhsB
	PROT.A2759PTOV4.Str	dirPhsC
	PROT.A2759PTUV4.Str	dirGeneral
	PROT.A2759PTUV4.Str	dirPhsA
	PROT.A2759PTUV4.Str	dirPhsB
	PROT.A2759PTUV4.Str	dirPhsC
	PROT.A2759PTOV5.Str	dirGeneral
	PROT.A2759PTUV5.Str	dirGeneral
	PROT.A47PTOV1.Str	dirGeneral
	PROT.A47PTOV2.Str	dirGeneral
	PROT.A59nDtPTOV1.Str	dirGeneral
	PROT.A81PTOF1.Str	dirGeneral
	PROT.A81PTUF1.Str	dirGeneral
	PROT.A81PTOF2.Str	dirGeneral
	PROT.A81PTUF2.Str	dirGeneral
	PROT.A81PTOF3.Str	dirGeneral
	PROT.A81PTUF3.Str	dirGeneral
	PROT.A81PTOF4.Str	dirGeneral
	PROT.A81PTUF4.Str	dirGeneral
	PROT.A81PTOF5.Str	dirGeneral
	PROT.A81PTUF5.Str	dirGeneral
	PROT.A81PTOF6.Str	dirGeneral
	PROT.A81PTUF6.Str	dirGeneral
	PROT.A46BcPTOC1.Str	dirGeneral
	PROT.A50LCPTOC1.Str	dirGeneral
	PROT.A50LCPTOC1.Str	dirPhsA
	PROT.A50LCPTOC1.Str	dirPhsB
	PROT.A50LCPTOC1.Str	dirPhsC
	PROT.A50LCPTOC2.Str	dirGeneral
	PROT.A50LCPTOC2.Str	dirPhsA
	PROT.A50LCPTOC2.Str	dirPhsB
	PROT.A50LCPTOC2.Str	dirPhsC
	PROT.A50gLCPTOC1.Str	dirGeneral
	PROT.A50gLCPTOC2.Str	dirGeneral
	PROT.A50SefLCPTOC1.Str	dirGeneral
	PROT.A50SefLCPTOC2.Str	dirGeneral
	PROT.A50BfRBRF1.Str	dirGeneral
Out of Service		
	PROT.LLNO.Mod	stVal
	PROT.LLNO.Beh	stVal
	PROT.A81Hb2PHAR1.Beh	stVal
	PROT.A51PTOC1.Beh	stVal
	PROT.A51PTOC2.Beh	stVal
	PROT.A51PTOC3.Beh	stVal
	PROT.A51PTOC4.Beh	stVal
	PROT.A50PTOC1.Beh	stVal
	PROT.A50PTOC2.Beh	stVal

	PROT.A50PTOC3.Beh	stVal
	PROT.A50PTOC4.Beh	stVal
	PROT.A51nPTOC1.Beh	stVal
	PROT.A51nPTOC2.Beh	stVal
	PROT.A51nPTOC3.Beh	stVal
	PROT.A51nPTOC4.Beh	stVal
	PROT.A50nPTOC1.Beh	stVal
	PROT.A50nPTOC2.Beh	stVal
	PROT.A50nPTOC3.Beh	stVal
	PROT.A50nPTOC4.Beh	stVal
	PROT.A51gPTOC1.Beh	stVal
	PROT.A51gPTOC2.Beh	stVal
	PROT.A51gPTOC3.Beh	stVal
	PROT.A51gPTOC4.Beh	stVal
	PROT.A50gPTOC1.Beh	stVal
	PROT.A50gPTOC2.Beh	stVal
	PROT.A50gPTOC3.Beh	stVal
	PROT.A50gPTOC4.Beh	stVal
	PROT.A51SefPTOC1.Beh	stVal
	PROT.A51SefPTOC2.Beh	stVal
	PROT.A51SefPTOC3.Beh	stVal
	PROT.A51SefPTOC4.Beh	stVal
	PROT.A50SefPTOC1.Beh	stVal
	PROT.A50SefPTOC2.Beh	stVal
	PROT.A50SefPTOC3.Beh	stVal
	PROT.A50SefPTOC4.Beh	stVal
	PROT.A64hPTOC1.Beh	stVal
	PROT.A46ItPTOC1.Beh	stVal
	PROT.A46DtPTOC1.Beh	stVal
	PROT.A37PTUC1.Beh	stVal
	PROT.A37PTUC2.Beh	stVal
	PROT.A37gPTUC1.Beh	stVal
	PROT.A37gPTUC2.Beh	stVal
	PROT.A37SefPTUC1.Beh	stVal
	PROT.A37SefPTUC2.Beh	stVal
	PROT.A49PTTR1.Beh	stVal
	PROT.A2759PTOV1.Beh	stVal
	PROT.A2759PTUV1.Beh	stVal
	PROT.A2759PTOV2.Beh	stVal
	PROT.A2759PTUV2.Beh	stVal
	PROT.A2759PTOV3.Beh	stVal
	PROT.A2759PTUV3.Beh	stVal
	PROT.A2759PTOV4.Beh	stVal
	PROT.A2759PTUV4.Beh	stVal
	PROT.A2759PTOV5.Beh	stVal
	PROT.A2759PTUV5.Beh	stVal
	PROT.A47PTOV1.Beh	stVal
	PROT.A47PTOV2.Beh	stVal
	PROT.A59nItPTOV1.Beh	stVal
	PROT.A59nDtPTOV1.Beh	stVal
	PROT.A81PTOF1.Beh	stVal
	PROT.A81PTUF1.Beh	stVal
	PROT.A81PTOF2.Beh	stVal
	PROT.A81PTUF2.Beh	stVal
	PROT.A81PTOF3.Beh	stVal
	PROT.A81PTUF3.Beh	stVal
	PROT.A81PTOF4.Beh	stVal
	PROT.A81PTUF4.Beh	stVal
	PROT.A81PTOF5.Beh	stVal
	PROT.A81PTUF5.Beh	stVal
	PROT.A81PTOF6.Beh	stVal
	PROT.A81PTUF6.Beh	stVal
	PROT.A46BcPTOC1.Beh	stVal
	PROT.A50LCPTOC1.Beh	stVal

	PROT.A50LCPTOC2.Beh	stVal
	PROT.A50gLCPTOC1.Beh	stVal
	PROT.A50gLCPTOC2.Beh	stVal
	PROT.A50SefLCPTOC1.Beh	stVal
	PROT.A50SefLCPTOC2.Beh	stVal
	PROT.A50BfrBRF1.Beh	stVal
	PROT.PTRC1.Beh	stVal
	CTRL.LLNO.Mod	stVal
	CTRL.LLNO.Beh	stVal
	CTRL.CntPhAGGIO1.Beh	stVal
	CTRL.CntPhBGGIO1.Beh	stVal
	CTRL.CntPhCGGIO1.Beh	stVal
	CTRL.CntEFGGIO1.Beh	stVal
	CTRL.CntDelGGIO1.Beh	stVal
	CTRL.QOCSW11.Beh	stVal
	CTRL.QOXCBR1.Beh	stVal
	CTRL.QOCILO1.Beh	stVal
	CTRL.BI13GGIO1.Beh	stVal
	CTRL.BO14GGIO1.Beh	stVal
	CTRL.L16GGIO1.Beh	stVal
	CTRL.V16GGIO1.Beh	stVal
	CTRL.E16GGIO1.Beh	stVal
	CTRL.SPi64GGIO1.Beh	stVal
	CTRL.SPo32GGIO1.Beh	stVal
	CTRL.SPDOnsGGIO1.Beh	stVal
	CTRL.SPDOnsGGIO2.Beh	stVal
	CTRL.SPDOnsGGIO3.Beh	stVal
	CTRL.SPDOnsGGIO4.Beh	stVal
	CTRL.SPDOesGGIO1.Beh	stVal
	CTRL.SPDOesGGIO2.Beh	stVal
	CTRL.SPDOesGGIO3.Beh	stVal
	CTRL.SPDOesGGIO4.Beh	stVal
	CTRL.DPDOnsGGIO1.Beh	stVal
	CTRL.DPDOnsGGIO2.Beh	stVal
	CTRL.DPDOnsGGIO3.Beh	stVal
	CTRL.DPDOnsGGIO4.Beh	stVal
	CTRL.DPDOesGGIO1.Beh	stVal
	CTRL.DPDOesGGIO2.Beh	stVal
	CTRL.DPDOesGGIO3.Beh	stVal
	CTRL.DPDOesGGIO4.Beh	stVal
	CTRL.DPi8GGIO1.Beh	stVal
	CTRL.DPi8GGIO2.Beh	stVal
	CTRL.DPo8GGIO1.Beh	stVal
	CTRL.DPo8GGIO2.Beh	stVal
	MEAS.LLNO.Mod	stVal
	MEAS.LLNO.Beh	stVal
	MEAS.V_MSQI1.Beh	stVal
	MEAS.I_MSQI1.Beh	stVal
	DR.LLNO.Mod	stVal
	DR.LLNO.Beh	stVal
	DR.RDRE1.Beh	stVal
Protection Active		
	PROT.LLNO.Mod	stVal
	PROT.LLNO.Beh	stVal
	PROT.A49PTTR1.Beh	stVal
	PROT.A50BfrBRF1.Beh	stVal
	PROT.PTRC1.Mod	stVal
	PROT.PTRC1.Beh	stVal
Protection Healthy		
	PROT.LLNO.Health	stVal
	PROT.A81Hb2PHAR1.Health	stVal
	PROT.A51PTOC1.Health	stVal
	PROT.A51PTOC2.Health	stVal
	PROT.A51PTOC3.Health	stVal

	PROT.A51PTOC4.Health	stVal
	PROT.A50PTOC1.Health	stVal
	PROT.A50PTOC2.Health	stVal
	PROT.A50PTOC3.Health	stVal
	PROT.A50PTOC4.Health	stVal
	PROT.A51nPTOC1.Health	stVal
	PROT.A51nPTOC2.Health	stVal
	PROT.A51nPTOC3.Health	stVal
	PROT.A51nPTOC4.Health	stVal
	PROT.A50nPTOC1.Health	stVal
	PROT.A50nPTOC2.Health	stVal
	PROT.A50nPTOC3.Health	stVal
	PROT.A50nPTOC4.Health	stVal
	PROT.A51gPTOC1.Health	stVal
	PROT.A51gPTOC2.Health	stVal
	PROT.A51gPTOC3.Health	stVal
	PROT.A51gPTOC4.Health	stVal
	PROT.A50gPTOC1.Health	stVal
	PROT.A50gPTOC2.Health	stVal
	PROT.A50gPTOC3.Health	stVal
	PROT.A50gPTOC4.Health	stVal
	PROT.A51SefPTOC1.Health	stVal
	PROT.A51SefPTOC2.Health	stVal
	PROT.A51SefPTOC3.Health	stVal
	PROT.A51SefPTOC4.Health	stVal
	PROT.A50SefPTOC1.Health	stVal
	PROT.A50SefPTOC2.Health	stVal
	PROT.A50SefPTOC3.Health	stVal
	PROT.A50SefPTOC4.Health	stVal
	PROT.A64hPTOC1.Health	stVal
	PROT.A46ItPTOC1.Health	stVal
	PROT.A46DtPTOC1.Health	stVal
	PROT.A37PTUC1.Health	stVal
	PROT.A37PTUC2.Health	stVal
	PROT.A37gPTUC1.Health	stVal
	PROT.A37gPTUC2.Health	stVal
	PROT.A37SefPTUC1.Health	stVal
	PROT.A37SefPTUC2.Health	stVal
	PROT.A49PTTR1.Health	stVal
	PROT.A2759PTOV1.Health	stVal
	PROT.A2759PTUV1.Health	stVal
	PROT.A2759PTOV2.Health	stVal
	PROT.A2759PTUV2.Health	stVal
	PROT.A2759PTOV3.Health	stVal
	PROT.A2759PTUV3.Health	stVal
	PROT.A2759PTOV4.Health	stVal
	PROT.A2759PTUV4.Health	stVal
	PROT.A2759PTOV5.Health	stVal
	PROT.A2759PTUV5.Health	stVal
	PROT.A47PTOV1.Health	stVal
	PROT.A47PTOV2.Health	stVal
	PROT.A59nItPTOV1.Health	stVal
	PROT.A59nDtPTOV1.Health	stVal
	PROT.A81PTOF1.Health	stVal
	PROT.A81PTUF1.Health	stVal
	PROT.A81PTOF2.Health	stVal
	PROT.A81PTUF2.Health	stVal
	PROT.A81PTOF3.Health	stVal
	PROT.A81PTUF3.Health	stVal
	PROT.A81PTOF4.Health	stVal
	PROT.A81PTUF4.Health	stVal
	PROT.A81PTOF5.Health	stVal
	PROT.A81PTUF5.Health	stVal
	PROT.A81PTOF6.Health	stVal

	PROT.A81PTUF6.Health	stVal
	PROT.A46BcPTOC1.Health	stVal
	PROT.A50LCPTOC1.Health	stVal
	PROT.A50LCPTOC2.Health	stVal
	PROT.A50gLCPTOC1.Health	stVal
	PROT.A50gLCPTOC2.Health	stVal
	PROT.A50SefLCPTOC1.Health	stVal
	PROT.A50SefLCPTOC2.Health	stVal
	PROT.A50BfRBRF1.Health	stVal
	PROT.PTRC1.Health	stVal
	CTRL.LLNO.Mod	stVal
	CTRL.LLNO.Beh	stVal
	CTRL.LLNO.Health	stVal
	CTRL.CntPhAGGIO1.Health	stVal
	CTRL.CntPhBGGIO1.Health	stVal
	CTRL.CntPhCGGIO1.Health	stVal
	CTRL.CntEFGGIO1.Health	stVal
	CTRL.CntDelGGIO1.Health	stVal
	CTRL.Q0CSW11.Health	stVal
	CTRL.Q0XCBR1.Health	stVal
	CTRL.Q0CILO1.Health	stVal
	CTRL.BI13GGIO1.Health	stVal
	CTRL.BO14GGIO1.Health	stVal
	CTRL.L16GGIO1.Health	stVal
	CTRL.V16GGIO1.Health	stVal
	CTRL.E16GGIO1.Health	stVal
	CTRL.SPi64GGIO1.Health	stVal
	CTRL.SP032GGIO1.Health	stVal
	CTRL.SPDOnsGGIO1.Health	stVal
	CTRL.SPDOnsGGIO2.Health	stVal
	CTRL.SPDOnsGGIO3.Health	stVal
	CTRL.SPDOnsGGIO4.Health	stVal
	CTRL.SPDOesGGIO1.Health	stVal
	CTRL.SPDOesGGIO2.Health	stVal
	CTRL.SPDOesGGIO3.Health	stVal
	CTRL.SPDOesGGIO4.Health	stVal
	CTRL.DPDOnsGGIO1.Health	stVal
	CTRL.DPDOnsGGIO2.Health	stVal
	CTRL.DPDOnsGGIO3.Health	stVal
	CTRL.DPDOnsGGIO4.Health	stVal
	CTRL.DPDOesGGIO1.Health	stVal
	CTRL.DPDOesGGIO2.Health	stVal
	CTRL.DPDOesGGIO3.Health	stVal
	CTRL.DPDOesGGIO4.Health	stVal
	CTRL.DPi8GGIO1.Health	stVal
	CTRL.DPi8GGIO2.Health	stVal
	CTRL.DPo8GGIO1.Health	stVal
	CTRL.DPo8GGIO2.Health	stVal
	MEAS.LLNO.Mod	stVal
	MEAS.LLNO.Beh	stVal
	MEAS.LLNO.Health	stVal
	MEAS.V_MSQI1.Health	stVal
	MEAS.I_MSQI1.Health	stVal
	DR.LLNO.Mod	stVal
	DR.LLNO.Beh	stVal
	DR.LLNO.Health	stVal
	DR.RDRE1.Mod	stVal
	DR.RDRE1.Beh	stVal
	DR.RDRE1.Health	stVal
Software Revision		
	PROT.LLNO.NamPIt	swRev
	CTRL.LLNO.NamPIt	swRev
	MEAS.LLNO.NamPIt	swRev
	DR.LLNO.NamPIt	swRev

Vendor Name		
	PROT.LLNO.NamPIt	vendor
	CTRL.LLNO.NamPIt	vendor
	MEAS.LLNO.NamPIt	vendor
	DR.LLNO.NamPIt	vendor

1.2 AR Lockout Trip Counters

Reyrolle	DOI	DA Group
CB Count To AR Block		
	CTRL.CntLOGGIO1.ISCSO1	stVal
CB Count To AR Block Enabled		
	CTRL.CntLOGGIO1.Mod	stVal
	CTRL.CntLOGGIO1.Beh	stVal
CB Count To AR Block Operated		
	CTRL.CntLOGGIO1.SPCSO	stVal
CB Count To AR Block Target		
	CTRL.CntLOGGIO1.ISCSO2	stVal

1.3 Autoreclose

Reyrolle	DOI	DA Group
In		
	PROT.A79RREC1.Mod	stVal
	PROT.A79RREC1.Beh	stVal
In Progress		
	PROT.A79RREC1.AutoRecSt	stVal
Operated		
	PROT.A79RREC1.Op	general
Out		
	PROT.A79RREC1.Mod	stVal
	PROT.A79RREC1.Beh	stVal
Successful		
	PROT.A79RREC1.AutoRecSt	stVal
Inhibit		
	PROT.A79RREC1.Mod	stVal
	PROT.A79RREC1.Beh	stVal

1.4 BROKEN CONDUCTOR MENU

Reyrolle	DOI	DA Group
46BC Enabled		
	PROT.A46BcPTOC1.Mod	stVal
	PROT.A46BcPTOC1.Beh	stVal
46BC Operated		
	PROT.A46BcPTOC1.Op	general
46BC Pickup		
	PROT.A46BcPTOC1.Str	general
Inhibit 46BC		
	PROT.A46BcPTOC1.Mod	stVal
	PROT.A46BcPTOC1.Beh	stVal

1.5 CB E/F Trip Counter

Reyrolle	DOI	DA Group
CB E/F Trip Count		
	CTRL.CntEFGGIO1.ISCSO1	stVal
CB E/F Trip Count Enabled		
	CTRL.CntEFGGIO1.Mod	stVal
	CTRL.CntEFGGIO1.Beh	stVal
CB E/F Trip Count Operated		
	CTRL.CntEFGGIO1.SPCSO	stVal
CB E/F Trip Count Target		
	CTRL.CntEFGGIO1.ISCSO2	stVal

1.6 CB FAIL

Reyrolle	DOI	DA Group
50BF Enabled		
	PROT.A50BfRBRF1.Mod	stVal
	PROT.A50BfRBRF1.Beh	stVal
50BF Pickup		
	PROT.A50BfRBRF1.Str	general
50BF-1		
	PROT.A50BfRBRF1.OpIn	general
50BF-2		
	PROT.A50BfRBRF1.OpEx	general
Inhibit 50BF		
	PROT.A50BfRBRF1.Mod	stVal
	PROT.A50BfRBRF1.Beh	stVal

1.7 CB Ph A Trip Counter

Reyrolle	DOI	DA Group
CB Ph A Trip Count		
	CTRL.CntPhAGGIO1.ISCSO1	stVal
CB Ph A Trip Count Enabled		
	CTRL.CntPhAGGIO1.Mod	stVal
	CTRL.CntPhAGGIO1.Beh	stVal
CB Ph A Trip Count Operated		
	CTRL.CntPhAGGIO1.SPCSO	stVal
CB Ph A Trip Count Target		
	CTRL.CntPhAGGIO1.ISCSO2	stVal

1.8 CB Ph B Trip Counter

Reyrolle	DOI	DA Group
CB Ph B Trip Count		
	CTRL.CntPhBGGIO1.ISCSO1	stVal
CB Ph B Trip Count Enabled		
	CTRL.CntPhBGGIO1.Mod	stVal
	CTRL.CntPhBGGIO1.Beh	stVal
CB Ph B Trip Count Operated		
	CTRL.CntPhBGGIO1.SPCSO	stVal
CB Ph B Trip Count Target		
	CTRL.CntPhBGGIO1.ISCSO2	stVal

1.9 CB Ph C Trip Counter

Reyrolle	DOI	DA Group
CB Ph C Trip Count		
	CTRL.CntPhCGGIO1.ISCSO1	stVal
CB Ph C Trip Count Enabled		
	CTRL.CntPhCGGIO1.Mod	stVal
	CTRL.CntPhCGGIO1.Beh	stVal
CB Ph C Trip Count Operated		
	CTRL.CntPhCGGIO1.SPCSO	stVal
CB Ph C Trip Count Target		
	CTRL.CntPhCGGIO1.ISCSO2	stVal

1.10 Change Group

Reyrolle	DOI	DA Group
Active Setting Group 1		
	PROT.LLNO.SGCB	ActSG
	PROT.LLNO.SGCB	LActTm
Active Setting Group 2		
	PROT.LLNO.SGCB	ActSG
	PROT.LLNO.SGCB	LActTm
Active Setting Group 3		
	PROT.LLNO.SGCB	ActSG
	PROT.LLNO.SGCB	LActTm
Active Setting Group 4		
	PROT.LLNO.SGCB	ActSG
	PROT.LLNO.SGCB	LActTm
Number of 61850 Controllable Setting Groups		
	PROT.LLNO.SGCB	NumOfSG

1.11 CURRENT METERS

Reyrolle	DOI	DA Group
Sequence Components I Seq NPS		
	MEAS.I_MSQI1.SeqA	c2.instCVal.mag.f
	MEAS.I_MSQI1.SeqA	c2.cVal.mag.f
	MEAS.I_MSQI1.SeqA	c2.units.SIUnit
	MEAS.I_MSQI1.SeqA	c2.units.multiplier
Sequence Components I Seq PPS		
	MEAS.I_MSQI1.SeqA	c1.instCVal.mag.f
	MEAS.I_MSQI1.SeqA	c1.cVal.mag.f
	MEAS.I_MSQI1.SeqA	c1.units.SIUnit
	MEAS.I_MSQI1.SeqA	c1.units.multiplier
Sequence Components I Seq ZPS		
	MEAS.I_MSQI1.SeqA	c3.instCVal.mag.f
	MEAS.I_MSQI1.SeqA	c3.cVal.mag.f
	MEAS.I_MSQI1.SeqA	c3.units.SIUnit
	MEAS.I_MSQI1.SeqA	c3.units.multiplier

1.12 Delta Trip Counters

Reyrolle	DOI	DA Group
CB Delta Trip Count		
	CTRL.CntDelGGIO1.ISCSO1	stVal
CB Delta Trip Count Enabled		
	CTRL.CntDelGGIO1.Mod	stVal
	CTRL.CntDelGGIO1.Beh	stVal
CB Delta Trip Count Operated		
	CTRL.CntDelGGIO1.SPCSO	stVal
CB Delta Trip Count Target		
	CTRL.CntDelGGIO1.ISCSO2	stVal

1.13 DERIVED EARTH FAULT MENU

Reyrolle	DOI	DA Group
50N-1 Dir Pickup		
	PROT.A50nPTOC1.Str	dirGeneral
50N-1 Enabled		
	PROT.A50nPTOC1.Mod	stVal
	PROT.A50nPTOC1.Beh	stVal
50N-1 Operated		
	PROT.A50nPTOC1.Op	general
50N-1 Pickup		
	PROT.A50nPTOC1.Str	general
50N-2 Dir Pickup		
	PROT.A50nPTOC2.Str	dirGeneral
50N-2 Enabled		
	PROT.A50nPTOC2.Mod	stVal
	PROT.A50nPTOC2.Beh	stVal
50N-2 Operated		
	PROT.A50nPTOC2.Op	general
50N-2 Pickup		
	PROT.A50nPTOC2.Str	general
50N-3 Dir Pickup		
	PROT.A50nPTOC3.Str	dirGeneral
50N-3 Enabled		
	PROT.A50nPTOC3.Mod	stVal
	PROT.A50nPTOC3.Beh	stVal
50N-3 Operated		
	PROT.A50nPTOC3.Op	general
50N-3 Pickup		
	PROT.A50nPTOC3.Str	general
50N-4 Dir Pickup		
	PROT.A50nPTOC4.Str	dirGeneral
50N-4 Enabled		
	PROT.A50nPTOC4.Mod	stVal
	PROT.A50nPTOC4.Beh	stVal
50N-4 Operated		
	PROT.A50nPTOC4.Op	general
50N-4 Pickup		
	PROT.A50nPTOC4.Str	general
51N-1 Dir Pickup		
	PROT.A51nPTOC1.Str	dirGeneral
51N-1 Enabled		
	PROT.A51nPTOC1.Mod	stVal
	PROT.A51nPTOC1.Beh	stVal
51N-1 Operated		
	PROT.A51nPTOC1.Op	general
51N-1 Pickup		
	PROT.A51nPTOC1.Str	general

51N-2 Dir Pickup		
	PROT.A51nPTOC2.Str	dirGeneral
51N-2 Enabled		
	PROT.A51nPTOC2.Mod	stVal
	PROT.A51nPTOC2.Beh	stVal
51N-2 Operated		
	PROT.A51nPTOC2.Op	general
51N-2 Pickup		
	PROT.A51nPTOC2.Str	general
51N-3 Dir Pickup		
	PROT.A51nPTOC3.Str	dirGeneral
51N-3 Enabled		
	PROT.A51nPTOC3.Mod	stVal
	PROT.A51nPTOC3.Beh	stVal
51N-3 Operated		
	PROT.A51nPTOC3.Op	general
51N-3 Pickup		
	PROT.A51nPTOC3.Str	general
51N-4 Dir Pickup		
	PROT.A51nPTOC4.Str	dirGeneral
51N-4 Enabled		
	PROT.A51nPTOC4.Mod	stVal
	PROT.A51nPTOC4.Beh	stVal
51N-4 Operated		
	PROT.A51nPTOC4.Op	general
51N-4 Pickup		
	PROT.A51nPTOC4.Str	general
Inhibit 50N-1		
	PROT.A50nPTOC1.Mod	stVal
	PROT.A50nPTOC1.Beh	stVal
Inhibit 50N-2		
	PROT.A50nPTOC2.Mod	stVal
	PROT.A50nPTOC2.Beh	stVal
Inhibit 50N-3		
	PROT.A50nPTOC3.Mod	stVal
	PROT.A50nPTOC3.Beh	stVal
Inhibit 50N-4		
	PROT.A50nPTOC4.Mod	stVal
	PROT.A50nPTOC4.Beh	stVal
Inhibit 51N-1		
	PROT.A51nPTOC1.Mod	stVal
	PROT.A51nPTOC1.Beh	stVal
Inhibit 51N-2		
	PROT.A51nPTOC2.Mod	stVal
	PROT.A51nPTOC2.Beh	stVal
Inhibit 51N-3		
	PROT.A51nPTOC3.Mod	stVal
	PROT.A51nPTOC3.Beh	stVal
Inhibit 51N-4		
	PROT.A51nPTOC4.Mod	stVal
	PROT.A51nPTOC4.Beh	stVal

1.14 Disturbance Recorder

Reyrolle	DOI	DA Group
Fault Number		
	DR.RDRE1.FltNum	stVal
Grid Fault Number		
	DR.RDRE1.GriFltNum	stVal
Recording Made		
	DR.RDRE1.RcdMade	stVal

1.15 Double Point Controls (Enhanced Security)

Reyrolle	DOI	DA Group
DPDOes 1 Control		
	CTRL.DPDOesGGIO1.DPCSO	Oper.ctlVal
DPDOes 1 Status		
	CTRL.DPDOesGGIO1.DPCSO	stVal
DPDOes 2 Control		
	CTRL.DPDOesGGIO2.DPCSO	Oper.ctlVal
DPDOes 2 Status		
	CTRL.DPDOesGGIO2.DPCSO	stVal
DPDOes 3 Control		
	CTRL.DPDOesGGIO3.DPCSO	Oper.ctlVal
DPDOes 3 Status		
	CTRL.DPDOesGGIO3.DPCSO	stVal
DPDOes 4 Control		
	CTRL.DPDOesGGIO4.DPCSO	Oper.ctlVal
DPDOes 4 Status		
	CTRL.DPDOesGGIO4.DPCSO	stVal

1.16 Double Point Controls (Normal Security)

Reyrolle	DOI	DA Group
DPDOs 1 Control		
	CTRL.DPDOsGGIO1.DPCSO	Oper.ctlVal
DPDOs 1 Status		
	CTRL.DPDOsGGIO1.DPCSO	stVal
DPDOs 2 Control		
	CTRL.DPDOsGGIO2.DPCSO	Oper.ctlVal
DPDOs 2 Status		
	CTRL.DPDOsGGIO2.DPCSO	stVal
DPDOs 3 Control		
	CTRL.DPDOsGGIO3.DPCSO	Oper.ctlVal
DPDOs 3 Status		
	CTRL.DPDOsGGIO3.DPCSO	stVal
DPDOs 4 Control		
	CTRL.DPDOsGGIO4.DPCSO	Oper.ctlVal
DPDOs 4 Status		
	CTRL.DPDOsGGIO4.DPCSO	stVal

1.17 Double Point Inputs

Reyrolle	DOI	DA Group
DPI8GGIO1 DPCSO 1		
	CTRL.DPI8GGIO1.DPCSO1	ctlVal
DPI8GGIO1 DPCSO 2		
	CTRL.DPI8GGIO1.DPCSO2	ctlVal
DPI8GGIO1 DPCSO 3		
	CTRL.DPI8GGIO1.DPCSO3	ctlVal
DPI8GGIO1 DPCSO 4		
	CTRL.DPI8GGIO1.DPCSO4	ctlVal
DPI8GGIO1 DPCSO 5		
	CTRL.DPI8GGIO1.DPCSO5	ctlVal
DPI8GGIO1 DPCSO 6		
	CTRL.DPI8GGIO1.DPCSO6	ctlVal
DPI8GGIO1 DPCSO 7		
	CTRL.DPI8GGIO1.DPCSO7	ctlVal
DPI8GGIO1 DPCSO 8		
	CTRL.DPI8GGIO1.DPCSO8	ctlVal

DPI8GGIO2 DPCSO 1		
	CTRL.DPI8GGIO2.DPCSO1	ctVal
DPI8GGIO2 DPCSO 2		
	CTRL.DPI8GGIO2.DPCSO2	ctVal
DPI8GGIO2 DPCSO 3		
	CTRL.DPI8GGIO2.DPCSO3	ctVal
DPI8GGIO2 DPCSO 4		
	CTRL.DPI8GGIO2.DPCSO4	ctVal
DPI8GGIO2 DPCSO 5		
	CTRL.DPI8GGIO2.DPCSO5	ctVal
DPI8GGIO2 DPCSO 6		
	CTRL.DPI8GGIO2.DPCSO6	ctVal
DPI8GGIO2 DPCSO 7		
	CTRL.DPI8GGIO2.DPCSO7	ctVal
DPI8GGIO2 DPCSO 8		
	CTRL.DPI8GGIO2.DPCSO8	ctVal

1.18 Double Point Outputs

Reyrolle	DOI	DA Group
DPo8GGIO1 Ind 1		
	CTRL.DPo8GGIO1.DPCSO1	stVal
DPo8GGIO1 Ind 2		
	CTRL.DPo8GGIO1.DPCSO2	stVal
DPo8GGIO1 Ind 3		
	CTRL.DPo8GGIO1.DPCSO3	stVal
DPo8GGIO1 Ind 4		
	CTRL.DPo8GGIO1.DPCSO4	stVal
DPo8GGIO1 Ind 5		
	CTRL.DPo8GGIO1.DPCSO5	stVal
DPo8GGIO1 Ind 6		
	CTRL.DPo8GGIO1.DPCSO6	stVal
DPo8GGIO1 Ind 7		
	CTRL.DPo8GGIO1.DPCSO7	stVal
DPo8GGIO1 Ind 8		
	CTRL.DPo8GGIO1.DPCSO8	stVal
DPo8GGIO2 Ind 1		
	CTRL.DPo8GGIO2.DPCSO1	stVal
DPo8GGIO2 Ind 2		
	CTRL.DPo8GGIO2.DPCSO2	stVal
DPo8GGIO2 Ind 3		
	CTRL.DPo8GGIO2.DPCSO3	stVal
DPo8GGIO2 Ind 4		
	CTRL.DPo8GGIO2.DPCSO4	stVal
DPo8GGIO2 Ind 5		
	CTRL.DPo8GGIO2.DPCSO5	stVal
DPo8GGIO2 Ind 6		
	CTRL.DPo8GGIO2.DPCSO6	stVal
DPo8GGIO2 Ind 7		
	CTRL.DPo8GGIO2.DPCSO7	stVal
DPo8GGIO2 Ind 8		
	CTRL.DPo8GGIO2.DPCSO8	stVal

1.19 General Trip Information

Reyrolle	DOI	DA Group
CB Trip		
	PROT.PTRC1.Tr	general
CB Trip Count		
	PROT.PTRC1.OpCntRs	stVal
General Operate		
	PROT.PTRC1.Op	general
General Pickup		
	PROT.PTRC1.Str	general
	PROT.PTRC1.Str	dirGeneral
General Pickup & Fwd Direction		
	PROT.PTRC1.Str	dirGeneral
General Pickup & Rev Direction		
	PROT.PTRC1.Str	dirGeneral
Set CB Trip Count		
	PROT.PTRC1.OpCntRs	Oper.ctlVal

1.20 INRUSH DETECTOR

Reyrolle	DOI	DA Group
81HBL2 Enabled		
	PROT.A81Hb2PHAR1.Mod	stVal
	PROT.A81Hb2PHAR1.Beh	stVal
81HBL2 PhA Pickup		
	PROT.A81Hb2PHAR1.Str	general
	PROT.A81Hb2PHAR1.Str	phsA
81HBL2 PhB Pickup		
	PROT.A81Hb2PHAR1.Str	general
	PROT.A81Hb2PHAR1.Str	phsB
81HBL2 PhC Pickup		
	PROT.A81Hb2PHAR1.Str	general
	PROT.A81Hb2PHAR1.Str	phsC
Inhibit 81HBL2		
	PROT.A81Hb2PHAR1.Mod	stVal
	PROT.A81Hb2PHAR1.Beh	stVal

1.21 LINE CHECK

Reyrolle	DOI	DA Group
50 LC-1 Enabled		
	PROT.A50LCPTOC1.Mod	stVal
	PROT.A50LCPTOC1.Beh	stVal
50 LC-1 Operated		
	PROT.A50LCPTOC1.Op	general
50 LC-1 PhA Pickup		
	PROT.A50LCPTOC1.Str	general
	PROT.A50LCPTOC1.Str	phsA
50 LC-1 PhB Pickup		
	PROT.A50LCPTOC1.Str	general
	PROT.A50LCPTOC1.Str	phsB
50 LC-1 PhC Pickup		
	PROT.A50LCPTOC1.Str	general
	PROT.A50LCPTOC1.Str	phsC
50 LC-2 Enabled		
	PROT.A50LCPTOC2.Mod	stVal
	PROT.A50LCPTOC2.Beh	stVal
50 LC-2 Operated		

	PROT.A50LCPTOC2.Op	general
50 LC-2 PhA Pickup		
	PROT.A50LCPTOC2.Str	general
	PROT.A50LCPTOC2.Str	phsA
50 LC-2 PhB Pickup		
	PROT.A50LCPTOC2.Str	general
	PROT.A50LCPTOC2.Str	phsB
50 LC-2 PhC Pickup		
	PROT.A50LCPTOC2.Str	general
	PROT.A50LCPTOC2.Str	phsC
50G LC-1 Enabled		
	PROT.A50gLCPTOC1.Mod	stVal
	PROT.A50gLCPTOC1.Beh	stVal
50G LC-1 Operated		
	PROT.A50gLCPTOC1.Op	general
50G LC-1 Pickup		
	PROT.A50gLCPTOC1.Str	general
50G LC-2 Enabled		
	PROT.A50gLCPTOC2.Mod	stVal
	PROT.A50gLCPTOC2.Beh	stVal
50G LC-2 Operated		
	PROT.A50gLCPTOC2.Op	general
50G LC-2 Pickup		
	PROT.A50gLCPTOC2.Str	general
50SEF LC-1 Enabled		
	PROT.A50SefLCPTOC1.Mod	stVal
	PROT.A50SefLCPTOC1.Beh	stVal
50SEF LC-1 Operated		
	PROT.A50SefLCPTOC1.Op	general
50SEF LC-1 Pickup		
	PROT.A50SefLCPTOC1.Str	general
50SEF LC-2 Enabled		
	PROT.A50SefLCPTOC2.Mod	stVal
	PROT.A50SefLCPTOC2.Beh	stVal
50SEF LC-2 Operated		
	PROT.A50SefLCPTOC2.Op	general
50SEF LC-2 Pickup		
	PROT.A50SefLCPTOC2.Str	general
Inhibit 50 LC-1		
	PROT.A50LCPTOC1.Mod	stVal
	PROT.A50LCPTOC1.Beh	stVal
Inhibit 50 LC-2		
	PROT.A50LCPTOC2.Mod	stVal
	PROT.A50LCPTOC2.Beh	stVal
Inhibit 50G LC-1		
	PROT.A50gLCPTOC1.Mod	stVal
	PROT.A50gLCPTOC1.Beh	stVal
Inhibit 50G LC-2		
	PROT.A50gLCPTOC2.Mod	stVal
	PROT.A50gLCPTOC2.Beh	stVal
Inhibit 50SEF LC-1		
	PROT.A50SefLCPTOC1.Mod	stVal
	PROT.A50SefLCPTOC1.Beh	stVal
Inhibit 50SEF LC-2		
	PROT.A50SefLCPTOC2.Mod	stVal
	PROT.A50SefLCPTOC2.Beh	stVal

1.22 MEASURED EARTH FAULT MENU

Reyrolle	DOI	DA Group
50G-1 Dir Pickup		
	PROT.A50gPTOC1.Str	dirGeneral
50G-1 Enabled		
	PROT.A50gPTOC1.Mod	stVal
	PROT.A50gPTOC1.Beh	stVal
50G-1 Operated		
	PROT.A50gPTOC1.Op	general
50G-1 Pickup		
	PROT.A50gPTOC1.Str	general
50G-2 Dir Pickup		
	PROT.A50gPTOC2.Str	dirGeneral
50G-2 Enabled		
	PROT.A50gPTOC2.Mod	stVal
	PROT.A50gPTOC2.Beh	stVal
50G-2 Operated		
	PROT.A50gPTOC2.Op	general
50G-2 Pickup		
	PROT.A50gPTOC2.Str	general
50G-3 Dir Pickup		
	PROT.A50gPTOC3.Str	dirGeneral
50G-3 Enabled		
	PROT.A50gPTOC3.Mod	stVal
	PROT.A50gPTOC3.Beh	stVal
50G-3 Operated		
	PROT.A50gPTOC3.Op	general
50G-3 Pickup		
	PROT.A50gPTOC3.Str	general
50G-4 Dir Pickup		
	PROT.A50gPTOC4.Str	dirGeneral
50G-4 Enabled		
	PROT.A50gPTOC4.Mod	stVal
	PROT.A50gPTOC4.Beh	stVal
50G-4 Operated		
	PROT.A50gPTOC4.Op	general
50G-4 Pickup		
	PROT.A50gPTOC4.Str	general
51G-1 Dir Pickup		
	PROT.A51gPTOC1.Str	dirGeneral
51G-1 Enabled		
	PROT.A51gPTOC1.Mod	stVal
	PROT.A51gPTOC1.Beh	stVal
51G-1 Operated		
	PROT.A51gPTOC1.Op	general
51G-1 Pickup		
	PROT.A51gPTOC1.Str	general
51G-2 Dir Pickup		
	PROT.A51gPTOC2.Str	dirGeneral
51G-2 Enabled		
	PROT.A51gPTOC2.Mod	stVal
	PROT.A51gPTOC2.Beh	stVal
51G-2 Operated		
	PROT.A51gPTOC2.Op	general
51G-2 Pickup		
	PROT.A51gPTOC2.Str	general
51G-3 Dir Pickup		
	PROT.A51gPTOC3.Str	dirGeneral
51G-3 Enabled		
	PROT.A51gPTOC3.Mod	stVal
	PROT.A51gPTOC3.Beh	stVal

51G-3 Operated		
	PROT.A51gPTOC3.Op	general
51G-3 Pickup		
	PROT.A51gPTOC3.Str	general
51G-4 Dir Pickup		
	PROT.A51gPTOC4.Str	dirGeneral
51G-4 Enabled		
	PROT.A51gPTOC4.Mod	stVal
	PROT.A51gPTOC4.Beh	stVal
51G-4 Operated		
	PROT.A51gPTOC4.Op	general
51G-4 Pickup		
	PROT.A51gPTOC4.Str	general
Inhibit 50G-1		
	PROT.A50gPTOC1.Mod	stVal
	PROT.A50gPTOC1.Beh	stVal
Inhibit 50G-2		
	PROT.A50gPTOC2.Mod	stVal
	PROT.A50gPTOC2.Beh	stVal
Inhibit 50G-3		
	PROT.A50gPTOC3.Mod	stVal
	PROT.A50gPTOC3.Beh	stVal
Inhibit 50G-4		
	PROT.A50gPTOC4.Mod	stVal
	PROT.A50gPTOC4.Beh	stVal
Inhibit 51G-1		
	PROT.A51gPTOC1.Mod	stVal
	PROT.A51gPTOC1.Beh	stVal
Inhibit 51G-2		
	PROT.A51gPTOC2.Mod	stVal
	PROT.A51gPTOC2.Beh	stVal
Inhibit 51G-3		
	PROT.A51gPTOC3.Mod	stVal
	PROT.A51gPTOC3.Beh	stVal
Inhibit 51G-4		
	PROT.A51gPTOC4.Mod	stVal
	PROT.A51gPTOC4.Beh	stVal

1.23 NEUTRAL OVERVOLTAGE

Reyrolle	DOI	DA Group
59NDT Enabled		
	PROT.A59nDtPTOV1.Mod	stVal
	PROT.A59nDtPTOV1.Beh	stVal
59NDT Operated		
	PROT.A59nDtPTOV1.Op	general
59NDT Pickup		
	PROT.A59nDtPTOV1.Str	general
59NIT Enabled		
	PROT.A59nitPTOV1.Mod	stVal
	PROT.A59nitPTOV1.Beh	stVal
59NIT Operated		
	PROT.A59nitPTOV1.Op	general
59NIT Pickup		
	PROT.A59nitPTOV1.Str	general
Inhibit 59NDT		
	PROT.A59nDtPTOV1.Mod	stVal
	PROT.A59nDtPTOV1.Beh	stVal
Inhibit 59NIT		
	PROT.A59nitPTOV1.Mod	stVal
	PROT.A59nitPTOV1.Beh	stVal

1.24 NPS OVERCURRENT MENU

Reyrolle	DOI	DA Group
46DT Enabled		
	PROT.A46DtPTOC1.Mod	stVal
	PROT.A46DtPTOC1.Beh	stVal
46DT Operated		
	PROT.A46DtPTOC1.Op	general
46DT Pickup		
	PROT.A46DtPTOC1.Str	general
46IT Enabled		
	PROT.A46ItPTOC1.Mod	stVal
	PROT.A46ItPTOC1.Beh	stVal
46IT Operated		
	PROT.A46ItPTOC1.Op	general
46IT Pickup		
	PROT.A46ItPTOC1.Str	general
Inhibit 46DT		
	PROT.A46DtPTOC1.Mod	stVal
	PROT.A46DtPTOC1.Beh	stVal
Inhibit 46IT		
	PROT.A46ItPTOC1.Mod	stVal
	PROT.A46ItPTOC1.Beh	stVal

1.25 NPS OVERVOLTAGE

Reyrolle	DOI	DA Group
47-1 Enabled		
	PROT.A47PTOV1.Mod	stVal
	PROT.A47PTOV1.Beh	stVal
47-1 Operated		
	PROT.A47PTOV1.Op	general
47-1 Pickup		
	PROT.A47PTOV1.Str	general
47-2 Enabled		
	PROT.A47PTOV2.Mod	stVal
	PROT.A47PTOV2.Beh	stVal
47-2 Operated		
	PROT.A47PTOV2.Op	general
47-2 Pickup		
	PROT.A47PTOV2.Str	general
Inhibit 47-1		
	PROT.A47PTOV1.Mod	stVal
	PROT.A47PTOV1.Beh	stVal
Inhibit 47-2		
	PROT.A47PTOV2.Mod	stVal
	PROT.A47PTOV2.Beh	stVal

1.26 OVERCURRENT MENU

Reyrolle	DOI	DA Group
50-1 Enabled		
	PROT.A50PTOC1.Mod	stVal
	PROT.A50PTOC1.Beh	stVal
50-1 Operated		
	PROT.A50PTOC1.Op	general
50-1 PhA Dir Pickup		
	PROT.A50PTOC1.Str	dirGeneral
	PROT.A50PTOC1.Str	dirPhsA
50-1 PhA Pickup		
	PROT.A50PTOC1.Str	general
	PROT.A50PTOC1.Str	phsA
50-1 PhB Dir Pickup		
	PROT.A50PTOC1.Str	dirGeneral
	PROT.A50PTOC1.Str	dirPhsB
50-1 PhB Pickup		
	PROT.A50PTOC1.Str	general
	PROT.A50PTOC1.Str	phsB
50-1 PhC Dir Pickup		
	PROT.A50PTOC1.Str	dirGeneral
	PROT.A50PTOC1.Str	dirPhsC
50-1 PhC Pickup		
	PROT.A50PTOC1.Str	general
	PROT.A50PTOC1.Str	phsC
50-2 Enabled		
	PROT.A50PTOC2.Mod	stVal
	PROT.A50PTOC2.Beh	stVal
50-2 Operated		
	PROT.A50PTOC2.Op	general
50-2 PhA Dir Pickup		
	PROT.A50PTOC2.Str	dirGeneral
	PROT.A50PTOC2.Str	dirPhsA
50-2 PhA Pickup		
	PROT.A50PTOC2.Str	general
	PROT.A50PTOC2.Str	phsA
50-2 PhB Dir Pickup		
	PROT.A50PTOC2.Str	dirGeneral
	PROT.A50PTOC2.Str	dirPhsB
50-2 PhB Pickup		
	PROT.A50PTOC2.Str	general
	PROT.A50PTOC2.Str	phsB
50-2 PhC Dir Pickup		
	PROT.A50PTOC2.Str	dirGeneral
	PROT.A50PTOC2.Str	dirPhsC
50-2 PhC Pickup		
	PROT.A50PTOC2.Str	general
	PROT.A50PTOC2.Str	phsC
50-3 Enabled		
	PROT.A50PTOC3.Mod	stVal
	PROT.A50PTOC3.Beh	stVal
50-3 Operated		
	PROT.A50PTOC3.Op	general
50-3 PhA Dir Pickup		
	PROT.A50PTOC3.Str	dirGeneral
	PROT.A50PTOC3.Str	dirPhsA
50-3 PhA Pickup		
	PROT.A50PTOC3.Str	general
	PROT.A50PTOC3.Str	phsA
50-3 PhB Dir Pickup		
	PROT.A50PTOC3.Str	dirGeneral

	PROT.A50PTOC3.Str	dirPhsB
50-3 PhB Pickup		
	PROT.A50PTOC3.Str	general
	PROT.A50PTOC3.Str	phsB
50-3 PhC Dir Pickup		
	PROT.A50PTOC3.Str	dirGeneral
	PROT.A50PTOC3.Str	dirPhsC
50-3 PhC Pickup		
	PROT.A50PTOC3.Str	general
	PROT.A50PTOC3.Str	phsC
50-4 Enabled		
	PROT.A50PTOC4.Mod	stVal
	PROT.A50PTOC4.Beh	stVal
50-4 Operated		
	PROT.A50PTOC4.Op	general
50-4 PhA Dir Pickup		
	PROT.A50PTOC4.Str	dirGeneral
	PROT.A50PTOC4.Str	dirPhsA
50-4 PhA Pickup		
	PROT.A50PTOC4.Str	general
	PROT.A50PTOC4.Str	phsA
50-4 PhB Dir Pickup		
	PROT.A50PTOC4.Str	dirGeneral
	PROT.A50PTOC4.Str	dirPhsB
50-4 PhB Pickup		
	PROT.A50PTOC4.Str	general
	PROT.A50PTOC4.Str	phsB
50-4 PhC Dir Pickup		
	PROT.A50PTOC4.Str	dirGeneral
	PROT.A50PTOC4.Str	dirPhsC
50-4 PhC Pickup		
	PROT.A50PTOC4.Str	general
	PROT.A50PTOC4.Str	phsC
51-1 Enabled		
	PROT.A51PTOC1.Mod	stVal
	PROT.A51PTOC1.Beh	stVal
51-1 Operated		
	PROT.A51PTOC1.Op	general
51-1 PhA Dir Pickup		
	PROT.A51PTOC1.Str	dirGeneral
	PROT.A51PTOC1.Str	dirPhsA
51-1 PhA Pickup		
	PROT.A51PTOC1.Str	general
	PROT.A51PTOC1.Str	phsA
51-1 PhB Dir Pickup		
	PROT.A51PTOC1.Str	dirGeneral
	PROT.A51PTOC1.Str	dirPhsB
51-1 PhB Pickup		
	PROT.A51PTOC1.Str	general
	PROT.A51PTOC1.Str	phsB
51-1 PhC Dir Pickup		
	PROT.A51PTOC1.Str	dirGeneral
	PROT.A51PTOC1.Str	dirPhsC
51-1 PhC Pickup		
	PROT.A51PTOC1.Str	general
	PROT.A51PTOC1.Str	phsC
51-2 Enabled		
	PROT.A51PTOC2.Mod	stVal
	PROT.A51PTOC2.Beh	stVal
51-2 Operated		
	PROT.A51PTOC2.Op	general
51-2 PhA Dir Pickup		
	PROT.A51PTOC2.Str	dirGeneral
	PROT.A51PTOC2.Str	dirPhsA

51-2 PhA Pickup		
	PROT.A51PTOC2.Str	general
	PROT.A51PTOC2.Str	phsA
51-2 PhB Dir Pickup		
	PROT.A51PTOC2.Str	dirGeneral
	PROT.A51PTOC2.Str	dirPhsB
51-2 PhB Pickup		
	PROT.A51PTOC2.Str	general
	PROT.A51PTOC2.Str	phsB
51-2 PhC Dir Pickup		
	PROT.A51PTOC2.Str	dirGeneral
	PROT.A51PTOC2.Str	dirPhsC
51-2 PhC Pickup		
	PROT.A51PTOC2.Str	general
	PROT.A51PTOC2.Str	phsC
51-3 Enabled		
	PROT.A51PTOC3.Mod	stVal
	PROT.A51PTOC3.Beh	stVal
51-3 Operated		
	PROT.A51PTOC3.Op	general
51-3 PhA Dir Pickup		
	PROT.A51PTOC3.Str	dirGeneral
	PROT.A51PTOC3.Str	dirPhsA
51-3 PhA Pickup		
	PROT.A51PTOC3.Str	general
	PROT.A51PTOC3.Str	phsA
51-3 PhB Dir Pickup		
	PROT.A51PTOC3.Str	dirGeneral
	PROT.A51PTOC3.Str	dirPhsB
51-3 PhB Pickup		
	PROT.A51PTOC3.Str	general
	PROT.A51PTOC3.Str	phsB
51-3 PhC Dir Pickup		
	PROT.A51PTOC3.Str	dirGeneral
	PROT.A51PTOC3.Str	dirPhsC
51-3 PhC Pickup		
	PROT.A51PTOC3.Str	general
	PROT.A51PTOC3.Str	phsC
51-4 Enabled		
	PROT.A51PTOC4.Mod	stVal
	PROT.A51PTOC4.Beh	stVal
51-4 Operated		
	PROT.A51PTOC4.Op	general
51-4 PhA Dir Pickup		
	PROT.A51PTOC4.Str	dirGeneral
	PROT.A51PTOC4.Str	dirPhsA
51-4 PhA Pickup		
	PROT.A51PTOC4.Str	general
	PROT.A51PTOC4.Str	phsA
51-4 PhB Dir Pickup		
	PROT.A51PTOC4.Str	dirGeneral
	PROT.A51PTOC4.Str	dirPhsB
51-4 PhB Pickup		
	PROT.A51PTOC4.Str	general
	PROT.A51PTOC4.Str	phsB
51-4 PhC Dir Pickup		
	PROT.A51PTOC4.Str	dirGeneral
	PROT.A51PTOC4.Str	dirPhsC
51-4 PhC Pickup		
	PROT.A51PTOC4.Str	general
	PROT.A51PTOC4.Str	phsC
Inhibit 50-1		
	PROT.A50PTOC1.Mod	stVal
	PROT.A50PTOC1.Beh	stVal

Inhibit 50-2		
	PROT.A50PTOC2.Mod	stVal
	PROT.A50PTOC2.Beh	stVal
Inhibit 50-3		
	PROT.A50PTOC3.Mod	stVal
	PROT.A50PTOC3.Beh	stVal
Inhibit 50-4		
	PROT.A50PTOC4.Mod	stVal
	PROT.A50PTOC4.Beh	stVal
Inhibit 51-1		
	PROT.A51PTOC1.Mod	stVal
	PROT.A51PTOC1.Beh	stVal
Inhibit 51-2		
	PROT.A51PTOC2.Mod	stVal
	PROT.A51PTOC2.Beh	stVal
Inhibit 51-3		
	PROT.A51PTOC3.Mod	stVal
	PROT.A51PTOC3.Beh	stVal
Inhibit 51-4		
	PROT.A51PTOC4.Mod	stVal
	PROT.A51PTOC4.Beh	stVal

1.27 PHASE U/O VOLTAGE

Reyrolle	DOI	DA Group
27/59-1 Enabled		
	PROT.A2759PTOV1.Mod	stVal
	PROT.A2759PTOV1.Beh	stVal
	PROT.A2759PTUV1.Mod	stVal
	PROT.A2759PTUV1.Beh	stVal
27/59-1 Operated		
	PROT.A2759PTOV1.Op	general
	PROT.A2759PTUV1.Op	general
27/59-1 PhA Pickup		
	PROT.A2759PTOV1.Str	general
	PROT.A2759PTOV1.Str	phsA
	PROT.A2759PTUV1.Str	general
	PROT.A2759PTUV1.Str	phsA
27/59-1 PhB Pickup		
	PROT.A2759PTOV1.Str	general
	PROT.A2759PTOV1.Str	phsB
	PROT.A2759PTUV1.Str	general
	PROT.A2759PTUV1.Str	phsB
27/59-1 PhC Pickup		
	PROT.A2759PTOV1.Str	general
	PROT.A2759PTOV1.Str	phsC
	PROT.A2759PTUV1.Str	general
	PROT.A2759PTUV1.Str	phsC
27/59-2 Enabled		
	PROT.A2759PTOV2.Mod	stVal
	PROT.A2759PTOV2.Beh	stVal
	PROT.A2759PTUV2.Mod	stVal
	PROT.A2759PTUV2.Beh	stVal
27/59-2 Operated		
	PROT.A2759PTOV2.Op	general
	PROT.A2759PTUV2.Op	general
27/59-2 PhA Pickup		
	PROT.A2759PTOV2.Str	general
	PROT.A2759PTOV2.Str	phsA
	PROT.A2759PTUV2.Str	general
	PROT.A2759PTUV2.Str	phsA
27/59-2 PhB Pickup		

	PROT.A2759PTOV2.Str	general
	PROT.A2759PTOV2.Str	phsB
	PROT.A2759PTUV2.Str	general
	PROT.A2759PTUV2.Str	phsB
27/59-2 PhC Pickup		
	PROT.A2759PTOV2.Str	general
	PROT.A2759PTOV2.Str	phsC
	PROT.A2759PTUV2.Str	general
	PROT.A2759PTUV2.Str	phsC
27/59-3 Enabled		
	PROT.A2759PTOV3.Mod	stVal
	PROT.A2759PTOV3.Beh	stVal
	PROT.A2759PTUV3.Mod	stVal
	PROT.A2759PTUV3.Beh	stVal
27/59-3 Operated		
	PROT.A2759PTOV3.Op	general
	PROT.A2759PTUV3.Op	general
27/59-3 PhA Pickup		
	PROT.A2759PTOV3.Str	general
	PROT.A2759PTOV3.Str	phsA
	PROT.A2759PTUV3.Str	general
	PROT.A2759PTUV3.Str	phsA
27/59-3 PhB Pickup		
	PROT.A2759PTOV3.Str	general
	PROT.A2759PTOV3.Str	phsB
	PROT.A2759PTUV3.Str	general
	PROT.A2759PTUV3.Str	phsB
27/59-3 PhC Pickup		
	PROT.A2759PTOV3.Str	general
	PROT.A2759PTOV3.Str	phsC
	PROT.A2759PTUV3.Str	general
	PROT.A2759PTUV3.Str	phsC
27/59-4 Enabled		
	PROT.A2759PTOV4.Mod	stVal
	PROT.A2759PTOV4.Beh	stVal
	PROT.A2759PTUV4.Mod	stVal
	PROT.A2759PTUV4.Beh	stVal
27/59-4 Operated		
	PROT.A2759PTOV4.Op	general
	PROT.A2759PTUV4.Op	general
27/59-4 PhA Pickup		
	PROT.A2759PTOV4.Str	general
	PROT.A2759PTOV4.Str	phsA
	PROT.A2759PTUV4.Str	general
	PROT.A2759PTUV4.Str	phsA
27/59-4 PhB Pickup		
	PROT.A2759PTOV4.Str	general
	PROT.A2759PTOV4.Str	phsB
	PROT.A2759PTUV4.Str	general
	PROT.A2759PTUV4.Str	phsB
27/59-4 PhC Pickup		
	PROT.A2759PTOV4.Str	general
	PROT.A2759PTOV4.Str	phsC
	PROT.A2759PTUV4.Str	general
	PROT.A2759PTUV4.Str	phsC
Inhibit 27/59-1		
	PROT.A2759PTOV1.Mod	stVal
	PROT.A2759PTOV1.Beh	stVal
	PROT.A2759PTUV1.Mod	stVal
	PROT.A2759PTUV1.Beh	stVal
Inhibit 27/59-2		
	PROT.A2759PTOV2.Mod	stVal
	PROT.A2759PTOV2.Beh	stVal
	PROT.A2759PTUV2.Mod	stVal

	PROT.A2759PTUV2.Beh	stVal
Inhibit 27/59-3		
	PROT.A2759PTOV3.Mod	stVal
	PROT.A2759PTOV3.Beh	stVal
	PROT.A2759PTUV3.Mod	stVal
	PROT.A2759PTUV3.Beh	stVal
Inhibit 27/59-4		
	PROT.A2759PTOV4.Mod	stVal
	PROT.A2759PTOV4.Beh	stVal
	PROT.A2759PTUV4.Mod	stVal
	PROT.A2759PTUV4.Beh	stVal

1.28 RESTRICTED EARTH FAULT

Reyrolle	DOI	DA Group
64H Enabled		
	PROT.A64hPTOC1.Mod	stVal
	PROT.A64hPTOC1.Beh	stVal
64H Operated		
	PROT.A64hPTOC1.Op	general
64H Pickup		
	PROT.A64hPTOC1.Str	general
Inhibit 64H		
	PROT.A64hPTOC1.Mod	stVal
	PROT.A64hPTOC1.Beh	stVal

1.29 SENSITIVE EARTH FAULT MENU

Reyrolle	DOI	DA Group
50SEF-1 Dir Pickup		
	PROT.A50SefPTOC1.Str	dirGeneral
50SEF-1 Enabled		
	PROT.A50SefPTOC1.Mod	stVal
	PROT.A50SefPTOC1.Beh	stVal
50SEF-1 Operated		
	PROT.A50SefPTOC1.Op	general
50SEF-1 Pickup		
	PROT.A50SefPTOC1.Str	general
50SEF-2 Dir Pickup		
	PROT.A50SefPTOC2.Str	dirGeneral
50SEF-2 Enabled		
	PROT.A50SefPTOC2.Mod	stVal
	PROT.A50SefPTOC2.Beh	stVal
50SEF-2 Operated		
	PROT.A50SefPTOC2.Op	general
50SEF-2 Pickup		
	PROT.A50SefPTOC2.Str	general
50SEF-3 Dir Pickup		
	PROT.A50SefPTOC3.Str	dirGeneral
50SEF-3 Enabled		
	PROT.A50SefPTOC3.Mod	stVal
	PROT.A50SefPTOC3.Beh	stVal
50SEF-3 Operated		
	PROT.A50SefPTOC3.Op	general
50SEF-3 Pickup		
	PROT.A50SefPTOC3.Str	general
50SEF-4 Dir Pickup		
	PROT.A50SefPTOC4.Str	dirGeneral
50SEF-4 Enabled		
	PROT.A50SefPTOC4.Mod	stVal
	PROT.A50SefPTOC4.Beh	stVal

50SEF-4 Operated		
	PROT.A50SefPTOC4.Op	general
50SEF-4 Pickup		
	PROT.A50SefPTOC4.Str	general
51SEF-1 Dir Pickup		
	PROT.A51SefPTOC1.Str	dirGeneral
51SEF-1 Enabled		
	PROT.A51SefPTOC1.Mod	stVal
	PROT.A51SefPTOC1.Beh	stVal
51SEF-1 Operated		
	PROT.A51SefPTOC1.Op	general
51SEF-1 Pickup		
	PROT.A51SefPTOC1.Str	general
51SEF-2 Dir Pickup		
	PROT.A51SefPTOC2.Str	dirGeneral
51SEF-2 Enabled		
	PROT.A51SefPTOC2.Mod	stVal
	PROT.A51SefPTOC2.Beh	stVal
51SEF-2 Operated		
	PROT.A51SefPTOC2.Op	general
51SEF-2 Pickup		
	PROT.A51SefPTOC2.Str	general
51SEF-3 Dir Pickup		
	PROT.A51SefPTOC3.Str	dirGeneral
51SEF-3 Enabled		
	PROT.A51SefPTOC3.Mod	stVal
	PROT.A51SefPTOC3.Beh	stVal
51SEF-3 Operated		
	PROT.A51SefPTOC3.Op	general
51SEF-3 Pickup		
	PROT.A51SefPTOC3.Str	general
51SEF-4 Dir Pickup		
	PROT.A51SefPTOC4.Str	dirGeneral
51SEF-4 Enabled		
	PROT.A51SefPTOC4.Mod	stVal
	PROT.A51SefPTOC4.Beh	stVal
51SEF-4 Operated		
	PROT.A51SefPTOC4.Op	general
51SEF-4 Pickup		
	PROT.A51SefPTOC4.Str	general
Inhibit 50SEF-1		
	PROT.A50SefPTOC1.Mod	stVal
	PROT.A50SefPTOC1.Beh	stVal
Inhibit 50SEF-2		
	PROT.A50SefPTOC2.Mod	stVal
	PROT.A50SefPTOC2.Beh	stVal
Inhibit 50SEF-3		
	PROT.A50SefPTOC3.Mod	stVal
	PROT.A50SefPTOC3.Beh	stVal
Inhibit 50SEF-4		
	PROT.A50SefPTOC4.Mod	stVal
	PROT.A50SefPTOC4.Beh	stVal
Inhibit 51SEF-1		
	PROT.A51SefPTOC1.Mod	stVal
	PROT.A51SefPTOC1.Beh	stVal
Inhibit 51SEF-2		
	PROT.A51SefPTOC2.Mod	stVal
	PROT.A51SefPTOC2.Beh	stVal
Inhibit 51SEF-3		
	PROT.A51SefPTOC3.Mod	stVal
	PROT.A51SefPTOC3.Beh	stVal
Inhibit 51SEF-4		
	PROT.A51SefPTOC4.Mod	stVal
	PROT.A51SefPTOC4.Beh	stVal

1.30 Single Point Controls (Enhanced Security)

Reyrolle	DOI	DA Group
SPDOes 1 Control		
	CTRL.SPDOesGGIO1.SPCSO	Oper.ctlVal
SPDOes 1 Status		
	CTRL.SPDOesGGIO1.SPCSO	stVal
SPDOes 2 Control		
	CTRL.SPDOesGGIO2.SPCSO	Oper.ctlVal
SPDOes 2 Status		
	CTRL.SPDOesGGIO2.SPCSO	stVal
SPDOes 3 Control		
	CTRL.SPDOesGGIO3.SPCSO	Oper.ctlVal
SPDOes 3 Status		
	CTRL.SPDOesGGIO3.SPCSO	stVal
SPDOes 4 Control		
	CTRL.SPDOesGGIO4.SPCSO	Oper.ctlVal
SPDOes 4 Status		
	CTRL.SPDOesGGIO4.SPCSO	stVal

1.31 Single Point Controls (Normal Security)

Reyrolle	DOI	DA Group
SPDOns 1 Control		
	CTRL.SPDOnsGGIO1.SPCSO	Oper.ctlVal
SPDOns 1 Status		
	CTRL.SPDOnsGGIO1.SPCSO	stVal
SPDOns 2 Control		
	CTRL.SPDOnsGGIO2.SPCSO	Oper.ctlVal
SPDOns 2 Status		
	CTRL.SPDOnsGGIO2.SPCSO	stVal
SPDOns 3 Control		
	CTRL.SPDOnsGGIO3.SPCSO	Oper.ctlVal
SPDOns 3 Status		
	CTRL.SPDOnsGGIO3.SPCSO	stVal
SPDOns 4 Control		
	CTRL.SPDOnsGGIO4.SPCSO	Oper.ctlVal
SPDOns 4 Status		
	CTRL.SPDOnsGGIO4.SPCSO	stVal

1.32 Single Point Inputs

Reyrolle	DOI	DA Group
SPi64GGIO1 SPCSO 1		
	CTRL.SPi64GGIO1.SPCSO1	ctlVal
SPi64GGIO1 SPCSO 10		
	CTRL.SPi64GGIO1.SPCSO10	ctlVal
SPi64GGIO1 SPCSO 11		
	CTRL.SPi64GGIO1.SPCSO11	ctlVal
SPi64GGIO1 SPCSO 12		
	CTRL.SPi64GGIO1.SPCSO12	ctlVal
SPi64GGIO1 SPCSO 13		
	CTRL.SPi64GGIO1.SPCSO13	ctlVal
SPi64GGIO1 SPCSO 14		
	CTRL.SPi64GGIO1.SPCSO14	ctlVal
SPi64GGIO1 SPCSO 15		
	CTRL.SPi64GGIO1.SPCSO15	ctlVal
SPi64GGIO1 SPCSO 16		
	CTRL.SPi64GGIO1.SPCSO16	ctlVal

SPI64GGIO1 SPCSO 17		
	CTRL.SPI64GGIO1.SPCSO17	ctlVal
SPI64GGIO1 SPCSO 18		
	CTRL.SPI64GGIO1.SPCSO18	ctlVal
SPI64GGIO1 SPCSO 19		
	CTRL.SPI64GGIO1.SPCSO19	ctlVal
SPI64GGIO1 SPCSO 2		
	CTRL.SPI64GGIO1.SPCSO2	ctlVal
SPI64GGIO1 SPCSO 20		
	CTRL.SPI64GGIO1.SPCSO20	ctlVal
SPI64GGIO1 SPCSO 21		
	CTRL.SPI64GGIO1.SPCSO21	ctlVal
SPI64GGIO1 SPCSO 22		
	CTRL.SPI64GGIO1.SPCSO22	ctlVal
SPI64GGIO1 SPCSO 23		
	CTRL.SPI64GGIO1.SPCSO23	ctlVal
SPI64GGIO1 SPCSO 24		
	CTRL.SPI64GGIO1.SPCSO24	ctlVal
SPI64GGIO1 SPCSO 25		
	CTRL.SPI64GGIO1.SPCSO25	ctlVal
SPI64GGIO1 SPCSO 26		
	CTRL.SPI64GGIO1.SPCSO26	ctlVal
SPI64GGIO1 SPCSO 27		
	CTRL.SPI64GGIO1.SPCSO27	ctlVal
SPI64GGIO1 SPCSO 28		
	CTRL.SPI64GGIO1.SPCSO28	ctlVal
SPI64GGIO1 SPCSO 29		
	CTRL.SPI64GGIO1.SPCSO29	ctlVal
SPI64GGIO1 SPCSO 3		
	CTRL.SPI64GGIO1.SPCSO3	ctlVal
SPI64GGIO1 SPCSO 30		
	CTRL.SPI64GGIO1.SPCSO30	ctlVal
SPI64GGIO1 SPCSO 31		
	CTRL.SPI64GGIO1.SPCSO31	ctlVal
SPI64GGIO1 SPCSO 32		
	CTRL.SPI64GGIO1.SPCSO32	ctlVal
SPI64GGIO1 SPCSO 33		
	CTRL.SPI64GGIO1.SPCSO33	ctlVal
SPI64GGIO1 SPCSO 34		
	CTRL.SPI64GGIO1.SPCSO34	ctlVal
SPI64GGIO1 SPCSO 35		
	CTRL.SPI64GGIO1.SPCSO35	ctlVal
SPI64GGIO1 SPCSO 36		
	CTRL.SPI64GGIO1.SPCSO36	ctlVal
SPI64GGIO1 SPCSO 37		
	CTRL.SPI64GGIO1.SPCSO37	ctlVal
SPI64GGIO1 SPCSO 38		
	CTRL.SPI64GGIO1.SPCSO38	ctlVal
SPI64GGIO1 SPCSO 39		
	CTRL.SPI64GGIO1.SPCSO39	ctlVal
SPI64GGIO1 SPCSO 4		
	CTRL.SPI64GGIO1.SPCSO4	ctlVal
SPI64GGIO1 SPCSO 40		
	CTRL.SPI64GGIO1.SPCSO40	ctlVal
SPI64GGIO1 SPCSO 41		
	CTRL.SPI64GGIO1.SPCSO41	ctlVal
SPI64GGIO1 SPCSO 42		
	CTRL.SPI64GGIO1.SPCSO42	ctlVal
SPI64GGIO1 SPCSO 43		
	CTRL.SPI64GGIO1.SPCSO43	ctlVal
SPI64GGIO1 SPCSO 44		
	CTRL.SPI64GGIO1.SPCSO44	ctlVal
SPI64GGIO1 SPCSO 45		
	CTRL.SPI64GGIO1.SPCSO45	ctlVal

SPi64GGIO1 SPCSO 46		
	CTRL.SPi64GGIO1.SPCSO46	ctlVal
SPi64GGIO1 SPCSO 47		
	CTRL.SPi64GGIO1.SPCSO47	ctlVal
SPi64GGIO1 SPCSO 48		
	CTRL.SPi64GGIO1.SPCSO48	ctlVal
SPi64GGIO1 SPCSO 49		
	CTRL.SPi64GGIO1.SPCSO49	ctlVal
SPi64GGIO1 SPCSO 5		
	CTRL.SPi64GGIO1.SPCSO5	ctlVal
SPi64GGIO1 SPCSO 50		
	CTRL.SPi64GGIO1.SPCSO50	ctlVal
SPi64GGIO1 SPCSO 51		
	CTRL.SPi64GGIO1.SPCSO51	ctlVal
SPi64GGIO1 SPCSO 52		
	CTRL.SPi64GGIO1.SPCSO52	ctlVal
SPi64GGIO1 SPCSO 53		
	CTRL.SPi64GGIO1.SPCSO53	ctlVal
SPi64GGIO1 SPCSO 54		
	CTRL.SPi64GGIO1.SPCSO54	ctlVal
SPi64GGIO1 SPCSO 55		
	CTRL.SPi64GGIO1.SPCSO55	ctlVal
SPi64GGIO1 SPCSO 56		
	CTRL.SPi64GGIO1.SPCSO56	ctlVal
SPi64GGIO1 SPCSO 57		
	CTRL.SPi64GGIO1.SPCSO57	ctlVal
SPi64GGIO1 SPCSO 58		
	CTRL.SPi64GGIO1.SPCSO58	ctlVal
SPi64GGIO1 SPCSO 59		
	CTRL.SPi64GGIO1.SPCSO59	ctlVal
SPi64GGIO1 SPCSO 6		
	CTRL.SPi64GGIO1.SPCSO6	ctlVal
SPi64GGIO1 SPCSO 60		
	CTRL.SPi64GGIO1.SPCSO60	ctlVal
SPi64GGIO1 SPCSO 61		
	CTRL.SPi64GGIO1.SPCSO61	ctlVal
SPi64GGIO1 SPCSO 62		
	CTRL.SPi64GGIO1.SPCSO62	ctlVal
SPi64GGIO1 SPCSO 63		
	CTRL.SPi64GGIO1.SPCSO63	ctlVal
SPi64GGIO1 SPCSO 64		
	CTRL.SPi64GGIO1.SPCSO64	ctlVal
SPi64GGIO1 SPCSO 7		
	CTRL.SPi64GGIO1.SPCSO7	ctlVal
SPi64GGIO1 SPCSO 8		
	CTRL.SPi64GGIO1.SPCSO8	ctlVal
SPi64GGIO1 SPCSO 9		
	CTRL.SPi64GGIO1.SPCSO9	ctlVal

1.33 Single Point Outputs

Reyrolle	DOI	DA Group
SPo32GGIO1 Ind 1		
	CTRL.SPo32GGIO1.Ind1	stVal
SPo32GGIO1 Ind 10		
	CTRL.SPo32GGIO1.Ind10	stVal
SPo32GGIO1 Ind 11		
	CTRL.SPo32GGIO1.Ind11	stVal
SPo32GGIO1 Ind 12		
	CTRL.SPo32GGIO1.Ind12	stVal
SPo32GGIO1 Ind 13		
	CTRL.SPo32GGIO1.Ind13	stVal

SPo32GGIO1 Ind 14		
	CTRL.SPo32GGIO1.Ind14	stVal
SPo32GGIO1 Ind 15		
	CTRL.SPo32GGIO1.Ind15	stVal
SPo32GGIO1 Ind 16		
	CTRL.SPo32GGIO1.Ind16	stVal
SPo32GGIO1 Ind 17		
	CTRL.SPo32GGIO1.Ind17	stVal
SPo32GGIO1 Ind 18		
	CTRL.SPo32GGIO1.Ind18	stVal
SPo32GGIO1 Ind 19		
	CTRL.SPo32GGIO1.Ind19	stVal
SPo32GGIO1 Ind 2		
	CTRL.SPo32GGIO1.Ind2	stVal
SPo32GGIO1 Ind 20		
	CTRL.SPo32GGIO1.Ind20	stVal
SPo32GGIO1 Ind 21		
	CTRL.SPo32GGIO1.Ind21	stVal
SPo32GGIO1 Ind 22		
	CTRL.SPo32GGIO1.Ind22	stVal
SPo32GGIO1 Ind 23		
	CTRL.SPo32GGIO1.Ind23	stVal
SPo32GGIO1 Ind 24		
	CTRL.SPo32GGIO1.Ind24	stVal
SPo32GGIO1 Ind 25		
	CTRL.SPo32GGIO1.Ind25	stVal
SPo32GGIO1 Ind 26		
	CTRL.SPo32GGIO1.Ind26	stVal
SPo32GGIO1 Ind 27		
	CTRL.SPo32GGIO1.Ind27	stVal
SPo32GGIO1 Ind 28		
	CTRL.SPo32GGIO1.Ind28	stVal
SPo32GGIO1 Ind 29		
	CTRL.SPo32GGIO1.Ind29	stVal
SPo32GGIO1 Ind 3		
	CTRL.SPo32GGIO1.Ind3	stVal
SPo32GGIO1 Ind 30		
	CTRL.SPo32GGIO1.Ind30	stVal
SPo32GGIO1 Ind 31		
	CTRL.SPo32GGIO1.Ind31	stVal
SPo32GGIO1 Ind 32		
	CTRL.SPo32GGIO1.Ind32	stVal
SPo32GGIO1 Ind 4		
	CTRL.SPo32GGIO1.Ind4	stVal
SPo32GGIO1 Ind 5		
	CTRL.SPo32GGIO1.Ind5	stVal
SPo32GGIO1 Ind 6		
	CTRL.SPo32GGIO1.Ind6	stVal
SPo32GGIO1 Ind 7		
	CTRL.SPo32GGIO1.Ind7	stVal
SPo32GGIO1 Ind 8		
	CTRL.SPo32GGIO1.Ind8	stVal
SPo32GGIO1 Ind 9		
	CTRL.SPo32GGIO1.Ind9	stVal

1.34 THERMAL MENU

Reyrolle	DOI	DA Group
49 Enabled		
	PROT.A49PTTR1.Mod	stVal
	PROT.A49PTTR1.Beh	stVal
49 Operated		
	PROT.A49PTTR1.Op	general
49 Pickup		
	PROT.A49PTTR1.Str	general
49 Thermal Alarm		
	PROT.A49PTTR1.AlmThm	general
Inhibit 49		
	PROT.A49PTTR1.Mod	stVal
	PROT.A49PTTR1.Beh	stVal

1.35 U/O FREQUENCY

Reyrolle	DOI	DA Group
81-1 Enabled		
	PROT.A81PTOF1.Mod	stVal
	PROT.A81PTOF1.Beh	stVal
	PROT.A81PTUF1.Mod	stVal
	PROT.A81PTUF1.Beh	stVal
81-1 Operated		
	PROT.A81PTOF1.Op	general
	PROT.A81PTUF1.Op	general
81-1 Pickup		
	PROT.A81PTOF1.Str	general
	PROT.A81PTUF1.Str	general
81-2 Enabled		
	PROT.A81PTOF2.Mod	stVal
	PROT.A81PTOF2.Beh	stVal
	PROT.A81PTUF2.Mod	stVal
	PROT.A81PTUF2.Beh	stVal
81-2 Operated		
	PROT.A81PTOF2.Op	general
	PROT.A81PTUF2.Op	general
81-2 Pickup		
	PROT.A81PTOF2.Str	general
	PROT.A81PTUF2.Str	general
81-3 Enabled		
	PROT.A81PTOF3.Mod	stVal
	PROT.A81PTOF3.Beh	stVal
	PROT.A81PTUF3.Mod	stVal
	PROT.A81PTUF3.Beh	stVal
81-3 Operated		
	PROT.A81PTOF3.Op	general
	PROT.A81PTUF3.Op	general
81-3 Pickup		
	PROT.A81PTOF3.Str	general
	PROT.A81PTUF3.Str	general
81-4 Enabled		
	PROT.A81PTOF4.Mod	stVal
	PROT.A81PTOF4.Beh	stVal
	PROT.A81PTUF4.Mod	stVal
	PROT.A81PTUF4.Beh	stVal
81-4 Operated		
	PROT.A81PTOF4.Op	general
	PROT.A81PTUF4.Op	general
81-4 Pickup		

	PROT.A81PTOF4.Str	general
	PROT.A81PTUF4.Str	general
81-5 Enabled		
	PROT.A81PTOF5.Mod	stVal
	PROT.A81PTOF5.Beh	stVal
	PROT.A81PTUF5.Mod	stVal
	PROT.A81PTUF5.Beh	stVal
81-5 Operated		
	PROT.A81PTOF5.Op	general
	PROT.A81PTUF5.Op	general
81-5 Pickup		
	PROT.A81PTOF5.Str	general
	PROT.A81PTUF5.Str	general
81-6 Enabled		
	PROT.A81PTOF6.Mod	stVal
	PROT.A81PTOF6.Beh	stVal
	PROT.A81PTUF6.Mod	stVal
	PROT.A81PTUF6.Beh	stVal
81-6 Operated		
	PROT.A81PTOF6.Op	general
	PROT.A81PTUF6.Op	general
81-6 Pickup		
	PROT.A81PTOF6.Str	general
	PROT.A81PTUF6.Str	general
Inhibit 81-1		
	PROT.A81PTOF1.Mod	stVal
	PROT.A81PTOF1.Beh	stVal
	PROT.A81PTUF1.Mod	stVal
	PROT.A81PTUF1.Beh	stVal
Inhibit 81-2		
	PROT.A81PTOF2.Mod	stVal
	PROT.A81PTOF2.Beh	stVal
	PROT.A81PTUF2.Mod	stVal
	PROT.A81PTUF2.Beh	stVal
Inhibit 81-3		
	PROT.A81PTOF3.Mod	stVal
	PROT.A81PTOF3.Beh	stVal
	PROT.A81PTUF3.Mod	stVal
	PROT.A81PTUF3.Beh	stVal
Inhibit 81-4		
	PROT.A81PTOF4.Mod	stVal
	PROT.A81PTOF4.Beh	stVal
	PROT.A81PTUF4.Mod	stVal
	PROT.A81PTUF4.Beh	stVal
Inhibit 81-5		
	PROT.A81PTOF5.Mod	stVal
	PROT.A81PTOF5.Beh	stVal
	PROT.A81PTUF5.Mod	stVal
	PROT.A81PTUF5.Beh	stVal
Inhibit 81-6		
	PROT.A81PTOF6.Mod	stVal
	PROT.A81PTOF6.Beh	stVal
	PROT.A81PTUF6.Mod	stVal
	PROT.A81PTUF6.Beh	stVal

1.36 UNDER CURRENT MENU

Reyrolle	DOI	DA Group
37-1 Enabled		
	PROT.A37PTUC1.Mod	stVal
	PROT.A37PTUC1.Beh	stVal
37-1 Operated		
	PROT.A37PTUC1.Op	general
37-1 PhA Pickup		
	PROT.A37PTUC1.Str	general
	PROT.A37PTUC1.Str	phsA
37-1 PhB Pickup		
	PROT.A37PTUC1.Str	general
	PROT.A37PTUC1.Str	phsB
37-1 PhC Pickup		
	PROT.A37PTUC1.Str	general
	PROT.A37PTUC1.Str	phsC
37-2 Enabled		
	PROT.A37PTUC2.Mod	stVal
	PROT.A37PTUC2.Beh	stVal
37-2 Operated		
	PROT.A37PTUC2.Op	general
37-2 PhA Pickup		
	PROT.A37PTUC2.Str	general
	PROT.A37PTUC2.Str	phsA
37-2 PhB Pickup		
	PROT.A37PTUC2.Str	general
	PROT.A37PTUC2.Str	phsB
37-2 PhC Pickup		
	PROT.A37PTUC2.Str	general
	PROT.A37PTUC2.Str	phsC
37G-1 Enabled		
	PROT.A37gPTUC1.Mod	stVal
	PROT.A37gPTUC1.Beh	stVal
37G-1 Operated		
	PROT.A37gPTUC1.Op	general
37G-1 Pickup		
	PROT.A37gPTUC1.Str	general
37G-2 Enabled		
	PROT.A37gPTUC2.Mod	stVal
	PROT.A37gPTUC2.Beh	stVal
37G-2 Operated		
	PROT.A37gPTUC2.Op	general
37G-2 Pickup		
	PROT.A37gPTUC2.Str	general
37SEF-1 Enabled		
	PROT.A37SefPTUC1.Mod	stVal
	PROT.A37SefPTUC1.Beh	stVal
37SEF-1 Operated		
	PROT.A37SefPTUC1.Op	general
37SEF-1 Pickup		
	PROT.A37SefPTUC1.Str	general
37SEF-2 Enabled		
	PROT.A37SefPTUC2.Mod	stVal
	PROT.A37SefPTUC2.Beh	stVal
37SEF-2 Operated		
	PROT.A37SefPTUC2.Op	general
37SEF-2 Pickup		
	PROT.A37SefPTUC2.Str	general
Inhibit 37-1		
	PROT.A37PTUC1.Mod	stVal
	PROT.A37PTUC1.Beh	stVal

Inhibit 37-2		
	PROT.A37PTUC2.Mod	stVal
	PROT.A37PTUC2.Beh	stVal
Inhibit 37G-1		
	PROT.A37gPTUC1.Mod	stVal
	PROT.A37gPTUC1.Beh	stVal
Inhibit 37G-2		
	PROT.A37gPTUC2.Mod	stVal
	PROT.A37gPTUC2.Beh	stVal
Inhibit 37SEF-1		
	PROT.A37SefPTUC1.Mod	stVal
	PROT.A37SefPTUC1.Beh	stVal
Inhibit 37SEF-2		
	PROT.A37SefPTUC2.Mod	stVal
	PROT.A37SefPTUC2.Beh	stVal

1.37 VOLTAGE METERS

Reyrolle	DOI	DA Group
Sequence Components V Seq NPS		
	MEAS.V_MSQI1.SeqV	c2.instCVal.mag.f
	MEAS.V_MSQI1.SeqV	c2.cVal.mag.f
	MEAS.V_MSQI1.SeqV	c2.units.SIUnit
	MEAS.V_MSQI1.SeqV	c2.units.multiplier
Sequence Components V Seq PPS		
	MEAS.V_MSQI1.SeqV	c1.instCVal.mag.f
	MEAS.V_MSQI1.SeqV	c1.cVal.mag.f
	MEAS.V_MSQI1.SeqV	c1.units.SIUnit
	MEAS.V_MSQI1.SeqV	c1.units.multiplier
Sequence Components V Seq ZPS		
	MEAS.V_MSQI1.SeqV	c3.instCVal.mag.f
	MEAS.V_MSQI1.SeqV	c3.cVal.mag.f
	MEAS.V_MSQI1.SeqV	c3.units.SIUnit
	MEAS.V_MSQI1.SeqV	c3.units.multiplier

1.38 Vx U/O VOLTAGE

Reyrolle	DOI	DA Group
Inhibit Vx 27/59		
	PROT.A2759PTOV5.Mod	stVal
	PROT.A2759PTOV5.Beh	stVal
	PROT.A2759PTUV5.Mod	stVal
	PROT.A2759PTUV5.Beh	stVal
Vx 27/59 Enabled		
	PROT.A2759PTOV5.Mod	stVal
	PROT.A2759PTOV5.Beh	stVal
	PROT.A2759PTUV5.Mod	stVal
	PROT.A2759PTUV5.Beh	stVal
Vx 27/59 Operated		
	PROT.A2759PTOV5.Op	general
	PROT.A2759PTUV5.Op	general
Vx 27/59 Pickup		
	PROT.A2759PTOV5.Str	general
	PROT.A2759PTUV5.Str	general

2. IEC 61850 -> REYROLLE

2.1 PROT

2.1.1 A2759PTOV1

Beh		
	stVal	Out of Service
		Inhibit 27/59-1
		27/59-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-1
		27/59-1 Enabled
Op		
	general	27/59-1 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-1 PhA Pickup
		27/59-1 PhB Pickup
		27/59-1 PhC Pickup
	phsA	27/59-1 PhA Pickup
	phsB	27/59-1 PhB Pickup
	phsC	27/59-1 PhC Pickup

2.1.2 A2759PTOV2

Beh		
	stVal	Out of Service
		Inhibit 27/59-2
		27/59-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-2
		27/59-2 Enabled
Op		
	general	27/59-2 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-2 PhA Pickup
		27/59-2 PhB Pickup
		27/59-2 PhC Pickup
	phsA	27/59-2 PhA Pickup
	phsB	27/59-2 PhB Pickup
	phsC	27/59-2 PhC Pickup

2.1.3 A2759PTOV3

Beh		
	stVal	Out of Service
		Inhibit 27/59-3
		27/59-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-3
		27/59-3 Enabled
Op		
	general	27/59-3 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-3 PhA Pickup
		27/59-3 PhB Pickup
		27/59-3 PhC Pickup
	phsA	27/59-3 PhA Pickup
	phsB	27/59-3 PhB Pickup
	phsC	27/59-3 PhC Pickup

2.1.4 A2759PTOV4

Beh		
	stVal	Out of Service
		Inhibit 27/59-4
		27/59-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-4
		27/59-4 Enabled
Op		
	general	27/59-4 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-4 PhA Pickup
		27/59-4 PhB Pickup
		27/59-4 PhC Pickup
	phsA	27/59-4 PhA Pickup
	phsB	27/59-4 PhB Pickup
	phsC	27/59-4 PhC Pickup

2.1.5 A2759PTOV5

Beh		
	stVal	Out of Service
		Inhibit Vx 27/59
		Vx 27/59 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit Vx 27/59
		Vx 27/59 Enabled
Op		
	general	Vx 27/59 Operated
Str		
	dirGeneral	Non-Directional
	general	Vx 27/59 Pickup

2.1.6 A2759PTUV1

Beh		
	stVal	Out of Service
		Inhibit 27/59-1
		27/59-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-1
		27/59-1 Enabled
Op		
	general	27/59-1 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-1 PhA Pickup
		27/59-1 PhB Pickup
		27/59-1 PhC Pickup
	phsA	27/59-1 PhA Pickup
	phsB	27/59-1 PhB Pickup
	phsC	27/59-1 PhC Pickup

2.1.7 A2759PTUV2

Beh		
	stVal	Out of Service
		Inhibit 27/59-2
		27/59-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-2
		27/59-2 Enabled
Op		
	general	27/59-2 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-2 PhA Pickup
		27/59-2 PhB Pickup

		27/59-2 PhC Pickup
	phsA	27/59-2 PhA Pickup
	phsB	27/59-2 PhB Pickup
	phsC	27/59-2 PhC Pickup

2.1.8 A2759PTUV3

Beh		
	stVal	Out of Service
		Inhibit 27/59-3
		27/59-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-3
		27/59-3 Enabled
Op		
	general	27/59-3 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-3 PhA Pickup
		27/59-3 PhB Pickup
		27/59-3 PhC Pickup
	phsA	27/59-3 PhA Pickup
	phsB	27/59-3 PhB Pickup
	phsC	27/59-3 PhC Pickup

2.1.9 A2759PTUV4

Beh		
	stVal	Out of Service
		Inhibit 27/59-4
		27/59-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 27/59-4
		27/59-4 Enabled
Op		
	general	27/59-4 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	27/59-4 PhA Pickup
		27/59-4 PhB Pickup
		27/59-4 PhC Pickup
	phsA	27/59-4 PhA Pickup
	phsB	27/59-4 PhB Pickup
	phsC	27/59-4 PhC Pickup

2.1.10 A2759PTUV5

Beh		
	stVal	Out of Service
		Inhibit Vx 27/59
		Vx 27/59 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit Vx 27/59
		Vx 27/59 Enabled
Op		
	general	Vx 27/59 Operated
Str		
	dirGeneral	Non-Directional
	general	Vx 27/59 Pickup

2.1.11 A37gPTUC1

Beh		
	stVal	Out of Service
		Inhibit 37G-1
		37G-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 37G-1
		37G-1 Enabled
Op		
	general	37G-1 Operated
Str		
	dirGeneral	Non-Directional
	general	37G-1 Pickup

2.1.12 A37gPTUC2

Beh		
	stVal	Out of Service
		Inhibit 37G-2
		37G-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 37G-2
		37G-2 Enabled
Op		
	general	37G-2 Operated
Str		
	dirGeneral	Non-Directional
	general	37G-2 Pickup

2.1.13 A37PTUC1

Beh		
	stVal	Out of Service
		Inhibit 37-1
		37-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 37-1
		37-1 Enabled
Op		
	general	37-1 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	37-1 PhA Pickup
		37-1 PhB Pickup
		37-1 PhC Pickup
	phsA	37-1 PhA Pickup
	phsB	37-1 PhB Pickup
	phsC	37-1 PhC Pickup

2.1.14 A37PTUC2

Beh		
	stVal	Out of Service
		Inhibit 37-2
		37-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 37-2
		37-2 Enabled
Op		
	general	37-2 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	37-2 PhA Pickup
		37-2 PhB Pickup
		37-2 PhC Pickup
	phsA	37-2 PhA Pickup
	phsB	37-2 PhB Pickup
	phsC	37-2 PhC Pickup

2.1.15 A37SefPTUC1

Beh		
	stVal	Out of Service
		Inhibit 37SEF-1
		37SEF-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 37SEF-1
		37SEF-1 Enabled
Op		
	general	37SEF-1 Operated
Str		
	dirGeneral	Non-Directional
	general	37SEF-1 Pickup

2.1.16 A37SefPTUC2

Beh		
	stVal	Out of Service
		Inhibit 37SEF-2
		37SEF-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 37SEF-2
		37SEF-2 Enabled
Op		
	general	37SEF-2 Operated
Str		
	dirGeneral	Non-Directional
	general	37SEF-2 Pickup

2.1.17 A46BcPTOC1

Beh		
	stVal	Out of Service
		Inhibit 46BC
		46BC Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 46BC
		46BC Enabled
Op		
	general	46BC Operated
Str		
	dirGeneral	Non-Directional
	general	46BC Pickup

2.1.18 A46DtPTOC1

Beh		
	stVal	Out of Service
		Inhibit 46DT
		46DT Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 46DT

		46DT Enabled
Op		
	general	46DT Operated
Str		
	dirGeneral	Non-Directional
	general	46DT Pickup

2.1.19 A46ItPTOC1

Beh		
	stVal	Out of Service
		Inhibit 46IT
		46IT Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 46IT
		46IT Enabled
Op		
	general	46IT Operated
Str		
	general	46IT Pickup

2.1.20 A47PTOV1

Beh		
	stVal	Out of Service
		Inhibit 47-1
		47-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 47-1
		47-1 Enabled
Op		
	general	47-1 Operated
Str		
	dirGeneral	Non-Directional
	general	47-1 Pickup

2.1.21 A47PTOV2

Beh		
	stVal	Out of Service
		Inhibit 47-2
		47-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 47-2
		47-2 Enabled
Op		
	general	47-2 Operated
Str		
	dirGeneral	Non-Directional
	general	47-2 Pickup

2.1.22 A49PTTR1

AlmThm		
	general	49 Thermal Alarm
Beh		
	stVal	Inhibit 49
		49 Enabled
		Protection Active
		Out of Service
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 49
		49 Enabled
Op		
	general	49 Operated
Str		
	dirGeneral	Non-Directional
	general	49 Pickup

2.1.23 A50BfRBRF1

Beh		
	stVal	Inhibit 50BF
		50BF Enabled
		Protection Active
		Out of Service
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50BF
		50BF Enabled
OpEx		
	general	50BF-2
OpIn		
	general	50BF-1
Str		
	dirGeneral	Non-Directional
	general	50BF Pickup

2.1.24 A50gLCPTOC1

Beh		
	stVal	Out of Service
		Inhibit 50G LC-1
		50G LC-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50G LC-1
		50G LC-1 Enabled
Op		
	general	50G LC-1 Operated
Str		
	dirGeneral	Non-Directional
	general	50G LC-1 Pickup

2.1.25 A50gLCPTOC2

Beh		
	stVal	Out of Service
		Inhibit 50G LC-2
		50G LC-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50G LC-2
		50G LC-2 Enabled
Op		
	general	50G LC-2 Operated
Str		
	dirGeneral	Non-Directional
	general	50G LC-2 Pickup

2.1.26 A50gPTOC1

Beh		
	stVal	Out of Service
		Inhibit 50G-1
		50G-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50G-1
		50G-1 Enabled
Op		
	general	50G-1 Operated
Str		
	dirGeneral	50G-1 Dir Pickup
	general	50G-1 Pickup

2.1.27 A50gPTOC2

Beh		
	stVal	Out of Service
		Inhibit 50G-2
		50G-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50G-2
		50G-2 Enabled
Op		
	general	50G-2 Operated
Str		
	dirGeneral	50G-2 Dir Pickup
	general	50G-2 Pickup

2.1.28 A50gPTOC3

Beh		
	stVal	Out of Service
		Inhibit 50G-3
		50G-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50G-3
		50G-3 Enabled
Op		
	general	50G-3 Operated
Str		
	dirGeneral	50G-3 Dir Pickup
	general	50G-3 Pickup

2.1.29 A50gPTOC4

Beh		
	stVal	Out of Service
		Inhibit 50G-4
		50G-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50G-4
		50G-4 Enabled
Op		
	general	50G-4 Operated
Str		
	dirGeneral	50G-4 Dir Pickup
	general	50G-4 Pickup

2.1.30 A50LCPTOC1

Beh		
	stVal	Out of Service
		Inhibit 50 LC-1
		50 LC-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50 LC-1
		50 LC-1 Enabled
Op		
	general	50 LC-1 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	50 LC-1 PhA Pickup
		50 LC-1 PhB Pickup
		50 LC-1 PhC Pickup
	phsA	50 LC-1 PhA Pickup
	phsB	50 LC-1 PhB Pickup
	phsC	50 LC-1 PhC Pickup

2.1.31 A50LCPTOC2

Beh		
	stVal	Out of Service
		Inhibit 50 LC-2
		50 LC-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50 LC-2
		50 LC-2 Enabled
Op		
	general	50 LC-2 Operated
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	50 LC-2 PhA Pickup
		50 LC-2 PhB Pickup
		50 LC-2 PhC Pickup
	phsA	50 LC-2 PhA Pickup
	phsB	50 LC-2 PhB Pickup
	phsC	50 LC-2 PhC Pickup

2.1.32 A50nPTOC1

Beh		
	stVal	Out of Service
		Inhibit 50N-1
		50N-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50N-1
		50N-1 Enabled
Op		
	general	50N-1 Operated
Str		
	dirGeneral	50N-1 Dir Pickup
	general	50N-1 Pickup

2.1.33 A50nPTOC2

Beh		
	stVal	Out of Service
		Inhibit 50N-2
		50N-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50N-2
		50N-2 Enabled
Op		
	general	50N-2 Operated
Str		
	dirGeneral	50N-2 Dir Pickup
	general	50N-2 Pickup

2.1.34 A50nPTOC3

Beh		
	stVal	Out of Service
		Inhibit 50N-3
		50N-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50N-3
		50N-3 Enabled
Op		
	general	50N-3 Operated
Str		
	dirGeneral	50N-3 Dir Pickup
	general	50N-3 Pickup

2.1.35 A50nPTOC4

Beh		
	stVal	Out of Service
		Inhibit 50N-4
		50N-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50N-4
		50N-4 Enabled
Op		
	general	50N-4 Operated
Str		
	dirGeneral	50N-4 Dir Pickup
	general	50N-4 Pickup

2.1.36 A50PTOC1

Beh		
	stVal	Out of Service
		Inhibit 50-1
		50-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50-1
		50-1 Enabled
Op		
	general	50-1 Operated
Str		
	dirGeneral	50-1 PhA Dir Pickup
		50-1 PhB Dir Pickup
		50-1 PhC Dir Pickup
	dirPhsA	50-1 PhA Dir Pickup
	dirPhsB	50-1 PhB Dir Pickup
	dirPhsC	50-1 PhC Dir Pickup
	general	50-1 PhA Pickup
		50-1 PhB Pickup
		50-1 PhC Pickup
	phsA	50-1 PhA Pickup
	phsB	50-1 PhB Pickup
	phsC	50-1 PhC Pickup

2.1.37 A50PTOC2

Beh		
	stVal	Out of Service
		Inhibit 50-2
		50-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50-2
		50-2 Enabled
Op		
	general	50-2 Operated
Str		
	dirGeneral	50-2 PhA Dir Pickup
		50-2 PhB Dir Pickup
		50-2 PhC Dir Pickup
	dirPhsA	50-2 PhA Dir Pickup
	dirPhsB	50-2 PhB Dir Pickup
	dirPhsC	50-2 PhC Dir Pickup
	general	50-2 PhA Pickup
		50-2 PhB Pickup
		50-2 PhC Pickup
	phsA	50-2 PhA Pickup
	phsB	50-2 PhB Pickup
	phsC	50-2 PhC Pickup

2.1.38 A50PTOC3

Beh		
	stVal	Out of Service
		Inhibit 50-3
		50-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50-3
		50-3 Enabled
Op		
	general	50-3 Operated
Str		
	dirGeneral	50-3 PhA Dir Pickup
		50-3 PhB Dir Pickup
		50-3 PhC Dir Pickup
	dirPhsA	50-3 PhA Dir Pickup
	dirPhsB	50-3 PhB Dir Pickup
	dirPhsC	50-3 PhC Dir Pickup
	general	50-3 PhA Pickup
		50-3 PhB Pickup
		50-3 PhC Pickup
	phsA	50-3 PhA Pickup
	phsB	50-3 PhB Pickup
	phsC	50-3 PhC Pickup

2.1.39 A50PTOC4

Beh		
	stVal	Out of Service
		Inhibit 50-4
		50-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50-4
		50-4 Enabled
Op		
	general	50-4 Operated
Str		
	dirGeneral	50-4 PhA Dir Pickup
		50-4 PhB Dir Pickup
		50-4 PhC Dir Pickup
	dirPhsA	50-4 PhA Dir Pickup
	dirPhsB	50-4 PhB Dir Pickup
	dirPhsC	50-4 PhC Dir Pickup
	general	50-4 PhA Pickup
		50-4 PhB Pickup
		50-4 PhC Pickup
	phsA	50-4 PhA Pickup
	phsB	50-4 PhB Pickup
	phsC	50-4 PhC Pickup

2.1.40 A50SefLCPTOC1

Beh		
	stVal	Out of Service
		Inhibit 50SEF LC-1
		50SEF LC-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50SEF LC-1
		50SEF LC-1 Enabled
Op		
	general	50SEF LC-1 Operated
Str		
	dirGeneral	Non-Directional
	general	50SEF LC-1 Pickup

2.1.41 A50SefLCPTOC2

Beh		
	stVal	Out of Service
		Inhibit 50SEF LC-2
		50SEF LC-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50SEF LC-2
		50SEF LC-2 Enabled
Op		
	general	50SEF LC-2 Operated
Str		
	dirGeneral	Non-Directional
	general	50SEF LC-2 Pickup

2.1.42 A50SefPTOC1

Beh		
	stVal	Out of Service
		Inhibit 50SEF-1
		50SEF-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50SEF-1
		50SEF-1 Enabled
Op		
	general	50SEF-1 Operated
Str		
	dirGeneral	50SEF-1 Dir Pickup
	general	50SEF-1 Pickup

2.1.43 A50SefPTOC2

Beh		
	stVal	Out of Service
		Inhibit 50SEF-2
		50SEF-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50SEF-2
		50SEF-2 Enabled
Op		
	general	50SEF-2 Operated
Str		
	dirGeneral	50SEF-2 Dir Pickup
	general	50SEF-2 Pickup

2.1.44 A50SefPTOC3

Beh		
	stVal	Out of Service
		Inhibit 50SEF-3
		50SEF-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50SEF-3
		50SEF-3 Enabled
Op		
	general	50SEF-3 Operated
Str		
	dirGeneral	50SEF-3 Dir Pickup
	general	50SEF-3 Pickup

2.1.45 A50SefPTOC4

Beh		
	stVal	Out of Service
		Inhibit 50SEF-4
		50SEF-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 50SEF-4
		50SEF-4 Enabled
Op		
	general	50SEF-4 Operated
Str		
	dirGeneral	50SEF-4 Dir Pickup
	general	50SEF-4 Pickup

2.1.46 A51gPTOC1

Beh		
	stVal	Out of Service
		Inhibit 51G-1
		51G-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51G-1
		51G-1 Enabled
Op		
	general	51G-1 Operated
Str		
	dirGeneral	51G-1 Dir Pickup
	general	51G-1 Pickup

2.1.47 A51gPTOC2

Beh		
	stVal	Out of Service
		Inhibit 51G-2
		51G-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51G-2
		51G-2 Enabled
Op		
	general	51G-2 Operated
Str		
	dirGeneral	51G-2 Dir Pickup
	general	51G-2 Pickup

2.1.48 A51gPTOC3

Beh		
	stVal	Out of Service
		Inhibit 51G-3
		51G-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51G-3
		51G-3 Enabled
Op		
	general	51G-3 Operated
Str		
	dirGeneral	51G-3 Dir Pickup
	general	51G-3 Pickup

2.1.49 A51gPTOC4

Beh		
	stVal	Out of Service
		Inhibit 51G-4
		51G-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51G-4
		51G-4 Enabled
Op		
	general	51G-4 Operated
Str		
	dirGeneral	51G-4 Dir Pickup
	general	51G-4 Pickup

2.1.50 A51nPTOC1

Beh		
	stVal	Out of Service
		Inhibit 51N-1
		51N-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51N-1
		51N-1 Enabled
Op		
	general	51N-1 Operated
Str		
	dirGeneral	51N-1 Dir Pickup
	general	51N-1 Pickup

2.1.51 A51nPTOC2

Beh		
	stVal	Out of Service
		Inhibit 51N-2
		51N-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51N-2
		51N-2 Enabled
Op		
	general	51N-2 Operated
Str		
	dirGeneral	51N-2 Dir Pickup
	general	51N-2 Pickup

2.1.52 A51nPTOC3

Beh		
	stVal	Out of Service
		Inhibit 51N-3
		51N-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51N-3
		51N-3 Enabled
Op		
	general	51N-3 Operated
Str		
	dirGeneral	51N-3 Dir Pickup
	general	51N-3 Pickup

2.1.53 A51nPTOC4

Beh		
	stVal	Out of Service
		Inhibit 51N-4
		51N-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51N-4
		51N-4 Enabled
Op		
	general	51N-4 Operated
Str		
	dirGeneral	51N-4 Dir Pickup
	general	51N-4 Pickup

2.1.54 A51PTOC1

Beh		
	stVal	Out of Service
		Inhibit 51-1
		51-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51-1
		51-1 Enabled
Op		
	general	51-1 Operated
Str		
	dirGeneral	51-1 PhA Dir Pickup
		51-1 PhB Dir Pickup
		51-1 PhC Dir Pickup
	dirPhsA	51-1 PhA Dir Pickup
	dirPhsB	51-1 PhB Dir Pickup
	dirPhsC	51-1 PhC Dir Pickup
	general	51-1 PhA Pickup
		51-1 PhB Pickup
		51-1 PhC Pickup
	phsA	51-1 PhA Pickup
	phsB	51-1 PhB Pickup
	phsC	51-1 PhC Pickup

2.1.55 A51PTOC2

Beh		
	stVal	Out of Service
		Inhibit 51-2
		51-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51-2
		51-2 Enabled
Op		
	general	51-2 Operated
Str		
	dirGeneral	51-2 PhA Dir Pickup
		51-2 PhB Dir Pickup
		51-2 PhC Dir Pickup
	dirPhsA	51-2 PhA Dir Pickup
	dirPhsB	51-2 PhB Dir Pickup
	dirPhsC	51-2 PhC Dir Pickup
	general	51-2 PhA Pickup
		51-2 PhB Pickup
		51-2 PhC Pickup
	phsA	51-2 PhA Pickup
	phsB	51-2 PhB Pickup
	phsC	51-2 PhC Pickup

2.1.56 A51PTOC3

Beh		
	stVal	Out of Service
		Inhibit 51-3
		51-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51-3
		51-3 Enabled
Op		
	general	51-3 Operated
Str		
	dirGeneral	51-3 PhA Dir Pickup
		51-3 PhB Dir Pickup
		51-3 PhC Dir Pickup
	dirPhsA	51-3 PhA Dir Pickup
	dirPhsB	51-3 PhB Dir Pickup
	dirPhsC	51-3 PhC Dir Pickup
	general	51-3 PhA Pickup
		51-3 PhB Pickup
		51-3 PhC Pickup
	phsA	51-3 PhA Pickup
	phsB	51-3 PhB Pickup
	phsC	51-3 PhC Pickup

2.1.57 A51PTOC4

Beh		
	stVal	Out of Service
		Inhibit 51-4
		51-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51-4
		51-4 Enabled
Op		
	general	51-4 Operated
Str		
	dirGeneral	51-4 PhA Dir Pickup
		51-4 PhB Dir Pickup
		51-4 PhC Dir Pickup
	dirPhsA	51-4 PhA Dir Pickup
	dirPhsB	51-4 PhB Dir Pickup
	dirPhsC	51-4 PhC Dir Pickup
	general	51-4 PhA Pickup
		51-4 PhB Pickup
		51-4 PhC Pickup
	phsA	51-4 PhA Pickup
	phsB	51-4 PhB Pickup
	phsC	51-4 PhC Pickup

2.1.58 A51SefPTOC1

Beh		
	stVal	Out of Service
		Inhibit 51SEF-1
		51SEF-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51SEF-1
		51SEF-1 Enabled
Op		
	general	51SEF-1 Operated
Str		
	dirGeneral	51SEF-1 Dir Pickup
	general	51SEF-1 Pickup

2.1.59 A51SefPTOC2

Beh		
	stVal	Out of Service
		Inhibit 51SEF-2
		51SEF-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51SEF-2
		51SEF-2 Enabled
Op		
	general	51SEF-2 Operated
Str		
	dirGeneral	51SEF-2 Dir Pickup
	general	51SEF-2 Pickup

2.1.60 A51SefPTOC3

Beh		
	stVal	Out of Service
		Inhibit 51SEF-3
		51SEF-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51SEF-3
		51SEF-3 Enabled
Op		
	general	51SEF-3 Operated
Str		
	dirGeneral	51SEF-3 Dir Pickup
	general	51SEF-3 Pickup

2.1.61 A51SefPTOC4

Beh		
	stVal	Out of Service
		Inhibit 51SEF-4
		51SEF-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 51SEF-4
		51SEF-4 Enabled
Op		
	general	51SEF-4 Operated
Str		
	dirGeneral	51SEF-4 Dir Pickup
	general	51SEF-4 Pickup

2.1.62 A59nDtPTOV1

Beh		
	stVal	Out of Service
		Inhibit 59NDT
		59NDT Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 59NDT
		59NDT Enabled
Op		
	general	59NDT Operated
Str		
	dirGeneral	Non-Directional
	general	59NDT Pickup

2.1.63 A59nItPTOV1

Beh		
	stVal	Out of Service
		Inhibit 59NIT
		59NIT Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 59NIT
		59NIT Enabled
Op		
	general	59NIT Operated
Str		
	general	59NIT Pickup

2.1.64 A64hPTOC1

Beh		
	stVal	Out of Service
		Inhibit 64H
		64H Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 64H
		64H Enabled
Op		
	general	64H Operated
Str		
	dirGeneral	Non-Directional
	general	64H Pickup

2.1.65 A81Hb2PHAR1

Beh		
	stVal	Out of Service
		Inhibit 81HBL2
		81HBL2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81HBL2
		81HBL2 Enabled
Str		
	dirGeneral	Non-Directional
	dirPhsA	Non-Directional
	dirPhsB	Non-Directional
	dirPhsC	Non-Directional
	general	81HBL2 PhA Pickup
		81HBL2 PhB Pickup
		81HBL2 PhC Pickup
	phsA	81HBL2 PhA Pickup
	phsB	81HBL2 PhB Pickup
	phsC	81HBL2 PhC Pickup

2.1.66 A81PTOF1

Beh		
	stVal	Out of Service
		Inhibit 81-1
		81-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-1
		81-1 Enabled
Op		
	general	81-1 Operated
Str		
	dirGeneral	Non-Directional
	general	81-1 Pickup

2.1.67 A81PTOF2

Beh		
	stVal	Out of Service
		Inhibit 81-2
		81-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-2
		81-2 Enabled
Op		
	general	81-2 Operated
Str		
	dirGeneral	Non-Directional
	general	81-2 Pickup

2.1.68 A81PTOF3

Beh		
	stVal	Out of Service
		Inhibit 81-3
		81-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-3
		81-3 Enabled
Op		
	general	81-3 Operated
Str		
	dirGeneral	Non-Directional
	general	81-3 Pickup

2.1.69 A81PTOF4

Beh		
	stVal	Out of Service
		Inhibit 81-4
		81-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-4
		81-4 Enabled
Op		
	general	81-4 Operated
Str		
	dirGeneral	Non-Directional
	general	81-4 Pickup

2.1.70 A81PTOF5

Beh		
	stVal	Out of Service
		Inhibit 81-5
		81-5 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-5
		81-5 Enabled
Op		
	general	81-5 Operated
Str		
	dirGeneral	Non-Directional
	general	81-5 Pickup

2.1.71 A81PTOF6

Beh		
	stVal	Out of Service
		Inhibit 81-6
		81-6 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-6
		81-6 Enabled
Op		
	general	81-6 Operated
Str		
	dirGeneral	Non-Directional
	general	81-6 Pickup

2.1.72 A81PTUF1

Beh		
	stVal	Out of Service
		Inhibit 81-1
		81-1 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-1
		81-1 Enabled
Op		
	general	81-1 Operated
Str		
	dirGeneral	Non-Directional
	general	81-1 Pickup

2.1.73 A81PTUF2

Beh		
	stVal	Out of Service
		Inhibit 81-2
		81-2 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-2
		81-2 Enabled
Op		
	general	81-2 Operated
Str		
	dirGeneral	Non-Directional
	general	81-2 Pickup

2.1.74 A81PTUF3

Beh		
	stVal	Out of Service
		Inhibit 81-3
		81-3 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-3
		81-3 Enabled
Op		
	general	81-3 Operated
Str		
	dirGeneral	Non-Directional
	general	81-3 Pickup

2.1.75 A81PTUF4

Beh		
	stVal	Out of Service
		Inhibit 81-4
		81-4 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-4
		81-4 Enabled
Op		
	general	81-4 Operated
Str		
	dirGeneral	Non-Directional
	general	81-4 Pickup

2.1.76 A81PTUF5

Beh		
	stVal	Out of Service
		Inhibit 81-5
		81-5 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-5
		81-5 Enabled
Op		
	general	81-5 Operated
Str		
	dirGeneral	Non-Directional
	general	81-5 Pickup

2.1.77 A81PTUF6

Beh		
	stVal	Out of Service
		Inhibit 81-6
		81-6 Enabled
Health		
	stVal	Protection Healthy
Mod		
	stVal	Inhibit 81-6
		81-6 Enabled
Op		
	general	81-6 Operated
Str		
	dirGeneral	Non-Directional
	general	81-6 Pickup

2.1.78 LLNO

Beh		
	stVal	Protection Active
		Out of Service
Health		
	stVal	Protection Healthy
Mod		
	stVal	Protection Active
		Out of Service
NamPIt		
	swRev	Software Revision
	vendor	Vendor Name
SGCB		
	ActSG	Active Setting Group 1
		Active Setting Group 2
		Active Setting Group 3
		Active Setting Group 4
	LActTm	Active Setting Group 1
		Active Setting Group 2
		Active Setting Group 3
		Active Setting Group 4
	NumOfSG	Number of 61850 Controllable Setting Groups

2.1.79 PTRC1

Beh		
	stVal	Protection Active
		Out of Service
Health		
	stVal	Protection Healthy
Mod		
	stVal	Protection Active
Op		
	general	General Operate
OpCntRs		
	Oper.ctlVal	Set CB Trip Count
	stVal	CB Trip Count
Str		
	dirGeneral	General Pickup
		General Pickup & Fwd Direction
		General Pickup & Rev Direction
	general	General Pickup
Tr		
	general	CB Trip

2.2 MEAS

2.2.1 I_MSQ11

Beh		
	stVal	Out of Service
Health		
	stVal	Protection Healthy
SeqA		
	c1.cVal.mag.f	Sequence Components I Seq PPS
	c1.instCVal.mag.f	Sequence Components I Seq PPS
	c1.units.multiplier	Sequence Components I Seq PPS
	c1.units.SIUnit	Sequence Components I Seq PPS
	c2.cVal.mag.f	Sequence Components I Seq NPS
	c2.instCVal.mag.f	Sequence Components I Seq NPS
	c2.units.multiplier	Sequence Components I Seq NPS
	c2.units.SIUnit	Sequence Components I Seq NPS
	c3.cVal.mag.f	Sequence Components I Seq ZPS
	c3.instCVal.mag.f	Sequence Components I Seq ZPS
	c3.units.multiplier	Sequence Components I Seq ZPS
	c3.units.SIUnit	Sequence Components I Seq ZPS

2.2.2 LLNO

Beh		
	stVal	Protection Healthy
		Out of Service
Health		
	stVal	Protection Healthy
Mod		
	stVal	Protection Healthy
		Out of Service
NamPlt		
	swRev	Software Revision
	vendor	Vendor Name

2.2.3 V_MSQI1

Beh		
	stVal	Out of Service
Health		
	stVal	Protection Healthy
SeqV		
	c1.cVal.mag.f	Sequence Components V Seq PPS
	c1.instCVal.mag.f	Sequence Components V Seq PPS
	c1.units.multiplier	Sequence Components V Seq PPS
	c1.units.SIUnit	Sequence Components V Seq PPS
	c2.cVal.mag.f	Sequence Components V Seq NPS
	c2.instCVal.mag.f	Sequence Components V Seq NPS
	c2.units.multiplier	Sequence Components V Seq NPS
	c2.units.SIUnit	Sequence Components V Seq NPS
	c3.cVal.mag.f	Sequence Components V Seq ZPS
	c3.instCVal.mag.f	Sequence Components V Seq ZPS
	c3.units.multiplier	Sequence Components V Seq ZPS
	c3.units.SIUnit	Sequence Components V Seq ZPS

2.3 DR

2.3.1 LLNO

Beh		
	stVal	Protection Healthy
		Out of Service
Health		
	stVal	Protection Healthy
Mod		
	stVal	Protection Healthy
		Out of Service
NamPlt		
	swRev	Software Revision
	vendor	Vendor Name

2.3.2 RDRE1

Beh		
	stVal	Protection Healthy
		Out of Service
FltNum		
	stVal	Fault Number
GriFltNum		
	stVal	Grid Fault Number
Health		
	stVal	Protection Healthy
Mod		
	stVal	Protection Healthy
RcdMade		
	stVal	Recording Made

2.4 CTRL

2.4.1 BI13GGIO1

Beh		
	stVal	Out of Service
Health		
	stVal	Protection Healthy
Ind1		
	stVal	1
Ind10		
	stVal	10
Ind11		
	stVal	11
Ind12		
	stVal	12
Ind13		
	stVal	13
Ind2		
	stVal	2
Ind3		
	stVal	3
Ind4		
	stVal	4
Ind5		
	stVal	5
Ind6		
	stVal	6
Ind7		
	stVal	7
Ind8		
	stVal	8
Ind9		
	stVal	9