



# IEC 61850 Certificate Level A<sup>1</sup>

Page 1/2

No. 3082035-Consulting 09-1118

Issued to:  
Siemens A.G., PTD EA  
Protection and Substation Control Systems  
Wernerwerkdammm 5  
D-13623 Berlin  
Germany

For the product:  
Siprotec V4  
7UT612 Differential protection  
Firmware V04.60  
EN100 V04.03



The product has not shown to be non-conforming to:  
**IEC 61850-6, 7-1, 7-2, 7-3, 7-4 and 8-1**  
Communication networks and systems in substations

The conformance test has been performed according to IEC 61850-10 with product's protocol, model and technical issue implementation conformance statements: "SIPROTEC 4 Ethernet Module EN100 IEC 61850 Electrical / Optical Interface 100 MBit Manual, Edition May 2007, C53000-G1100-C167-7", "MICS, Mapping family 7UT613\_63, Mappingversion 1 Revision 5" and product's extra information for testing: "SIPROTEC Differential Protection 7UT6x V4.6 IEC 61850 PIXIT, C53000-G1176-C184-4"

The following IEC 61850 conformance blocks have been tested with a positive result (number of relevant and executed test cases / total number of test cases as defined in the UCA International Users Group Device Test procedures v2.2):

1 Basic Exchange (19/24)	9a GOOSE Publish (7/12)
2+ Data Set Definition (26/29)	9b GOOSE Subscribe (9/10)
4 Setting Group Selection (2/3)	12a Direct Control (5/12)
5 Unbuffered Reporting (16/18)	12c Enhanced Direct Control (4/13)
6 Buffered Reporting (17/20)	12d Enhanced SBO Control (12/20)
6+ Enhanced buffered reporting (12/12)	13 Time Synchronization (3/5)
	14 File Transfer (4/7)

This Certificate includes a summary of the test results as carried out at Berlin in Germany with UniCASim 61850 version 3.18 with test suite 3.18.01 and UniCA 61850 analyzer 4.18. The test is based on the UCA International Users Group Device Test Procedures version 2.2. This document has been issued for information purposes only, and the original paper copy of the KEMA report: No. 3082035-Consulting 09-1117 will prevail.

The test has been carried out on one single specimen of the products as referred above and submitted to KEMA by Siemens. The manufacturer's production process has not been assessed. This Certificate does not imply that KEMA has certified or approved any product other than the specimen tested.

Arnhem, June 5, 2009

W. Strassburg  
Manager intelligent Networks and Communication

R. Schimmel  
Certification Manager

1 Level A - Independent Test lab with certified ISO 9000 or ISO 17025 Quality System

Copyright © KEMA Nederland B.V., Arnhem, the Netherlands. All rights reserved. Please note that any electronic version of this KEMA certificate is provided to KEMA's customer for convenience purposes only. It is prohibited to update or change it in any manner whatsoever, including but not limited to dividing it into parts. In case of a conflict between the electronic version and the original version, the original paper version issued by KEMA will prevail.



Applicable Test Procedures from the UCA International Users Group Device Test Procedures version 2.2

Conformance Block	Mandatory	Conditional
1: Basic Exchange	Ass1, Ass2, Ass3, AssN2, AssN3, AssN4, AssN5  Srv1, Srv2, Srv3, Srv4, Srv5, SrvN1abcd, SrvN4	Srv6, Srv7, Srv8, SrvN1e, SrvN3
2: Data Sets	Dset1, Dset10a, DsetN1ae	
2+: Data Set Definition	Dset2, Dset3, Dset4, Dset5, Dset6, Dset7, Dset8, Dset9, DsetN1cd, DsetN2, DsetN3, DsetN4, DsetN5, DsetN6, DsetN7, DsetN8, DsetN9, DsetN10, DsetN11, DsetN12, DsetN13, DsetN14, DsetN15	
4: Setting Group Selection	Sg1, SgN1a	
5: Unbuffered Reporting	Rp1, Rp2, Rp3, Rp4, Rp7, Rp10 RpN1, RpN2, RpN3, RpN4	Rp5, Rp6, Rp8, Rp9, Rp11 RpN5
6: Buffered Reporting	Br1, Br2, Br3, Br4, Br7, Br8, Br9, Br12 BrN1, BrN2, BrN3, BrN4, BrN5	Br5, Br10, Br11, Br13
6+: Enhanced buffered reporting (tissue #453)	BrE1, BrE2, BrE3, BrE6, BrE7, BrE8, BrE9, BrE10, BrE11	BrE4, BrE5, BrE12
9a: GOOSE publish	Gop2, Gop3, Gop4, Gop7, Gop9	Gop1, GopN1
9b: GOOSE subscribe	Gos1, Gos2, Gos3, GosN1, GosN2, GosN3, GosN4, GosN5, GosN6	
12a: Direct control	CltN3, CltN8 DOns1, DOns3	Ctl2
12c: Enhanced Direct Control	CltN3, CltN8 DOes2, DOes5	
12d: Enhanced SBO control	Ctl3, CtlN1, CtlN2, CtlN3, CtlN4, CtlN9 SBOes1, SBOes2, SBOes3	Ctl2, Ctl7, CtlN11
13: Time sync	Tm1, Tm2, TmN1	
14: File transfer	Ft1, Ft2ab, FtN1ab	Ft4