

# SIEMENS

Ingenuity for life

## SIPROTEC 7UT87

Transformer Differential Protection

[www.siemens.com/siprotec](http://www.siemens.com/siprotec)

### Description

The SIPROTEC 7UT87 transformer differential protection has been designed specifically for the protection of multi-winding transformers (up to 5 sides). Furthermore, it is to be used where numerous measuring points (up to 9 3-phase current measuring points) are required. Another application is simultaneous protection of two parallel transformers (additional fast backup protection). The SIPROTEC 7UT87 is the main protection for the transformer and contains many other protection and monitoring functions. The additional protection functions can also be used as backup protection for subsequent protected objects (such as cables or lines). With its modular structure, flexibility and the powerful DIGSI 5 engineering tool, SIPROTEC 7UT87 offers future-oriented system solutions with high investment security and low operating costs.

Main function	Up to 3 differential protection functions with additional stabilization (in different transformer function groups); up to 5 ground fault differential protection functions.
---------------	---

For auto transformer applications, two differential protection functions can be processed in an auto transformer function group.

Usable measuring points	9 x 3-phase current measuring points, 5 x 1-phase current measuring points, 5 x 3-phase voltage measuring points
-------------------------	--

Inputs and outputs	2 predefined standard variants with 20 current transformers, 4 voltage transformers, 15 to 27 binary inputs, 22 to 38 binary outputs
--------------------	---

Hardware flexibility	Flexibly adjustable and expandable I/O quantity structure within the scope of the SIPROTEC 5 modular system.
----------------------	--

Housing width	2/3 x 19" - 2/1 x 19"
---------------	-----------------------



SIPROTEC 7UT87

### Applications

The SIPROTEC 7UT87 is intended for special applications (up to 5 sides and 7 measuring points), therefore, you must create your own application template depending on the application and store it in the device. To make work easier, you can use an available template and modify it.

### Functions

DIGSI 5 permits all functions to be configured and combined as required.

- In SIPROTEC 7UT87, two transformer function groups can be used.
- Transformer differential protection for multi-winding transformers with versatile, additional protection functions (multiwinding transformers are typical in power converter applications (such as HVDC))
- Transformer differential protection for phase-angle regulating transformers of the single core and two core types, and special transformers

# Modular and flexible

- Transformer protection applications with up to seven three-phase current measuring points
- Simultaneous differential protection for 2 transformers (such as two 2-winding transformers)
- Universal usability of the permissible measuring points
- Applicable from average up to extra-high voltage
- Protection of standard power transformers, auto transformers and motors
- Typical properties of a transformer differential protection such as flexible adaptation to the transformer vector group, control of inrush and overexcitation processes, safe behavior in case of current-transformer saturation with different degrees of saturation
- Arc protection
- Voltage controller function ANSI 90V for two-winding transformers, three-winding transformers and grid coupling transformers with parallel control (master/follower, circulating reactive current minimization)
- Adaptive adaptation of the operate curve to the transformer tap position
- Increased sensitivity with near-neutral-point ground faults through a separate restricted ground-fault protection
- Additional current and voltage inputs can be supplements for standard protection functions, such as overcurrent, voltage frequency, etc.
- Graphical logic editor to create powerful automation functions in the device
- Up to 4 pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Reliable data transmission via PRP and HSR redundancy protocols
- Extensive cyber security functionality, such as role-based access control (RBAC), protocolling security-related events or signed firmware
- Simple, quick and secure access to device data via a standard Web browser - without additional software
- Frequency tracked protection functions over a wide frequency range (10 Hz to 80 Hz) and the option to assign the protection functions in a single device to different frequency tracking groups .
- Phasor measurement unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Powerful fault recording (buffer for a max. record time of 80 sec. at 8 kHz or 320 sec. at 2 kHz)
- Auxiliary functions for simple tests and commissioning
- Flexibly adjustable I/O quantity structure within the scope of the SIPROTEC 5 modular system

## Benefits

- Safe and reliable automation and control of your systems
- Cyber security in accordance with NERC CIP and BDEW Whitepaper requirements
- Highest availability even under extreme environmental conditions by “conformal coating” of electronic boards
- Powerful communication components warrant safe and effective solutions



## Siemens AG

Energy Management Division  
Freyeslebenstraße 1  
91058 Erlangen, Germany

SIPROTEC 7UT87 Profile E7.8.docx  
Printed in Germany | © 09.18 Siemens AG

E-Mail: [support.energy@siemens.com](mailto:support.energy@siemens.com)  
Tel: +49 180 524 70 00

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit ([www.openssl.org](http://www.openssl.org)), cryptographic software written by Eric Young ([eay@cryptsoft.com](mailto:eay@cryptsoft.com)) and software developed by Bodo Moeller.