

SIEMENS

Ingenuity for life

SIPROTEC 7SJ82

Feeder and overcurrent protection

www.siemens.com/siprotec

Description

The SIPROTEC 7SJ82 overcurrent protection has specifically been designed for a cost-effective and compact protection of feeders and lines in medium-voltage and high-voltage systems. With its flexibility and the powerful DIGSI 5 engineering tool, SIPROTEC 7SJ82 offers future-oriented system solutions with high investment security and low operating costs.

Main function	Feeder and overcurrent protection for all voltage levels
Inputs and outputs	4 current transformers, 4 voltage transformers (optional), 11 or 23 binary inputs, 9 or 16 binary outputs, or 8 current transformers, 7 binary inputs, 7 binary outputs
Hardware flexibility	Different hardware quantity structures for binary inputs and outputs are available in the 1/3 base module. Adding 1/6 expansion modules is not possible; available with large or small display.
Housing width	1/3 × 19"

Applications

- Detection and selective 3-pole tripping of short circuits in electrical equipment of star networks, lines with infeed at one or two ends, parallel lines and open or closed ring systems of all voltage levels
- Detection of ground faults in isolated or arc-suppression-coil-ground power systems in star, ring, or meshed arrangement
- Backup protection for differential protection devices of all kind for lines, transformers, generators, motors, and busbars



Feeder and overcurrent protection SIPROTEC 7SJ82

- Protection and monitoring of simple capacitor banks
- Phasor Measurement Unit (PMU)
- Reverse-power protection
- Load shedding applications
- Automatic switchover

Functions

DIGSI 5 permits all functions to be configured and combined as required.

- Directional and non-directional overcurrent protection with additional functions
- Optimized tripping times due to directional comparison and protection data communication
- Detection of static, intermittent and transient ground faults (fleeting contact function) in arc-suppression-coil-ground and isolated power systems

Compact and flexible

- Arc protection
- Overvoltage and undervoltage protection
- Frequency protection and frequency change protection for load shedding applications
- Power protection, configurable as active or reactive power protection
- Protection functions for capacitor banks, such as over-current, overload, current unbalance, peak overvoltage, or differential protection
- Reactive power-undervoltage protection (QU protection)
- Control, synchrocheck and switchgear interlocking protection, circuit-breaker failure protection
- Circuit-breaker failure protection
- Circuit-breaker reignition monitoring
- Graphical logic editor to create powerful automation functions in the device
- Recognition of current and voltage signals up to the 50th harmonic with high accuracy for selected protection functions (such as peak overvoltage protection for capacitors) and operational measured values
- Single line representation in small or large display
- Integrated electrical Ethernet RJ45 for DIGSI 5 and IEC 61850 (reporting and GOOSE)
- Two optional pluggable communication modules, usable for different and redundant protocols (IEC 61850, IEC 60870-5-103, IEC 60870-5-104, Modbus TCP, DNP3 serial and TCP, PROFINET IO)
- Serial protection data communication via optical fibers, two-wire connections and communication networks (IEEE C37.94, and others), including automatic switchover between ring and chain topology.
- Redundancy protocols PRP and HSR
- Cyber security in accordance with NERC CIP and BDWE Whitepaper requirements
- Whitepaper Phasor Measurement Unit (PMU) for synchrophasor measured values and IEEE C37.118 protocol
- Time synchronization with IEEE 1588
- Powerful fault recording (buffer for a max. record time of 80 s at 8 kHz or 320 s at 2 kHz)
- Auxiliary functions for easy tests and commissioning

Benefits

- Compact and low-cost overcurrent protection
- Safety due to powerful protection functions
- Data security and transparency over the entire lifecycle of the plant save time and money
- Purposeful and easy handling of devices and software thanks to a user-friendly design
- Increased reliability and quality of the engineering process
- Consistent implementation of high safety and security mechanisms
- Powerful communication components ensure safe and effective solutions
- Full compatibility between IEC 61850 Editions 1 and 2
- High investment security and low operating costs due to future-oriented system solution



Siemens AG 2016
Energy Management Division
Freyeslebenstraße 1
91058 Erlangen, Germany

SIPROTEC 7SJ82 V7 Profile.docx
Printed in Germany | © 07.16 Siemens AG

E-Mail: support.energy@siemens.com
Tel: +49 180 524 70 00

For all products using security features of OpenSSL, the following shall apply:

This product includes software developed by the OpenSSL Project for use in the OpenSSL Toolkit (www.openssl.org) and cryptographic software written by Eric Young (eay@cryptsoft.com).