



Selection & Application Guide

BFT Main Feed Thru Modules

Power Mod[™]

usa.siemens.com/powermod

Power Mod[™] BFT - Main Feed Thru Modules

Ray, Sarr, Harrish Sarr, Harrish Sarrish Sarish Sarrish Sarrish Sarrish Sarrish Sarrish Sarrish Sarri

2



	•.
Configuration Graphic	05
Another Way to Use BFT	06
Schematic and Order Numbers	07
Features	08
Lug Kits	09
BFT Cut Sheets	10-19

Power Mod[™] BFT - Main Feed Thru Modules

The BFT is a main breaker module for the Power Mod group metering line up that has the ability to isolate power to side-mounted modules just like any other Power Mod main breaker module, but also contains feed-through lugs that can be used to supply and isolate power vertically to downstream group metering line ups. This is a revolutionary product in cabled riser applications.

Features include:


- QuickSystem[™] features
- Incoming & Outgoing Power Mod thru bus
- Standard compression lug capability
- 65K AIC standard, 100K AIC available for all models
- Main breaker with broad ampacity ratings from 1200A to 2000A
- Field installable shunt trip

Quick Reference


- 1200 2000A main bus rating
- 1200A Horizontal bus rating
- UL Standard #67
- UL file #E27100
- AIC rating (65K & 100K)
- Voltage: 240V AC max
- Available in single and three phase
- NEMA 1 (Indoor)
- G90 Galvanized Steel
- ANSI 61 Paint
- Bottom feed only
- All units come with no hubs
- EUSERC drawing number 347 (EUSERC applies to 1200A unit only)



Imagine a four-story building designed with a group metering line up on each floor. If the total load is between 1,200 and 2,000 amps, one BFT module can be placed on the first floor as the main for the first floor's meters and the service entrance main for the entire building using feed-through tapboxes on the second and third floors and a standard breaker main or WTB tapbox on the fourth floor.




Another way to use the BFT




The BFT can be used to get around an obstruction such as a doorway, fire safety equipment, etc. The Main Feed Thru is grounded for service entrance applications from the factory but the bond can be removed for non-SER applications.

Schematic for BFT31200B

FEED-THRU



- Connects via lugs and service entrance rated.
- Lug kits not included. Lug kits must be ordered separately per module.




1-Phase, 3 Wire SN, 240V AC Max.							
Catalog Number	Catalog Number	Breaker Amperage	Breaker Type	Breaker Type	Dimensions (inches)		
(65K AIC)	(100K AIC)	Rating	(65K AIC)	(100K AIC)	Height	Width	Depth
BFT11200B	BFT11200BU	1200	PXD6	HPXD6	89.78	35.53	15.05
BFT11400B	BFT11400BU	1400	PXD6	HPXD6	89.78	35.53	15.05
BFT11600B	BFT11600BU	1600	PXD6	HPXD6	89.78	35.53	15.05
BFT11800B	BFT11800BU	1800	RXD6	HRXD6	89.78	35.53	15.05
BFT12000B	BFT12000BU	2000	RXD6	HRXD6	89.78	35.53	15.05

3-Phase, 4 Wire SN, 240V AC Max.

					Dimensions (inches)		
Catalog Number (65K AIC)	Catalog Number (100K AIC)	Breaker Amperage Rating	Breaker Type (65K AIC)	Breaker Type (100K AIC)	Height	Width	Depth
BFT31200B	BFT31200BU	1200	PXD6	HPXD6	89.78	35.53	15.05
BFT31400B	BFT31400BU	1400	PXD6	HPXD6	89.78	35.53	15.05
BFT31600B	BFT31600BU	1600	PXD6	HPXD6	89.78	35.53	15.05
BFT31800B	BFT31800BU	1800	RXD6	HRXD6	89.78	35.53	15.05
BFT32000B	BFT32000BU	2000	RXD6	HRXD6	89.78	35.53	15.05

BFT Main Feed Thru Modules Features




BFT Main Feed Thru Modules Lug Kits


		Lug kits to use with the BFT						
		1 Phase	3 Phase	No. Wires/ Phase	Max CU wire size (KCMIL)	Max AL wire size (KCMIL)		
	0	LK14500N2E	LK34500N2E	4	600	600		
	1200-2000	LK15600N2	LK35600N2	5	600	600		
	200	LK13750N2E	LK33750N2E	3	750	800		
B	es 1	LK15750N2	LK35750N2	5	750	750		
	rages	LK16750N2	LK36750N2	6	750	750		
	Amper	LK18500N2CD	LK38500N2CD	8	500	750		
	◄	LK18750N2AD	LK38750N2AD	8	500	750		


These wire sizes are recommended based on wire size allowed by the lug size as well as wire bending space requirements of the enclosure.


		Lug Kit Contents					
		Wire Range: 1/0-750 kcmil	Wire Range: #2-600 kcmil	Wire Range: 300-800 kcmil	Downward Bus Entension		
		Wire Binding Screw Torque: 500 lbin.					
Lug Kit Catalog Number	Wire Range	Lug Qty.	Lug Qty.	Lug Qty.	Lug Qty.		
LK14500N2E	1/0-500 kcmil	3	6	-	-		
LK34500N2E	1/0-500 kcmil	4	8	-	-		
LK15600N2	1/0-500 kcmil	6	3	-	-		
LK35600N2	1/0-500 kcmil	8	4	-	-		
LK13750N2E	300-750 kcmil	-	-	9	-		
LK33750N2E	300-750 kcmil	-	-	12	-		
LK15750N2	300-750 kcmil	6	-	3	-		
LK35750N2	300-750 kcmil	8	-	4	-		
LK16750N2	1/0-750 kcmil	9	-	-	-		
LK36750N2	1/0-750 kcmil	12	-	-	-		
LK18500N2CD	1/0-500 kcmil CU	12	-	-	3		
LK38500N2CD	1/0-500 kcmil CU	16	-	-	4		
LK18570N2AD	1/0-500 kcmil AL	12	-	-	3		
LK38570N2AD	1/0-500 kcmil AL	16	-	-	4		




Indoor, 1 Phase, Main Feed-Thru, UG, 1400A Breaker
























Indoor, 3 Phase, Main Feed-Thru, UG, 2000A Breaker



Published by Siemens 2017

Siemens Industry, Inc. 5400 Triangle Parkway Norcross, GA 30092

1-800-241-4453 info.us@siemens.com

Order No. RPBR-BFTSA-1017

usa.siemens.com/powermod Printed in USA All Rights Reserved © 2017, Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.