

**IEC 60870-5-104**  
**Configuration/Interoperability**  
**Guide for**  
**SICAM MMU 7KG9663**

DOCUMENT VERSION V2.00  
APRIL, 2013

---

E50417-C1076-C514-A2

© Siemens AG

# REVISION HISTORY

**Document Version:** V1.00  
**Date:** May, 2012

- First revision.

---

**Document Version:** V2.00  
**Date:** April, 2013

- Transmission of Integrated Totals added (ASDUs 15 and 37; spontaneous transmission and with counter interrogation; counter reset)
- Redundant connection added (one redundancy group with two connections)
- C\_IC\_NA\_1 support added in the "Cause of transmission" table
- Station Interrogation of Group 1 to Group 7 supported
- No Deactivation for ASDU 45 on page 9
- Marking for COT 21-36 for Group interrogation added on page 8
- Reset of counters with a separate Single Command added on page 13

---

# TABLE OF CONTENTS

INTRODUCTION .....	1
<b>1. INTEROPERABILITY .....</b>	<b>2</b>
1.1 System or device .....	2
1.2 Network configuration.....	2
1.3 Physical layer .....	3
1.4 Link layer.....	3
1.5 Application layer .....	4
1.6 Basic application functions.....	11

# INTRODUCTION

The purpose of this document is to describe the specific implementation of the IEC 60870-5-104 protocol within the device SENTRON T 7KG9661.

This document and the documents listed below provide complete information on how to communicate with SENTRON T 7KG9661 via the IEC 60870-5-104 protocol.

- IEC 60870-5-104 = Companion standard for IEC 60870-5-101 over TCP/IP
- IEC 60870-5-101 = Companion standard for basic telecontrol tasks
- IEC 60870-5-101 A2 = Addendum 2 for IEC 60870-5-101
- IEC 60870-5-5 = Basic Application Functions
- IEC 60870-5-4 = Definition and Coding of Application Information Elements
- IEC 60870-5-3 = General Structure of Application Data

## 1. Interoperability

This companion standard presents sets of parameters and alternatives from which subsets must be selected to implement particular telecontrol systems. Certain parameter values, such as the choice of “structured” or “unstructured” fields of the INFORMATION OBJECT ADDRESS of ASDUs represent mutually exclusive alternatives. This means that only one value of the defined parameters is admitted per system. Other parameters, such as the listed set of different process information in command and in monitor direction allow the specification of the complete set or subsets, as appropriate for given applications. This clause summarizes the parameters of the previous clauses to facilitate a suitable selection for a specific application. If a system is composed of equipment stemming from different manufacturers, it is necessary that all partners agree on the selected parameters.

The interoperability list is defined as in IEC 60870-5-101 and extended with parameters used in this standard. The text descriptions of parameters which are not applicable to this companion standard are strike-through (corresponding check box is marked black).

Note:- In addition, the full specification of a system may require individual selection of certain parameters for certain parts of the system, such as the individual selection of scaling factors for individually addressable measured values.

The selected parameters should be marked in the white boxes as follows:

- Function or ASDU is not used
- Function or ASDU is used as standardized (default)
- Function or ASDU is used in reverse mode
- Function or ASDU is used in standard and reverse mode

The possible selection (blank, X, R, or B) is specified for each specific clause or parameter.

A black check box indicates that the option cannot be selected in this companion standard.

### 1.1 System or device

(system-specific parameter, indicate the station's function by marking one of the following with 'X')

- System definition
- Controlling station definition (Master)
- Controlled station definition (Slave)

### 1.2 Network configuration

(network-specific parameter, all configurations that are used are to be marked 'X')

- |  |  |
|--|--|
| <input checked="" type="checkbox"/> <del>Point-to-point</del>          | <input checked="" type="checkbox"/> <del>Multipoint</del>      |
| <input checked="" type="checkbox"/> <del>Multiple point-to-point</del> | <input checked="" type="checkbox"/> <del>Multipoint star</del> |

### 1.3 Physical layer

(network-specific parameter, all interfaces and data rates that are used are to be marked 'X')

#### Transmission speed (control direction)

Unbalanced interchange Circuit V.24/V.28 Standard	Unbalanced interchange Circuit V.24/V.28 Recommended if >1 200bit/s	Balanced interchange Circuit X.24/X.27	
<input type="checkbox"/> 100 bit/s	<input type="checkbox"/> 2 400 bit/s	<input type="checkbox"/> 2 400 bit/s	<input type="checkbox"/> 56 000 bit/s
<input type="checkbox"/> 200 bit/s	<input type="checkbox"/> 4 800 bit/s	<input type="checkbox"/> 4 800 bit/s	<input type="checkbox"/> 64 000 bit/s
<input type="checkbox"/> 300 bit/s	<input type="checkbox"/> 9 600 bit/s	<input type="checkbox"/> 9 600 bit/s	
<input type="checkbox"/> 600 bit/s		<input type="checkbox"/> 19 200 bit/s	
<input type="checkbox"/> 1 200 bit/s		<input type="checkbox"/> 38 400 bit/s	

#### Transmission speed (monitor direction)

Unbalanced interchange Circuit V.24/V.28 Standard	Unbalanced interchange Circuit V.24/V.28 Recommended if >1 200bit/s	Balanced interchange Circuit X.24/X.27	
<input type="checkbox"/> 100 bit/s	<input type="checkbox"/> 2 400 bit/s	<input type="checkbox"/> 2 400 bit/s	<input type="checkbox"/> 56 000 bit/s
<input type="checkbox"/> 200 bit/s	<input type="checkbox"/> 4 800 bit/s	<input type="checkbox"/> 4 800 bit/s	<input type="checkbox"/> 64 000 bit/s
<input type="checkbox"/> 300 bit/s	<input type="checkbox"/> 9 600 bit/s	<input type="checkbox"/> 9 600 bit/s	
<input type="checkbox"/> 600 bit/s		<input type="checkbox"/> 19 200 bit/s	
<input type="checkbox"/> 1 200 bit/s		<input type="checkbox"/> 38 400 bit/s	

### 1.4 Link layer

(network-specific parameter, all options that are used are to be marked 'X'. Specify the maximum frame length. If a non-standard assignment of class 2 messages is implemented for unbalanced transmission, indicate the Type ID and COT of all messages assigned to class 2.)

~~Frame format FT 1.2, single character 1 and the fixed time out interval are used exclusively in this companion standard.~~

#### Link transmission procedure

~~Balanced transmission~~

#### Address field of the link

~~not present (balanced transmission only)~~

Unbalanced transmission

One octet

Frame length

Two octets

Structured

Maximum length L  
(number of octets)

Unstructured

When using an unbalanced link layer, the following ASDU types are returned in class 2 messages (low priority) with the indicated causes of transmission:

The standard assignment of ASDUs to class 2 messages is used as follows:

Type identification	Cause of transmission
9, 11, 13, 21	<1>

A special assignment of ASDUs to class 2 messages is used as follows:

Type identification	Cause of transmission

Note: (In response to a class 2 poll, a controlled station may respond with class 1 data when there is no class 2 data available).

## 1.5 Application layer

### Transmission mode for application data

Mode 1 (Least significant octet first), as defined in clause 4.10 of IEC 60870-5-4, is used exclusively in this companion standard.

### Common address of ASDU

(system-specific parameter, all configurations that are used are to be marked 'X')

One octet

Two octets

### Information object address

(system-specific parameter, all configurations that are used are to be marked 'X')

One octet

Structured

Two octets

Unstructure

Three octets

### Cause of transmission

(system-specific parameter, all configurations that are used are to be marked 'X')

One octet

Two octets (with originator address)  
Originator address is set to zero if not used

## Length of APDU

(system-specific parameter, specify the maximum length of the APDU per system)

The maximum length of APDU for both directions is 253. It is a fixed system parameter.

<input type="checkbox"/>	Maximum length of APDU per system in control direction
<input type="checkbox"/>	Maximum length of APDU per system in monitor direction

## Selection of standard ASDUs

### Process information in monitor direction

(station-specific parameter, mark each Type ID 'X' if it is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

<input checked="" type="checkbox"/>	<1> := Single-point information	M_SP_NA_1
<input type="checkbox"/>	<del>&lt;2&gt; := Single-point information with time tag</del>	<del>M_SP_TA_1</del>
<input type="checkbox"/>	<3> := Double-point information	M_DP_NA_1
<input type="checkbox"/>	<del>&lt;4&gt; := Double-point information with time tag</del>	<del>M_DP_TA_1</del>
<input type="checkbox"/>	<5> := Step position information	M_ST_NA_1
<input type="checkbox"/>	<del>&lt;6&gt; := Step position information with time tag</del>	<del>M_ST_TA_1</del>
<input checked="" type="checkbox"/>	<7> := Bitstring of 32 bit	M_BO_NA_1
<input type="checkbox"/>	<del>&lt;8&gt; := Bitstring of 32 bit with time tag</del>	<del>M_BO_TA_1</del>
<input type="checkbox"/>	<9> := Measured value, normalized value	M_ME_NA_1
<input type="checkbox"/>	<del>&lt;10&gt; := Measured value, normalized value with time tag</del>	<del>M_ME_TA_1</del>
<input type="checkbox"/>	<11> := Measured value, scaled value	M_ME_NB_1
<input type="checkbox"/>	<del>&lt;12&gt; := Measured value, scaled value with time tag</del>	<del>M_ME_TB_1</del>
<input checked="" type="checkbox"/>	<13> := Measured value, short floating point value	M_ME_NC_1
<input type="checkbox"/>	<del>&lt;14&gt; := Measured value, short floating point value with time tag</del>	<del>M_ME_TC_1</del>
<input checked="" type="checkbox"/>	<15> := Integrated totals	M_IT_NA_1
<input type="checkbox"/>	<del>&lt;16&gt; := Integrated totals with time tag</del>	<del>M_IT_TA_1</del>
<input type="checkbox"/>	<del>&lt;17&gt; := Event of protection equipment with time tag</del>	<del>M_EP_TA_1</del>
<input type="checkbox"/>	<del>&lt;18&gt; := Packed start events of protection equipment with time tag</del>	<del>M_EP_TB_1</del>
<input type="checkbox"/>	<del>&lt;19&gt; := Packed output circuit information of protection equipment with time tag</del>	<del>M_EP_TC_1</del>
<input type="checkbox"/>	<20> := Packed single-point information with status change detection	M_SP_NA_1
<input type="checkbox"/>	<21> := Measured value, normalized value without quality descriptor	M_ME_ND_1
<input checked="" type="checkbox"/>	<30> := Single-point information with time tag CP56Time2a	M_SP_TB_1
<input type="checkbox"/>	<31> := Double-point information with time tag CP56Time2a	M_DP_TB_1
<input type="checkbox"/>	<32> := Step position information with time tag CP56Time2a	M_ST_TB_1
<input type="checkbox"/>	<33> := Bitstring of 32 bit with time tag CP56Time2a	M_BO_TB_1
<input type="checkbox"/>	<34> := Measured value, normalized value with time tag CP56Time2a	M_ME_TD_1



<input type="checkbox"/>	<35> := Measured value, scaled value with time tag CP56Time2a	M_ME_TE_1
<input checked="" type="checkbox"/>	<36> := Measured value, short floating point value with time tag CP56Time2a	M_ME_TF_1
<input checked="" type="checkbox"/>	<37> := Integrated totals with time tag CP56Time2a	M_IT_TB_1
<input type="checkbox"/>	<38> := Event of protection equipment with time tag CP56Time2a	M_EP_TD_1
<input type="checkbox"/>	<39> := Packed start events of protection equipment with time tag CP56Time2a	M_EP_TE_1
<input type="checkbox"/>	<40> := Packed output circuit information of protection equipment with time tag CP56Time2a	M_EP_TF_1

In this companion standard only the use of the set <30> – <40> for ASDUs with time tag is permitted.

### Process information in control direction

(station-specific parameter, mark each Type ID 'X' if it is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

<input checked="" type="checkbox"/>	<45> := Single command	C_SC_NA_1
<input type="checkbox"/>	<46> := Double command	C_DC_NA_1
<input type="checkbox"/>	<47> := Regulating step command	C_RC_NA_1
<input type="checkbox"/>	<48> := Set point command, normalized value	C_SE_NA_1
<input type="checkbox"/>	<49> := Set point command, scaled value	C_SE_NB_1
<input type="checkbox"/>	<50> := Set point command, short floating point value	C_SE_NC_1
<input type="checkbox"/>	<51> := Bitstring of 32 bit	C_BO_NA_1
<input type="checkbox"/>	<58> := Single command with time tag CP56Time 2a	C_SC_TA_1
<input type="checkbox"/>	<59> := Double command with time tag CP56Time 2a	C_DC_TA_1
<input type="checkbox"/>	<60> := Regulating step command with time tag CP56Time 2a	C_RC_TA_1
<input type="checkbox"/>	<61> := Set point command, normalized value with time tag CP56Time 2a	C_SE_TA_1
<input type="checkbox"/>	<62> := Set point command, scaled value with time tag CP56Time 2a	C_SE_TB_1
<input type="checkbox"/>	<63> := Set point command, short floating point value with time tag CP56Time 2a	C_SE_TC_1
<input type="checkbox"/>	<64> := Bitstring of 32 bit with time tag CP56Time 2a	C_BO_TA_1

Either the ASDUs of the set <45> – <51> or of the set <58> – <64> are used.

### System information in monitor direction

(station-specific parameter, mark with an "X" if it is only used in the standard direction, "R" if only used in the reverse direction, and "B" if used in both directions).

<input checked="" type="checkbox"/>	<70> := End of initialization	M_EI_NA_1
-------------------------------------	-------------------------------	-----------

### System information in control direction

(station-specific parameter, mark each Type ID 'X' if it is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

<input checked="" type="checkbox"/>	<100>:= Interrogation command	C_IC_NA_1
<input checked="" type="checkbox"/>	<101>:= Counter interrogation command	C_CI_NA_1
<input type="checkbox"/>	<102>:= Read command	C_RD_NA_1

<input type="checkbox"/>	<103>:= Clock synchronization command (option see 7.6)	C_CS_NA_1
<input checked="" type="checkbox"/>	<del>&lt;104&gt;:= Test command</del>	<del>C_TS_NA_1</del>
<input type="checkbox"/>	<105>:= Reset process command	C_RP_NA_1
<input checked="" type="checkbox"/>	<del>&lt;106&gt;:= Delay acquisition command</del>	<del>C_CD_NA_1</del>
<input checked="" type="checkbox"/>	<107>:= Test command with time tag CP56time2a	C_TS_TA_1

### Parameter in control direction

(station-specific parameter, mark each Type ID 'X' if it is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

<input type="checkbox"/>	<110>:= Parameter of measured value, normalized value	P_ME_NA_1
<input type="checkbox"/>	<111>:= Parameter of measured value, scaled value	P_ME_NB_1
<input type="checkbox"/>	<112>:= Parameter of measured value, short floating point value	P_ME_NC_1
<input type="checkbox"/>	<113>:= Parameter activation	P_AC_NA_1

### File Transfer

(station-specific parameter, mark each Type ID 'X' if it is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

<input type="checkbox"/>	<120>:= File ready	F_FR_NA_1
<input type="checkbox"/>	<121>:= Section ready	F_SR_NA_1
<input type="checkbox"/>	<122>:= Call directory, select file, call file, call section	F_SC_NA_1
<input type="checkbox"/>	<123>:= Last section, last segment	F_LS_NA_1
<input type="checkbox"/>	<124>:= Ack file, ack section	F_AF_NA_1
<input type="checkbox"/>	<125>:= Segment	F_SG_NA_1
<input type="checkbox"/>	<126>:= Directory {blank or X, only available in monitor (standard) direction}	F_DR_TA_1
<input type="checkbox"/>	<127>:= Query Log – Request archive file	F_SC_NB_1

**Type identifier and cause of transmission assignments**  
(station-specific parameters)

Shaded boxes are not required.

Black boxes are not permitted in this companion standard

Blank: functions or ASDU not used.

Mark Type Identification/Cause of transmission combinations:

'X' if only used in the standard direction

'R' if only used in the reverse direction

'B' if used in both directions

Type identification		Cause of transmission																			
		periodic, cyclic	background scan	spontaneous	initialized	request or requested	activation	activation confirmation	deactivation	deactivation confirmation	activation termination	return info caused by a remote cmd	return info caused by a local cmd	file transfer	interrogated by station interrogation	interrogated by group <n>	request by group <n> counter request	unknown type identification	unknown cause of transmission	unknown common address of ASDU	unknown information object address
		1	2	3	4	5	6	7	8	9	10	11	12	13	20	21 to 36	37 to 41	44	45	46	47
<1>	M_SP_NA_1														X	X					
<2>	M_SP_TA_4																				
<3>	M_DP_NA_1																				
<4>	M_DP_TA_4																				
<5>	M_ST_NA_1																				
<6>	M_ST_TA_4																				
<7>	M_BO_NA_1														X	X					
<8>	M_BO_TA_4																				
<9>	M_ME_NA_1																				
<10>	M_ME_TA_4																				
<11>	M_ME_NB_1																				
<12>	M_ME_TB_4																				
<13>	M_ME_NC_1	X													X	X					
<14>	M_ME_TC_4																				
<15>	M_IT_NA_1																X				
<16>	M_IT_TA_4																				
<17>	M_EP_TA_4																				
<18>	M_EP_TB_4																				

Type identification		Cause of transmission																				
		periodic, cyclic	background scan	spontaneous	initialized	request or requested	activation	activation confirmation	deactivation	deactivation confirmation	activation termination	return info caused by a remote cmd	return info caused by a local cmd	file transfer	interrogated by station interrogation	interrogated by group <n> counter request	unknown type identification	unknown cause of transmission	unknown common address of ASDU	unknown information object address		
		1	2	3	4	5	6	7	8	9	10	11	12	13	20	21 to 36	37 to 41	44	45	46	47	
<19>	M_EP_TC_4																					
<20>	M_PS_NA_1																					
<21>	M_ME_ND_1																					
<30>	M_SP_TB_1			X																		
<31>	M_DP_TB_1																					
<32>	M_ST_TB_1																					
<33>	M_BO_TB_1																					
<34>	M_ME_TD_1																					
<35>	M_ME_TE_1																					
<36>	M_ME_TF_1			X																		
<37>	M_IT_TB_1			X																		
<38>	M_EP_TD_1																					
<39>	M_EP_TE_1																					
<40>	M_EP_TF_1																					
<45>	C_SC_NA_1						X	X			X							X	X	X	X	
<46>	C_DC_NA_1																					
<47>	C_RC_NA_1																					
<48>	C_SE_NA_1																					
<49>	C_SE_NB_1																					
<50>	C_SE_NC_1																					
<51>	C_BO_NA_1																					
<58>	C_SC_TA_1																					
<59>	C_DC_TA_1																					
<60>	C_RC_TA_1																					
<61>	C_SE_TA_1																					
<62>	C_SE_TB_1																					
<63>	C_SE_TC_1																					
<64>	C_BO_TA_1																					
<70>	M_EI_NA_1*																					

Type identification		Cause of transmission																			
		periodic, cyclic	background scan	spontaneous	initialized	request or requested	activation	activation confirmation	deactivation	deactivation confirmation	activation termination	return info caused by a remote cmd	return info caused by a local cmd	file transfer	interrogated by station interrogation	interrogated by group <n> counter request	unknown type identification	unknown cause of transmission	unknown common address of ASDU	unknown information object address	
		1	2	3	4	5	6	7	8	9	10	11	12	13	20	21 to 36	37 to 41	44	45	46	47
<100>	C_IC_NA_1						X	X			X							X	X	X	X
<101>	C_CI_NA_1						X	X			X							X	X	X	X
<102>	C_RD_NA_1																				
<103>	C_CS_NA_1																				
<104>	C_TS_NA_4																				
<105>	C_RP_NA_1																				
<106>	C_CD_NA_4																				
<107>	C_TS_TA_1																				
<110>	P_ME_NA_1																				
<111>	P_ME_NB_1																				
<112>	P_ME_NC_1																				
<113>	P_AC_NA_1																				
<120>	F_FR_NA_1																				
<121>	F_SR_NA_1																				
<122>	F_SC_NA_1																				
<123>	F_LS_NA_1																				
<124>	F_AF_NA_1																				
<125>	F_SG_NA_1																				
<126>	F_DR_TA_1*																				
<127>	F_SC_NB_1*																				

## 1.6 Basic application functions

### Station initialization

(station-specific parameter, mark 'X' if function is used)

Remote initialization

### Cyclic data transmission

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

Cyclic data transmission

### Read procedure

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

Read procedure

### Spontaneous transmission

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

Spontaneous transmission

### Double transmission of information objects with cause of transmission spontaneous

(station-specific parameter, mark each information type 'X' where both a Type ID without time and corresponding Type ID with time are issued in response to a single spontaneous change of a monitored object)

The following type identifications may be transmitted in succession caused by a single status change of an information object. The particular information object addresses for which double transmission is enabled are defined in a project-specific list.

- Single-point information M\_SP\_NA\_1, M\_SP\_TA\_1, M\_SP\_TB\_1 and M\_PS\_NA\_1
- Double-point information M\_DP\_NA\_1, M\_DP\_TA\_1 and M\_DP\_TB\_1
- Step position information M\_ST\_NA\_1, M\_ST\_TA\_1 and M\_ST\_TB\_1
- Bitstring of 32 bit M\_BO\_NA\_1, M\_BO\_TA\_1 and M\_BO\_TB\_1 (if defined for a specific project)
- Measured value, normalized value M\_ME\_NA\_1, M\_ME\_TA\_1, M\_ME\_ND\_1 and M\_ME\_TD\_1
- Measured value, scaled value M\_ME\_NB\_1, M\_ME\_TB\_1 and M\_ME\_TE\_1
- Measured value, short floating point number M\_ME\_NC\_1, M\_ME\_TC\_1 and M\_ME\_TF\_1

### Station interrogation

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

- |   |   |                                   |
|---|---|-----------------------------------|
| <input checked="" type="checkbox"/> global  |   |                                   |
| <input checked="" type="checkbox"/> group 1 | <input checked="" type="checkbox"/> group 7 | <input type="checkbox"/> group 13 |
| <input checked="" type="checkbox"/> group 2 | <input type="checkbox"/> group 8            | <input type="checkbox"/> group 14 |
| <input checked="" type="checkbox"/> group 3 | <input type="checkbox"/> group 9            | <input type="checkbox"/> group 15 |
| <input checked="" type="checkbox"/> group 4 | <input type="checkbox"/> group 10           | <input type="checkbox"/> group 16 |
| <input checked="" type="checkbox"/> group 5 | <input type="checkbox"/> group 11           |                                   |
| <input checked="" type="checkbox"/> group 6 | <input type="checkbox"/> group 12           |                                   |

Information Object Addresses assigned to each group  
must be shown in a separate table  
→ see SICAM\_MMU\_104\_PIXIT\_A1.pdf

### Clock synchronization

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

- Clock synchronization
- Day of week used
- RES1, GEN (time tag substituted/ not substituted) used
- SU-bit (summertime) used

optional, see 7.6

### Command transmission

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

- Direct command transmission
- Direct set point command transmission
- Select and execute command
- Select and execute set point command
- C\_SE ACTTERM used
  
- No additional definition
- Short pulse duration (duration determined by a system parameter in the outstation)
- Long pulse duration (duration determined by a system parameter in the outstation)
- Persistent output
  
- Supervision of maximum delay in command direction of commands and set point commands

Maximum allowable delay of commands and set point commands

### Transmission of integrated totals

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

- Mode A: Local freeze with spontaneous transmission
- Mode B: Local freeze with counter interrogation
- Mode C: Freeze and transmit by counter-interrogation commands
- Mode D: Freeze by counter-interrogation command, frozen values reported spontaneously
  
- Counter read
- Counter freeze without reset
- Counter freeze with reset
- Counter reset (with a separate Single Command, IOA 2025)
  
- General request counter
- Request counter group 1
- Request counter group 2
- Request counter group 3
- Request counter group 4

### Parameter loading

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

- Threshold value
- Smoothing factor
- Low limit for transmission of measured values
- High limit for transmission of measured values

### Parameter activation

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

- Act/deact of persistent cyclic or periodic transmission of the addressed object



**Test procedure**

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

Test procedure

**File transfer**

(station-specific parameter, mark 'X' if function is used)

File transfer in monitor direction

- Transparent file
- Transmission of disturbance data of protection equipment
- Transmission of sequences of events
- Transmission of sequences of recorded analog values

File transfer in control direction

Transparent file

**Background scan**

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

Background scan

**Acquisition of transmission delay**

(station-specific parameter, mark 'X' if function is only used in the standard direction, 'R' if only used in the reverse direction, and 'B' if used in both directions)

Acquisition of transmission delay

**Definition of time outs**

Parameter	Default value	Remarks	Selected value
$t_0$	30s	Time-out of connection establishment	-
$t_1$	15s	Time-out of send or test APDUs	Configurable
$t_2$	10s	Time-out for acknowledges in case of no data messages $t_2 < t_1$	Configurable
$t_3$	20s	Time-out for sending test frames in case of a long idle state	Configurable

Maximum range of values for all time outs: 1 to 255 s, accuracy 1 s

**Maximum number of outstanding I format APDUs k and latest acknowledge APDUs (w)**

Parameter	Default value	Remarks	Selected value
k	12 APDUs	Maximum difference receive sequence number to send state variable	<b>12</b>
w	8 APDUs	Latest acknowledge after receiving w I-format APDUs	<b>8</b>

Maximum range of values k: 1 to 32767 ( $2^{15}-1$ ) APDUs, accuracy 1 APDU

Maximum range of values w: 1 to 32767 APDUs, accuracy 1 APDU (Recommendation: w should not exceed two-thirds of k).

**Portnumber**

Parameter	Value	Remarks
Portnumber	2404	<b>Configurable (2000 ... 65535)</b>

**Redundant connections**

<b>2</b>
----------

Number N of redundancy group connections used

**RFC 2200 suite**

RFC 2200 is an official Internet Standard which describes the state of standardization of protocols used in the Internet as determined by the Internet Architecture Board (IAB). It offers a broad spectrum of actual standards used in the Internet. The suitable selection of documents from RFC 2200 defined in this standard for given projects has to be chosen by the user of this standard.

Ethernet 802.3

Serial X.21 interface

Other selection from RFC 2200:

List of valid documents from RFC 2200

1. ....
2. ....
3. ....
4. ....