

SIEMENS

SIPROTEC 4
SIPROTEC Compact
Reyrolle IEDs

EN100 Communication Module

IEC 61850
PIXIT, PICS, TICS

Manual

Preface

Contents

Applications

1

IEC 61850 Conformance Statements

2

Disclaimer of Liability

This document has been subjected to rigorous technical review before being published. It is revised at regular intervals, and any modifications and amendments are included in the subsequent issues. The content of this document has been compiled for information purposes only. Although Siemens AG has made best efforts to keep the document as precise and up-to-date as possible, Siemens AG shall not assume any liability for defects and damage which result through use of the information contained herein.

This content does not form part of a contract or of business relations; nor does it change these. All obligations of Siemens AG are stated in the relevant contractual agreements.

Siemens AG reserves the right to revise this document from time to time.

Document Release: C53000-G1140-C385-2.06
Release 08.2016

Copyright

Copyright © Siemens AG 2016. All rights reserved. The disclosure, duplication, distribution and editing of this document, or utilization and communication of the content are not permitted, unless authorized in writing. All rights, including rights created by patent grant or registration of a utility model or a design, are reserved.

Registered Trademarks

SIPROTEC® and DIGSI® are registered trademarks of SIEMENS AG. An unauthorized use is illegal.

All other designations in this document can be trademarks whose use by third parties for their own purposes can infringe the rights of the owner.

Preface

Purpose of this manual

In this Manual, you will find the Specification of the applications of the IEC 61850 interface EN100.

Target audience

This manual is intended mainly for all persons who configure, parameterize and operate SIPROTEC 4, SIPROTEC Compact and Reyrolle IED devices.

Scope of validity

This manual is valid for SIPROTEC 4, SIPROTEC Compact and Reyrolle IED devices with Edition 1 and Edition 2 mode of IEC 61850 and EN100 Firmware version V4.29 and higher.

Standards

This manual has been created according to the ISO 9001 quality standards.

Additional support

For questions about EN100, please contact your Siemens sales representative.

Support

Our Customer Support Center provides around-the-clock support.

Phone: +49 (180) 524-8437
Fax: +49 (180) 524-2471
e-mail: support.energy@siemens.com

Training courses

If you are interested in our current training program, please contact our training center:

Siemens AG
Siemens Power Academy TD

Humboldtstr. 59
90459 Nuremberg
Germany

Phone: +49 (911) 433-7415
Fax: +49 (911) 433-5482
E-mail: poweracademy@siemens.com
Internet: www.siemens.com/poweracademy

Contents

| | | |
|----------|--|-----------|
| | Preface | 3 |
| 1 | Applications | 7 |
| 1.1 | General | 8 |
| 1.2 | Association model | 9 |
| 1.3 | Server model | 10 |
| 1.4 | Data set model | 11 |
| 1.5 | Setting group control model | 12 |
| 1.6 | Reporting model | 13 |
| 1.7 | GOOSE publish model | 15 |
| 1.8 | GOOSE subscribe model | 16 |
| 1.9 | Control model | 18 |
| 1.10 | Time and time synchronisation model | 21 |
| 1.11 | File transfer model | 22 |
| 1.12 | General items | 23 |
| 1.13 | TICS - Technical Issues Implementation Conformance Statement | 24 |
| 1.13.1 | TISSUES Edition 1 | 24 |
| 1.13.2 | TISSUES Edition 2 | 26 |
| 2 | IEC 61850 Conformance Statements | 27 |
| 2.1 | Definitions of the ISO/OSI Reference Model | 28 |
| 2.2 | Definition of the Communication Services Acc. to Standard (PICS) | 29 |
| 2.2.1 | Profile Compliance | 29 |
| 2.3 | Model Implementation Conformance Statement (MICS) | 35 |

1 Applications

Contents

This chapter specifies the protocol implementation extra information for testing (PIXIT) of the IEC 61850 interface EN100.

| | | |
|------|--|----|
| 1.1 | General | 8 |
| 1.2 | Association model | 9 |
| 1.3 | Server model | 10 |
| 1.4 | Data set model | 11 |
| 1.5 | Setting group control model | 12 |
| 1.6 | Reporting model | 13 |
| 1.7 | GOOSE publish model | 15 |
| 1.8 | GOOSE subscribe model | 16 |
| 1.9 | Control model | 18 |
| 1.10 | Time and time synchronisation model | 21 |
| 1.11 | File transfer model | 22 |
| 1.12 | General items | 23 |
| 1.13 | TICS - Technical Issues Implementation Conformance Statement | 24 |

1.1 General

This manual specifies the protocol implementation extra information for testing (PIXIT) of the IEC 61850 interface EN100.

The following applicable ACSI service models are specified:

- Association model
- Server model
- Data set model
- Reporting model
- Setting Group model
- GOOSE publish model
- GOOSE subscribe model
- Control model
- Time and time synchronisation model
- File transfer model
- General items

Together with the PICS and the MICS the PIXIT forms the basis for a conformance test according to IEC 61850-10.

The mapping between the IEC 61850 server data model and the SIPROTEC 4 or SIPROTEC Compact specific data is specified in the device specific MICS Descriptions, Chapter 2.3.

1.2 Association model

| ID | ED | Description | Value / Clarification |
|-----|------|---|--|
| As1 | 1 | Maximum number of clients that can set-up an association simultaneously | 6 |
| As2 | 1, 2 | TCP_KEEPALIVE value | 1 second to 20 seconds |
| As3 | 1, 2 | Lost connection detection time range | 10 seconds |
| As4 | | Authentication is not supported | Not supported |
| As5 | 1, 2 | What association parameters are necessary for successful association ? | Y Transport selector Y Session selector Y Presentation selector Y AP Title (ANY) Y AE Qualifier (ANY) Where Y means: as defined within the ICD-File ANY means: any value accepted |
| As6 | 1, 2 | If association parameters are necessary for association, describe the correct values e.g. | Transport selector 0001 Session selector 0001 Presentation selector 00000001 |
| As7 | 1, 2 | What is the maximum and minimum MMS PDU size ? | Max MMS PDU size 32768 Min MMS PDU size 8192 |
| As8 | 1, 2 | What is the maximum startup time after a power supply interrupt ? | Typical 15 seconds The value depends on the size of the object directory |

1.3 Server model

| ID | ED | Description | Value / Clarification |
|-----|------|---|--|
| Sr1 | 1, 2 | Which analogue value (MX) quality bits are supported (can be set by server) ? | Validity: Y Good, Y Invalid, N Reserved, Y Questionable Y Overflow Y OutofRange N BadReference N Oscillatory Y Failure Y OldData N Inconsistent Y Inaccurate Source: Y Process N Substituted Y Test N OperatorBlocked |
| Sr2 | 1, 2 | Which status value (ST) quality bits are supported (can be set by server) ? | Validity: Y Good, Y Invalid, N Reserved, Y Questionable N BadReference Y Oscillatory Y Failure Y OldData N Inconsistent N Inaccurate Source: Y Process N Substituted Y Test N OperatorBlocked |
| Sr3 | | What is the maximum number of data values in one GetDataValues request ? | Not restricted; depends on the max. MMS PDU size given above. |
| Sr4 | | What is the maximum number of data values in one SetDataValues request ? | Not restricted; depends on the max. MMS PDU size given above. |
| Sr5 | | Which Mode / Behaviour values are supported? | Y On N (On-)Blocked Y Test N Test/Blocked Y Off |

1.4 Data set model

| ID | ED | Description | Value / Clarification |
|-----|----|---|--|
| Ds1 | 1 | What is the maximum number of data elements in one data set? (compare ICD setting) | Not limited by an internal configuration parameter. It depends on the available memory and MMS PDU size. |
| Ds2 | 1 | How many persistent data sets can be created by one or more clients ? | 64 data sets for each LD. It depends on the available memory. |
| Ds3 | 1 | How many non-persistent data sets can be created by one or more clients ? | 10 data sets. It depends on the available memory. |

1.5 Setting group control model

| ID | ED | Description | Value / Clarification |
|-----|------|--|--|
| Sg1 | 1 | What is the number of supported setting groups for each logical device? | Setting groups available for LLN0 only in LD PROT. The number of supported setting groups is 1 or 4, it depends on the given configuration. Specified in the ICD-File. |
| Sg2 | 1, 2 | What is the effect of when and how the non-volatile storage is updated ? (compare IEC 61850-8-1 §16.2.4) | Not applicable |
| Sg3 | 1 | Can multiple clients edit the same setting group? | Not applicable |
| Sg4 | 1 | What happens if the association is lost while editing a setting group? | Not applicable |
| Sg5 | 1 | Is EditSG value 0 allowed? | Not applicable |
| Sg6 | 2 | When ResvTms is not present how long is an edit setting group locked? | Not applicable |

1.6 Reporting model

| ID | ED | Description | Value / Clarification |
|-------------------|------|--|--|
| Rp1 | 1 | The supported trigger conditions are (compare PICS) | Y Integrity Y Data change Y Quality change Y Data update Y General Interrogation |
| Rp2 | 1 | The supported optional fields are | Y Sequence-number Y Report-time-stamp Y Reason-for-inclusion Y Data-set-name Y Data-reference Y Buffer-overflow - for Buffered report Y EntryID - for Buffered report Y Conf-rev Y Segmentation |
| Rp3 | 1, 2 | Can the server send segmented reports ? | Y |
| Rp4 | 1, 2 | Mechanism on second internal data change notification of the same analogue data value within buffer period (Compare IEC 61850-7-2 §14.2.2.9) | Send report immediately for Buffered Report: Buffer the Entry Send report if the report is enabled |
| Rp5 | 1 | Multi client URCB approach (Compare IEC 61850-7-2 §14.2.1) | All clients can access all URCB's |
| Rp6 | - | What is the format of EntryID? | First 2 Byte : Integer Last 6 Bytes: BTime6 time stamp |
| Rp7 | 1, 2 | What is the buffer size for each BRCB or how many reports can be buffered ? | About 270 kB are available for the buffering. Each BRCB has an extension attribute Memory that display the percentage of those 270 kB that have been reserved/foreseen for its own entries. Default amount 270 kB/(2*Number of logical devices). The buffer size can also be adapted by configuration. |
| Rp8 | - | Pre-configured RCB attributes that cannot be changed online when RptEna = FALSE (see also the ICD report settings) | For Buffered and Unbuffered: All pre-configured RCB attributes can be changed online when RptEna = FALSE |
| Rp9 | 1 | May the reported data set contain: - structured data objects? - data attributes? | Y Y |
| Rp10 | 1, 2 | What is the scan cycle for binary events? Is this fixed, configurable | 1 msecond Fixed |
| Rp11 | 1 | Does the device support to pre-assign a RCB to a specific client in SCL | N ResvTms is set to -1 for the SCL BufferedReportControl that are associated to ClientLN. However, authentication of specific clients is not standardized and thus not supported. |
| Rp12 | 2 | After restart of the server is the value of ConfRev restored from the original configuration or retained prior to restart | Restore from original configuration |
| additional items: | | | |

| ID | ED | Description | Value / Clarification |
|----|----|---|---|
| | | Interrupt of general interrogation | Running GI could not be interrupted. If a new GI request occurs during a running GI, the current GI will be finished first before the second GI request will be processed. |
| | | Integrity period | Configurable ≥ 1 second; |
| | | URCB reservation after an abort of the client/server association | Reservation of the URCB is lost. After a re-establishment of the association the URCB reservation has to be renewed by the client. This behavior is implemented to avoid unnecessary memory residuals if temporarily client associations (e.g. for maintenance) are established. |
| | | Configured URCB reservation after an abort of the client/server association | Reservation of the URCB is lost. |
| | | Optional use of a flow control for transmitting history of a BRCB | <p>As specified in the IEC61850-7-2, transmission of entries may require some time, depending of the amount of entries that have to be transmitted.</p> <p>Therefore, the EN100 has an optional flow control feature to accelerate the transmission of the entries: each BRCB has an extended attribute MaxOutReports that can be set from the associated-client to change the transmission strategy of the entries. Those attributes are located in VMD variables. The number ordered will then be transmitted as long as they exist in the buffer; the server then reset the attribute to 0 and wait for the client to set it again in order to continue the history transmission with MaxOutReports entries. The attribute only influences the flow control of entries while dealing with the history, and not after the history transmission has completed.</p> |

1.7 GOOSE publish model

| ID | ED | Description | Value / Clarification |
|-------------------|------|---|--|
| Gp1 | 1, 2 | Can the test flag in the published GOOSE be turned on / off | N |
| Gp2 | 1 | What is the behavior when the GOOSE publish configuration is incorrect | DUT will send GOOSE with NdsCom = TRUE as long as the minimum required configuration is available (dstAddress, dataSet) |
| Gp3 | 1, 2 | Published FCD supported common data classes are | SPS, DPS, INS, ENS, ACT, ACD, BCR, MV, CMV, WYE, DEL, SEQ, SPC, DPC, INC, ENC, APC, BAC, BSC Arrays are not supported |
| Gp4 | 1, 2 | What is the slow retransmission time? Is it fixed or configurable? | Configured by SCD file |
| Gp5 | 1, 2 | What is the fast retransmission scheme? Is it fixed or configurable? | Configured by SCD file |
| Gp6 | - | Can the GOOSE publish be turned on / off by using SetGoCBValues(GoEna) | Deprecated See PICS - SetGoCBValues |
| Gp7 | 1, 2 | What is the initial GOOSE sqNum after restart | sqNum = 1 |
| Gp8 | 1 | May the GOOSE data set contain: - structured data objects (FCD)? - Timestamp data attributes? | Y Y |
| additional items: | | | |
| | | Maximum number of GOOSE messages which could be sent | ≤ 16 ; It depends on the available memory. |

1.8 GOOSE subscribe model

| ID | ED | Description | Value / Clarification |
|-------------------|------|--|--|
| Gs1 | 1, 2 | What elements of a subscribed GOOSE header are checked to decide the message is valid and the allData values are accepted? If yes, describe the conditions. Note: the VLAN tag may be removed by a ethernet switch and should not be checked | N Source MAC address Y Destination MAC address Y Ethertype = 0x88B8 Y APPIP Y gocbRef N timeAllowedtoLive Y datSet Y goID N t Y stNum Y sqNum Y test/simulation Y confRev Y ndsCom Y numDatSetEntries |
| Gs2 | 1, 2 | When is a subscribed GOOSE marked as lost ? (TAL = time allowed to live value from the last received GOOSE message) | When message does not arrive by 2 · TAL |
| Gs3 | 1, 2 | What is the behavior when one or more subscribed GOOSE message isn't received or syntactically incorrect ? (missing GOOSE) | The telegram will be discarded (i.e not forwarded to the application) since it is corrupt or syntactically incorrect and therefore not readable. The data objects will be declared as invalid after a timeout detection since no telegram have been received by the application. |
| Gs4 | 1, 2 | What is the behavior when a subscribed GOOSE message is out-of-order ? | When a given state number n, sequence number l is received, only the following telegrams will be accepted: n, l + 1 n, l + 2 n + 1, 0 n + 1, 1 1,0 All other telegrams are ignored |
| Gs5 | 1, 2 | What is the behavior when a subscribed GOOSE message is duplicated ? | The repetition will be ignored |
| Gs6 | 1 | Does the device subscribe to GOOSE messages with/without the VLAN tag? | Y with the VLAN tag Y without the VLAN tag |
| Gs7 | 1 | May the GOOSE data set contain: - structured data objects? - timestamp data attributes? | Y Y |
| Gs8 | 1, 2 | Subscribed FCD supported common data classes are | SPS, DPS, INS, ENS, ACT, ACD, BCR, MV, CMV, WYE, DEL, SEQ, SPC, DPC, INC, ENC, BSC, ISC, APC, BAC Arrays are not supported |
| additional items: | | | |
| | | Maximum number of GOOSE messages which could be received | ≤ 128 ; It depends on the available memory. |
| | | Interpretation of GOOSE messages at subscriber side | 1. Received GOOSE data objects without assigned quality attribute are interpreted as invalid. 2. Received GOOSE data objects which quality attribute are set to questionable are changed to invalid. |

| ID | ED | Description | Value / Clarification |
|----|----|--|---|
| | | GOOSE subscriber behavior in case of missing GOOSE messages | After a GOOSE multicast application association has been interrupted, the reception of a valid GOOSE telegram is required to validate the state of this GOOSE association again. However, the IED tolerates a missing telegram as long as the next telegram (expected n, received n+1) is received within the time allowed to live time out detection (the time allowed to live timeout detection occurs after 2 · TAL). |
| | | What is the behavior when a GOOSE header parameter is mismatching with the expected one? (datSet, goID, confRev, numDatSetEntries, number of allData) | Error message will be stored into the error buffer (could be accessed by EN100 web-server). The received telegram with the mismatched attribute will be discarded: It has not been subscribed. |
| | | What is the behavior when there is an out-of-order entry in the allData? | The confRev attribute in the header guarantees that the allData entries are in the correct order. Therefore, it's necessary to check the confRev attribute. There is no chance to detect a semantic out-of-order if the types are identical. |
| | | What is the behavior when numDatSetEntries and number of allData are inconsistent? | The telegram is discarded since it is corrupt (not well formed). After the timeout detection (no telegram forwarded to the application) the data objects are declared invalid. |
| | | Does the device support Fixed Offset of GOOSE? | N |

1.9 Control model

| ID | ED | Description | Value / Clarification |
|-----|------|---|---|
| Ct1 | - | What control models are supported? (compare PICS) | Y Status-only Y Direct-with-normal-security N Sbo-with-normal-security Y Direct-with-enhanced-security Y Sbo-with-enhanced-security |
| Ct2 | 1, 2 | Is the control model fixed, configurable and/ or online changeable? | Fixed |
| Ct3 | - | Is TimeActivatedOperate supported (compare PICS or SCL) | N |
| Ct4 | - | Is "operate-many" supported (compare sboClass)? | N |
| Ct5 | 1 | What is the behavior of the DUT when the test attribute is set in the SelectWithValue and/or Operate request | The request will be proceed if the Beh of the logical node where the controllable object is located is test. Otherwise, it will be discarded as blocked-by-mode |
| Ct6 | - | What are the conditions for the time (T) at- tribute in the SelectWithValue and/or Operate request | Time attribute is not relevant. |
| Ct7 | - | Is pulse configuration supported ? | N |
| Ct8 | 1 | What is the behavior of the DUT when the check conditions are set Is this behavior fixed, configurable, online changeable? | Y synchrocheck Y interlock-check DUT uses the check value to perform the check according to the control request Configurable |

| ID | ED | Description | Value / Clarification |
|------|------|--|--|
| Ct9 | 1, 2 | What additional cause diagnosis are supported | Y Blocked-by-switching-hierarchy Y Select-failed Y Invalid-position Y Position-reached Y Parameter-change-in-execution (in Ed1 only) Y Step-limit Y Blocked-by-Mode Y Blocked-by-process Y Blocked-by-interlocking Y Blocked-by-synchrocheck Y Command-already-in-execution N Blocked-by-health Y 1-of-n-control Y Abortion-by-cancel Y Time-limit-over N Abortion-by-trip Y Object-not-selected Edition 2 specific values: Y Object-already-selected N No-access-authority N Ended-with-overshoot N Abortion-due-to-deviation N Abortion-by-communication-loss N Blocked-by-command N None Y Inconsistent-parameters Y Locked-by-other-client |
| Ct10 | 1, 2 | How to force a "test-not-ok" respond with SelectWithValue request? | Test and logical node Beh do not match Wrong orCat |
| Ct11 | 1, 2 | How to force a "test-not-ok" respond with Select request? | When the control object has already been selected |
| Ct12 | 1, 2 | How to force a "test-not-ok" respond with Operate request? | DOns: Test and logical node Beh do not match Wrong orCat SBOs: N/A DOes: Test and logical node Beh do not match Wrong orCat SBOes: Test and logical node Beh do not match Wrong orCat |
| Ct13 | 1, 2 | Which origin categories are supported? | Bay-control, station-control, remote-control, automatic-station, automatic-remote, maintenance, process |
| Ct14 | 1, 2 | What happens if the orCat value is not supported? | DOns: Operate.Resp- SBOs: N/A DOes: Operate.Resp-, addCause = not-supported SBOes: SelectWithValue.Resp-, addCause = not-supported |

1.9 Control model

| ID | ED | Description | Value / Clarification |
|-------------------|------|---|---|
| Ct15 | 1, 2 | Does the IED accept a SelectWithValue/Operate with the same ctIVal as the current status value? | DOns: Y SBOns: N/A DOes: Y SBOes SelectWithValue: Y SBOes Operate: N Depending if the verify check has been disabled with |
| Ct16 | 1 | Does the IED accept a Select/Operate on the same control object from 2 different clients at the same time? | DOns: Y SBOns: N/A DOes: N SBOes: N No, if the second request occurred when the object is not in unselected state (SBOes), resp. Ready state (DOns, DOes), then it will lead to a negative response |
| Ct17 | 1 | Does the IED accept a Select/SelectWithValue from the same client when the control object is already selected (tissue 334) | SBOns: N/A SBOes: N |
| Ct18 | 1, 2 | Is for SBOes the internal validation performed during the SelectWithValue and/or Operate step? | Operate |
| Ct19 | - | Can a control operation be blocked by Mod=Off or Blocked | Y |
| Ct20 | 1, 2 | Does the IED support local / remote operation? | Y |
| Ct21 | 1, 2 | Does the IED send an InformationReport with LastApplError as part of the Operate response for control with normal security? | SBOns: N/A DOns: N |
| Ct22 | 2 | How to force a "parameter-change-in-execution" | SBOns: N/A SBOes: parameter-change-in-execution is supported in Ed1 only |
| additional items: | | | |
| | | Inconsistency between SelectWithValue and (Operate or Cancel) | Operate or Cancel will be acknowledged with negative response if inconsistencies to the SelectWithValue request are detected. The following attributes will not be checked in this case: T (Time) The controlled object returns then in state "unselected" |
| | | Cancel request could be sent after an operate request. | Y |
| | | Format of the control time stamp attribute ? | Time stamp instead of EntryTime acc. to the 7-2 Errata List. |
| | | What is the behavior of the control state machines when the association is lost with the client that issued a successful control? | For SBOes: If the current state is "Ready", then the selection ends. |

1.10 Time and time synchronisation model

| ID | ED | Description | Value / Clarification |
|-------------------|------|---|--|
| Tm1 | 1, 2 | What quality bits are supported (may be set by the IED)? | Y LeapSecondsKnown Y ClockFailure Y ClockNotSynchronized |
| Tm2 | 1, 2 | Describe the behavior when the time synchronization signal/messages are lost | The quality attribute "ClockNotSynchronized" will be set to TRUE after a configured time period |
| Tm3 | 1, 2 | How long does it take to take over the new time from time server | Configurable Default: 10 min |
| Tm4 | 1, 2 | When is the time quality bit "Clock failure" set? | Clock failure is set when the device internal clock drifts from the external synchronization |
| Tm5 | 1, 2 | When is the time quality bit "Clock not synchronised" set? | The "ClockNotSynchronized" attribute is set to TRUE as long as no time synchronization is established. |
| Tm6 | - | Is the timestamp of a binary event adjusted to the configured scan cycle? | Deprecated |
| Tm7 | 1 | Does the device support time zone and day-light saving? | Y |
| Tm8 | 1,2 | Which attributes of the SNTP response packet are validated? | N Leap indicator not equal to 3? Y Mode is equal to SERVER Y OriginateTimestamp is equal to value sent by the SNTP client as Transmit Timestamp Y RX/TX timestamp fields are checked for reasonableness Y SNTP version 3 and/or 4 Y Other (describe): Stratum is not KISS OF DEATH Clock of STNP Server is synchronized Response comes from the server to which the request was sent |
| Tm9 | 1, 2 | Do the COMTRADE files have local time or UTC time and is this configurable | Local time Not configurable |
| additional items: | | | |
| | | What is the behaviour when the time synchronisation messages indicate that the stratum is greater than 3? | A stratum with a value greater than 3 with the SNTP time synchronization messages indicates that the time server has a questionable synchronisation. It might also indicate that no GPS connection are available. Therefore the time quality attribute "ClockNotSynchronized" will be set to TRUE as long as the stratum content is greater than 3. |
| | | What is the behavior when the time synchronization signal/messages are lost? | The quality attribute "Clock Failure" will be set to TRUE after losing communication with the Time Master for a configured time period. |

1.11 File transfer model

| ID | ED | Description | Value / Clarification |
|-------------------|------|--|--|
| Ft1 | 1 | What is structure of files and directories? Where are the COMTRADE files stored? Are COMTRADE Files zipped and what files are included in each zip file? | Directory name / COMTRADE / *; Files according to the COMTRADE standard and not zipped. |
| Ft2 | 1, 2 | Directory names are separated from the file name by | "/" |
| Ft3 | 1 | The maximum file name size including path (default 64 chars) | 64 |
| Ft4 | 1, 2 | Are directory/file name case sensitive | Case sensitive |
| Ft5 | 1, 2 | Maximum file size for SetFile | SetFile is not supported |
| Ft6 | 1 | Is the requested file path included in the file name of the MMS fileDirectory respond? | Y |
| Ft7 | 1 | Is the wild char supported MMS fileDirectory request? | Y only as *; not as name completion wild card |
| Ft8 | 1, 2 | Is it allowed that 2 clients get a file at the same time? | N |
| additional items: | | | |
| | | Maximum number of clients that can use the File transfer service simultaneously | 1 |
| | | Maximum number of files that can be accessed simultaneously | 1 |
| | | Maximum time the file transfer service is locked for one client | 10 min |

1.12 General items

| ID | ED | Description | Value / Clarification |
|-------------------|----|---|--|
| | | | |
| additional items: | | | |
| | | What is the type of the attribute actVal in the BCR (Binary Counter Reading) CDC? | Depending on the edition mode used. The type is integer 32 (INT32) if the software is running in edition 1 mode, otherwise it is integer 64 (INT64). |
| | | What is the behaviour of the Device by GetAllDataValues? | GetAllDataValues is not supported without functional constraint indication. |

1.13 TICS - Technical Issues Implementation Conformance Statement

1.13.1 TISSUES Edition 1

The implemented TISSUES are only relevant when the Edition Setting is set to Edition 1, otherwise those TISSUES are not relevant for Edition 2.

| Topic | TISSUE No. | Link | Description | Impact of Interoper. |
|------------------|------------|---|---|----------------------|
| Object Directory | 433 | http://tissue.iec61850.com/tissue.aspx?issueid=433 | Order of attributes in specialized CDCs for control service mapping | - |
| | 422 | http://tissue.iec61850.com/tissue.aspx?issueid=422 | Order of extension data objects and data attributes | - |
| | 168 | http://tissue.iec61850.com/tissue.aspx?issueid=168 | Order of attributes in MMS components | - |
| | 141 | http://tissue.iec61850.com/tissue.aspx?issueid=141 | Desc: object reference length extended to 129 | x ¹⁾ |
| Object Model | 120 | http://tissue.iec61850.com/tissue.aspx?issueid=120 | Type - Mod.stVal and Mod.ctlVal | - |
| | 146 | http://tissue.iec61850.com/tissue.aspx?issueid=146 | CtxInt | - |
| | 173 | http://tissue.iec61850.com/tissue.aspx?issueid=173 | Ctl modelling harmonization | - |
| | 234 | http://tissue.iec61850.com/tissue.aspx?issueid=234 | New type CtxInt | x |
| | 75 | http://tissue.iec61850.com/tissue.aspx?issueid=75 | Desc: Str and Op Data Object in GAPC | - |
| Services | 377 | http://tissue.iec61850.com/tissue.aspx?issueid=377 | DeleteDataSet response- | - |
| | 276 | http://tissue.iec61850.com/tissue.aspx?issueid=276 | File Services Negative Responses | - |
| | 183 | http://tissue.iec61850.com/tissue.aspx?issueid=183 | GetNameList error handling | x |
| | 165 | http://tissue.iec61850.com/tissue.aspx?issueid=165 | Improper Error Response for GetDataSetValues | x |
| | 116 | http://tissue.iec61850.com/tissue.aspx?issueid=116 | GetNameList with empty response? | x |

| Topic | TISSUE No. | Link | Description | Impact of Interoper. |
|-----------|---|---|--|----------------------|
| Reporting | 474 | http://tissue.iec61850.com/tissue.aspx?issueid=474 | GI for URCB | - |
| | 453 | http://tissue.iec61850.com/tissue.aspx?issueid=453 | Reporting & Logging model revision | x |
| | 438 | http://tissue.iec61850.com/tissue.aspx?issueid=438 | EntryTime base should be GMT | - |
| | 349 | http://tissue.iec61850.com/tissue.aspx?issueid=349 | BRCB TimeOfEntry has two definitions | x |
| | 348 | http://tissue.iec61850.com/tissue.aspx?issueid=348 | URCB class and report | x |
| | 344 | http://tissue.iec61850.com/tissue.aspx?issueid=344 | TimeOfEntry misspelled | - |
| | 335 | http://tissue.iec61850.com/tissue.aspx?issueid=335 | Clearing of Bufovfl | x |
| | 332 | http://tissue.iec61850.com/tissue.aspx?issueid=332 | Ambiguity in use of trigger options | x |
| | 329 | http://tissue.iec61850.com/tissue.aspx?issueid=329 | Reporting and BufOvl | x |
| | 322 | http://tissue.iec61850.com/tissue.aspx?issueid=322 | Write Configuration attribute of BRCBs | |
| | 301 | http://tissue.iec61850.com/tissue.aspx?issueid=301 | SqNum in Buffered Reports | - |
| | 300 | http://tissue.iec61850.com/tissue.aspx?issueid=300 | Attribute Resv in BRCB | x |
| | 298 | http://tissue.iec61850.com/tissue.aspx?issueid=298 | Type of SqNum | x |
| | 297 | http://tissue.iec61850.com/tissue.aspx?issueid=297 | Sequence number | x |
| | 278 | http://tissue.iec61850.com/tissue.aspx?issueid=278 | EntryId not valid for a server | x |
| | 275 | http://tissue.iec61850.com/tissue.aspx?issueid=275 | Confusing statement on GI usage | x |
| | 191 | http://tissue.iec61850.com/tissue.aspx?issueid=191 | BRCB: Integrity and buffering reports | x |
| | 190 | http://tissue.iec61850.com/tissue.aspx?issueid=190 | BRCB: EntryId and TimeOfEntry | x |
| | 177 | http://tissue.iec61850.com/tissue.aspx?issueid=177 | Ignoring OptFlds bits for URCB | - |
| | 52 | http://tissue.iec61850.com/tissue.aspx?issueid=52 | Ambiguity GOOSE SqNum | x |
| 49 | http://tissue.iec61850.com/tissue.aspx?issueid=49 | BRCB TimeOfEntry? | x | |

| Topic | TISSUE No. | Link | Description | Impact of Interoper. |
|---------------|------------|---|--|----------------------|
| Control Model | 46 | http://tissue.iec61850.com/tissue.aspx?issueid=46 | Synchro check cancel | x |
| | 44 | http://tissue.iec61850.com/tissue.aspx?issueid=44 | AddCause - Object not sel | x |
| | 30 | http://tissue.iec61850.com/tissue.aspx?issueid=30 | control parameter T | x |
| | 520 | http://tissue.iec61850.com/tissue.aspx?issueid=520 | Desc: control canceling at connection loss | - |
| Setting Group | 593 | http://tissue.iec61850.com/tissue.aspx?issueid=593 | Desc: Setting Group Canceling, eding | x |
| File Transfer | 545 | http://tissue.iec61850.com/tissue.aspx?issueid=545 | Files Directories | x |

1) No impact as long as the IED Name and the logical device inst have together a length smaller than 13 char.

1.13.2 TISSUES Edition 2

The following Edition 2 TISSUES have been implemented in the device and are active within the name space of IEC 61850-7-4:2007.

| Topic | TISSUE No. | Link | Description | Impact of Interoper. |
|---------------|------------|---|---|----------------------|
| Object Model | 671 | http://tissue.iec61850.com/tissue.aspx?issueid=671 | Mistake in definition of Mod & Beh | x |
| | 686 | http://tissue.iec61850.com/tissue.aspx?issueid=686 | Desc: New annex H - enums types in XML | x |
| | 722 | http://tissue.iec61850.com/tissue.aspx?issueid=722 | Desc: unit enumeration for min and h | x |
| | 742 | http://tissue.iec61850.com/tissue.aspx?issueid=742 | Desc: GAPC.Str, Op, StrVal are not intanceable | x |
| | 929 | http://tissue.iec61850.com/tissue.aspx?issueid=929 | AC_SCAV presence condition definition | x |
| Configuration | 719 | http://tissue.iec61850.com/tissue.aspx?issueid=719 | ConfDataSet - maxAttributes definition is confusing | x |
| | 823 | http://tissue.iec61850.com/tissue.aspx?issueid=823 | ValKind for structured data attributes | |

2 IEC 61850 Conformance Statements

Contents

This chapter describes conformity with IEC 61850. It does not describe the entire standard but only parts in which there is a choice in the services.

| | | |
|-----|--|----|
| 2.1 | Definitions of the ISO/OSI Reference Model | 28 |
| 2.2 | Definition of the Communication Services Acc. to Standard (PICS) | 29 |
| 2.3 | Model Implementation Conformance Statement (MICS) | 35 |

2.1 Definitions of the ISO/OSI Reference Model

To achieve stable data exchange, all communication is based on the OSI Reference Model (OSI/IEC 7498-1) for a multi-layer communication function. Fig. 2-1 shows the seven layers defined there.




Fig. 2-1 OSI reference model and profiles

This section on using the ISO application (application profile) and transport profiles (T profile) describes the various stack profiles. An ISO application profile is a set of specifications and declarations regarding the top 3 layers of the ISO/OSI reference model (i.e. the application, presentation, and session layers). The T profile is a set of specifications and declarations regarding the lower 4 layers (i.e. transport, network, data link, and physical layers).

A and T profiles can be combined in various ways to form different types of services and information items that can be exchanged. The services specified in Part 7-2 of the IEC 61850 standard are mapped onto 4 different combinations of the profiles. These 4 combinations are used for

- Client/server services,
- GOOSE services,
- Time synchronization,
- Services for sampled measured values.

2.2 Definition of the Communication Services Acc. to Standard (PICS)

The tables in the sections below are specified according to IEC61850 Part 7-2 Annex A.

The descriptions below refer to implementation in the SIPROTEC 4, the SIPROTEC Compact and the Reyrolle IED device range.

The tables give the names stated in the standard.

2.2.1 Profile Compliance

Basic conformance statement

| | | Client/ Subscriber | Server/ Publisher | Value/Comments |
|---|--|-----------------------|----------------------|----------------|
| Client-Server roles | | | | |
| B11 | Server side (of TWO-PARTY-APPLICATION-ASSOCIATION) | -- | Y | |
| B12 | Client side (of TWO-PARTY-APPLICATION-ASSOCIATION) | N | -- | |
| SCSMs supported | | | | |
| B21 | SCSM: IEC 6185-8-1 used | Y | Y | |
| B22 | SCSM: IEC 6185-9-1 used | | | |
| B23 | SCSM: IEC 6185-9-2 used | | | |
| B24 | SCSM: other | | | |
| Generic substation event model (GSE) | | | | |
| B31 | Publisher side | -- | Y | |
| B32 | Subscriber side | Y | -- | |
| Transmission of sample value model (SVC) | | | | |
| B41 | Publisher side | -- | N | |
| B42 | Subscriber side | N | -- | |
| Y = supported N or empty = not supported | | | | |

ACSI models conformance statement

| | | Client/ Subscriber | Server/ Publisher | Value/Comments |
|--|----------------------------------|-----------------------|----------------------|----------------|
| If Server or Client side (B11/12) supported | | | | |
| M1 | Logical device | | Y | |
| M2 | Logical node | | Y | |
| M3 | Data | | Y | |
| M4 | Data set | | Y | |
| M5 | Substitution | | N | |
| M6 | Setting group control | | Y | |
| | Reporting | | | |
| M7 | Buffered report control | | Y | |
| M7-1 | sequence-number | | Y | |
| M7-2 | report-time-stamp | | Y | |
| M7-3 | reason-for-inclusion | | Y | |
| M7-4 | data-set-name | | Y | |
| M7-5 | data-reference | | Y | |
| M7-6 | buffer-overflow | | Y | |
| M7-7 | entryID | | Y | |
| M7-8 | BufTim | | Y | |
| M7-9 | IntgPd | | Y | |
| M7-10 | GI | | Y | |
| M7-11 | conf-revision | | Y | |
| M8 | Unbuffered report control | | Y | |
| M8-1 | sequence-number | | Y | |
| M8-2 | report-time-stamp | | Y | |
| M8-3 | reason-for-inclusion | | Y | |
| M8-4 | data-set-name | | Y | |
| M8-5 | data-reference | | Y | |
| M8-6 | BufTim | | Y | |
| M8-7 | IntgPd | | Y | |
| M8-8 | GI | | Y | |
| M8-9 | conf-revision | | Y | |
| | Logging | | N | |
| M9 | Log control | | N | |
| M9-1 | IntgPd | | N | |
| M10 | Log | | N | |
| M11 | Control | | Y | |

20

| | | Client/ Subscriber | Server/ Publisher | Value/Comments |
|---|----------------------|-----------------------|----------------------|----------------|
| If GSE (B31/32) is supported | | | | |
| M12 | GOOSE | Y | Y | |
| M13 | GSSE | N | N | |
| If SVC (41/42) is supported | | | | |
| M14 | Multicast SVC | N | N | |
| M15 | Unicast SVC | N | N | |
| If Server or Client side (B11/B12) supported | | | | |
| M16 | Time | Y | N | |
| M17 | File Transfer | N | Y | |
| Y = supported N or empty = not supported | | | | |

ACSI service conformance statement

| | Services | AA: TP/MC | Client (C) | Server (S) | |
|--------------------------------|--------------------------------|-----------|------------|------------|--|
| Server | | | | | |
| S1 | GetServerDirectory | TP | N | Y | |
| Application association | | | | | |
| S2 | Associate | TP | N | Y | |
| S3 | Abort | TP | N | Y | |
| S4 | Release | TP | N | Y | |
| Logical device | | | | | |
| S5 | GetLogicalDeviceDirectory | TP | N | Y | |
| Logical Node | | | | | |
| S6 | GetLogicalNodeDirectory | TP | N | Y | |
| S7 | GetAllDataValues | TP | N | Y | |
| Data | | | | | |
| S8 | GetDataValues | TP | N | Y | |
| S9 | SetDataValues | TP | N | Y | |
| S10 | GetDataDirectory | TP | N | Y | |
| S11 | GetDataDefinition | TP | N | Y | |
| Data set | | | | | |
| S12 | GetDataSetValues | TP | N | Y | |
| S13 | SetDataSetValues | TP | N | N | |
| S14 | CreateDataSet | TP | N | Y | |
| S15 | DeleteDataSet | TP | N | Y | |
| S16 | GetDataSetDirectory | TP | N | Y | |
| Substitution | | | | | |
| S17 | SetDataValues | TP | N | N | |
| Setting group control | | | | | |
| S18 | SelectActiveSG | TP | N | Y | |
| S19 | SelectEditSG | TP | N | N | |
| S20 | SetSGValues/ SetEditSGValue | TP | N | N | |
| S21 | ConfirmEditSGValues | TP | N | N | |
| S22 | GetSGValues/ GetEditSGValue | TP | N | N | |
| S23 | GetSGCBValues | TP | N | Y | |

| | Services | AA: TP/MC | Client (C) | Server (S) | |
|---|-----------------------|-----------|------------|------------|--|
| Reporting | | | | | |
| Buffered report control block (BRCB) | | | | | |
| S24 | Report | TP | N | Y | |
| S24-1 | data-change (dchg) | | N | Y | |
| S24-2 | qchg-change (qchg) | | N | Y | |
| S24-3 | data-update (dupd) | | N | Y | |
| S25 | GetBRCBValues | TP | N | Y | |
| S26 | SetBRCBValues | TP | N | Y | |
| Unbuffered report control block (URCB) | | | | | |
| S27 | Report | TP | N | Y | |
| S27-1 | data-change (dchg) | | N | Y | |
| S27-2 | qchg-change (qchg) | | N | Y | |
| S27-3 | data-update (dupd) | | N | Y | |
| S28 | GetURCBValues | TP | N | Y | |
| S29 | SetURCBValues | TP | N | Y | |
| Logging | | | | | |
| Log control block | | | | | |
| S30 | GetLCBValues | TP | N | N | |
| S31 | SetLCBValues | TP | N | N | |
| Log | | | | | |
| S32 | QueryLogByTime | TP | N | N | |
| S33 | QueryLogAfter | TP | N | N | |
| S34 | GetLogStatusValues | TP | N | N | |
| Generic substation event model (GSE) | | | | | |
| GOOSE-CONTROL-BLOCK | | | | | |
| S35 | SendGOOSEMessage | MC | Y | Y | |
| S36 | GetReference | TP | N | N | |
| S37 | GetGOOSEElementNumber | TP | N | N | |
| S38 | GetGoCBValues | TP | N | Y | |
| S39 | SetGoCBValues | TP | N | Y | |
| GSSE-CONTROL-BLOCK | | | | | |
| S40 | SendGSSEMessage | MC | N | N | |
| S41 | GetReference | TP | N | N | |
| S42 | GetGSSEElementNumber | TP | N | N | |
| S43 | GetGsCBValues | TP | N | N | |
| S44 | SetGsCBValues | TP | N | N | |

2.2 Definition of the Communication Services Acc. to Standard (PICS)

| | Services | AA: TP/MC | Client (C) | Server (S) | |
|---|-----------------------------------|-----------|------------|---------------------|--|
| Transmission of sample value model (SVC) | | | | | |
| Multicast SVC | | | | | |
| S45 | SendMSVMessage | MC | N | N | |
| S46 | GetMSVCBValues | TP | N | N | |
| S47 | SetMSVCBValues | TP | N | N | |
| Unicast SVC | | | | | |
| S48 | SendUSVMessage | TP | N | N | |
| S49 | GetUSVCBValues | TP | N | N | |
| S50 | SetUSVCBValues | TP | N | N | |
| Control | | | | | |
| S51 | Select | TP | N | N | |
| S52 | SelectWithValue | TP | N | Y | |
| S53 | Cancel | TP | N | Y | |
| S54 | Operate | TP | N | Y | |
| S55 | Command-Termination | TP | N | Y | |
| S56 | TimeActivated-Operate | TP | N | N | |
| File transfer | | | | | |
| S57 | GetFile | TP | N | Y | |
| S58 | SetFile | TP | N | N | |
| S59 | DeleteFile | TP | N | N | |
| S60 | GetFileAttributeValues | TP | N | Y | |
| Time | | | | | |
| T1 | Time resolution of internal clock | | | 10 (1 ms) | nearest negative power of 2 in seconds |
| T2 | Time accuracy of internal clock | | | | T0 |
| | | | | ClassT1 | T1 |
| | | | | | T2 |
| | | | | | T3 |
| | | | | | T4 |
| | | | | | T5 |
| T3 | Supported TimeStamp resolution | - | | 10 (approx. 0.9 ms) | nearest negative power of 2 in seconds |
| Y = supported N or empty = not supported | | | | | |

2.3 Model Implementation Conformance Statement (MICS)

Content of the statement

This statement contains the description of all objects that are provided by a device and is especially important if devices are connected to a central system that supplies data to certain applications via the objects provided by the device.

In the case of SIPROTEC 4 or SIPROTEC Compact or Reyrolle IEDs, this document depends on both the device type and the defined user objects and can therefore not be a permanent part of the manual. It is therefore generated from DIGSI.

Generation in DIGSI 4

Generation is selected in the device processing via menu items *File* → *Export* → *IEC 61850 System Interface for Documentation (PDF)*. The dialog that opens let you enter a device-related, editable filename under which the MICS document to be generated will be stored.

The document is generated with the correct version and device type data. It shows the assignment lists of the devices to IEC 61850 and vice versa. The whole document is shown in a hyperlinked table of contents. The MICS is a readable form of the current mapping of a device on IEC 61850.

