



MCCZ2.MH26134 Controls, Primary Safety - Component

[Page Bottom](#)

Controls, Primary Safety - Component

[See General Information for Controls, Primary Safety - Component](#)**SIEMENS AG**

MH26134

Ic Bt Cps

BERLINER RING 23

76437 Rastatt, GERMANY

Combustion detector bases, Model(s) AGM410490500, AGM410490550**Combustion detectors**, Model(s) RAR, followed by 7, 7(1), 8 or 8(1), QRA2(1), QRA2, QRA2.9, QRA2.9(1), QRA2M, QRA2M(1), QRA4.U, QRA4M.U, QRA10, QRA10.C, QRA10M, QRA10M.C, or QRB followed by 1A, 1B, 3, 3(1), 3S or 3S(1) all with or without a suffix.**Primary safety controls**, Model(s) LAL2.14, LAL2.25, LAL2.65, LAL3.25, LFL1.122, LFL1.133, LFL1.322, LFL1.333, LFL1.335, LFL1.622, LFL1.635, LFL1.638

LME, followed by 7, followed by 0, 1, 2, 3 or 4, followed by 0 thru 9, followed by a suffix, followed by A1, may be followed by two digits, with program module PME followed by 7, followed by 0, 1, 2, 3 or 4, followed 0 thru 9, with a two digit suffix, followed by A1, followed by a suffix, with Combustion Detector QRA2, QRA4, QRA10 or QRB, may be followed by suffixes, with optional Display Module AZL followed by 21, 22 or 23, followed by 00 or 10, followed by A thru Z, may be followed by 0 thru 9, may be followed by two digits.

LME, followed by 8, followed by 0 thru 9, followed by 0, 1, 2, 3 or 4, followed by a suffix, followed by A1, may be followed by two digits, with program module PME followed by 7, followed by 0, 1, 2, 3 or 4, followed 0, 1, 2, 3 or 4, with a two digit suffix, followed by A1, followed by a suffix, with Combustion Detector QRA2, QRA4, QRA10 or QRB, may be followed by suffixes, with optional Display Module AZL, followed by 21, 22 or 23, followed by 00 or 10, followed by A thru Z, may be followed by 0 thru 9, may be followed by two digits.

LMO88.530A1RL, LMO88.620C1RL

LMV, followed by 37, followed by 4 or 5, followed by 10 or 20, followed by A thru Z, followed by 1, followed by two digits, with Combustion Detector+ QRA2, QRA4, QRA10 or QRB, with optional suffixes, with optional Display Module AZL, followed by 21, 22 or 23, followed by 00 or 10, followed by A thru Z, may be followed by 0 thru 9, may be followed by two digits, with optional Actuator SQM33, followed by 41, 51, 52, 55, 61, 65, 71 or 75, followed by 0, 1, 8 or 9, followed by A, followed by 9, with optional additional suffix.

LMV36.520, followed by A1, with Combustion Detector+ QRA2, QRA4, QRA10 or QRB, may be followed by suffixes, with optional Display Module AZL, followed by 21, 22 or 23, followed by 00 or 10, followed by A thru Z, may be followed by 0 thru 9, may be followed by two digits; with optional Actuator SQM33, followed by 41, 51, 52, 55, 61, 65, 71 or 75, followed by 0, 1, 8 or 9, followed by A, followed by 9, may be followed by additional suffix; with optional Fuel Switch AGM60.

LMV37.820, followed by A1, with optional Display Module AZL followed by 21, 22 or 23, followed by 00 or 10, followed by A thru Z, may be followed by 0 thru 9, may be followed by two digits, with optional Actuator SQM33, followed by 41, 51, 52, 55, 61, 65, 71 or 75, followed by 0, 1, 8 or 9, followed by A, followed by 9, with optional additional suffix.

LMV51, followed by 0, 1 or 3; LMV52 followed by 2 or 4; followed by 00 or 40, followed by A thru Z, followed by 1, followed by a two digit suffix, with Combustion Detector+ QRI, followed by 2, followed by A or B, followed by a two digits, followed by A, B or C, followed by 1.

PLL52, with QG020 and/or AGG5.310 or AGG5.315 speed sensor for use with LMV52 series controls.

QRA7, followed by 3 or 5, followed by .A17, with Transformer AGG 5.2X with optional Display module AZL, followed by 51, 52 or 53, followed by 00 or 40, followed by A thru Z, may be followed by 1 or 4, followed by a two digits, with optional Actuator SQM4, followed by 5 or 8, followed by 2, 4 or 6, followed by 9, followed by 1, 5 or 7, followed by A, followed by 9, followed by a two digits, with optional Actuator SQM91 followed by 3 or 5, followed by 91, followed by A, followed by 9.

+ - May also be used in conjunction with R/C(MCCZ2) GN Electronics 5002-01 or 5002-01NC UV flame scanner.

Marking: Company name and model designation.

[Last Updated](#) on 2015-02-16[Questions?](#)[Print this page](#)[Terms of Use](#)[Page Top](#)

© 2015 UL LLC

The appearance of a company's name or product in this database does not in itself assure that products so identified have been manufactured under UL's Follow-Up Service. Only those products bearing the UL Mark should be considered to be Certified and covered under UL's Follow-Up Service. Always look for the Mark on the product.

UL permits the reproduction of the material contained in the Online Certification Directory subject to the following conditions: 1. The Guide Information, Assemblies, Constructions, Designs, Systems, and/or Certifications (files) must be presented in their entirety and in a non-misleading manner, without any manipulation of the data (or drawings). 2. The statement "Reprinted from the Online Certifications Directory with permission from UL" must appear adjacent to the extracted material. In addition, the reprinted material must include a copyright notice in the following format: "© 2015 UL LLC".