



NK8000  
MP4.80

## Product Datasheet

### NK8021 Analog Modem

- V24/V28 Serial Interface Modem compatible to the following standards: V.90, V.34+, V.34, V.32bis, V.32, V.22bis, V.22, V.21
- Provides backup dial-up connection (secondary connection) from NK8000 Ethernet Port units to Management Stations if primary IP network is down
- Provides primary dial-up connection from NK8000 Ethernet Port units to Management Stations if no IP network is present
- Automatically detects the correct modulation scheme – V.90 in multistandard mode

## Technical data

### Features

Mountable in NE8001 cabinets using holder brackets (included)



- Multistandard modem V.90, V.34+, V.34, V.32bis, V.32, V.22bis, V.22, V.21
- Line speeds (bps): 300 – 33600
- DTE Autospeed up to 115200 bps
- Asynchronous format 8, 9, 10, 11 bit
- Data compression according to MNP5 and V.42 bis
- V54 diagnostics
- AT command set
- Pan European CTR21 approval
- DTMF and pulse dialling
- Automatic answering
- Upgradeable firmware on Flash memory
- Error correction according to MNP2-4 and ITU-T V.42

### Connectors

- 4-pin screw terminal connector for power supply
- 10-pin screw terminal connector for RS232 line or via included cable with D-Sub 9 pin, male type (cable length 30cm)

### Power Supply

Input voltage	12Vdc
Input current	200mA

### Environmental limits

- Operation: +0 ... +45 °C  
 Humidity: 20 ... 80%, non condensing  
**Caution:** Avoid rapid changes in temperature / humidity (0.03°C/min)  
**Note:** This equipment, including cables, should be installed in an area free from:
- Dust, humidity, heat from direct sun light.
  - Objects which irradiate heat. These could cause damage to the container or other problems.
  - Objects which produce a strong electromagnetic field (loudspeakers, etc.)
  - Liquids or chemical corrosive substances.

### Dimensions

Modem provided with metallic plate	100(W) x 150(H) x 18(D)
------------------------------------	-------------------------

### Weight

Modem and plate	0.186kg
-----------------	---------

### Approval

CE

### Disposal



This device includes electrical and electronic components and must not be disposed of as domestic waste. **Current local legislation must be observed.**

### Related documentation

<b>NE8000 Datasheet</b>	Sales material binder Section 2	Document no.: A6V10062421	NE8001 Housing Solutions for NK822x
<b>NK8000 Technical manual</b>	Technical material binder Section 2	Document no.: A6V10062437	NK8000 Installation, Function & Configuration, Commissioning, Safety Regulations

## Ordering information

---

<b>NK8021 Analog modem</b>	A6E600245	NK8021	Analog modem for public switched telephone network (PSTN)
----------------------------	-----------	--------	---

---

## Related Products

---

<b>NK8231</b>	CEI Interface	S54461-C5-A1	NK8231.2	<ul style="list-style-type: none"><li>– 1 Ethernet line for remote host</li><li>– 2 serial lines for subsystems / modem</li></ul>
<b>NK8232</b>	Ethernet port for a single subsystem	S54461-C2-A3	NK8232.2	<ul style="list-style-type: none"><li>– 2 Ethernet lines for remote host</li><li>– 2 serial lines for a single subsystem / local host / modem</li></ul>
<b>NK8235</b>	Ethernet port	S54461-C2-A1	NK8235.2	<ul style="list-style-type: none"><li>– 2 Ethernet lines for remote host</li><li>– 2 serial lines for subsystems / modem</li></ul>
		S54461-C2-A2	NK8235.4	<ul style="list-style-type: none"><li>– 2 Ethernet lines for remote host</li><li>– 4 serial lines for subsystems / modem</li></ul>
<b>NE8000</b>	NE8001	A6E600066	Wall-mountable, metallic cabinet with DIN-rail	The unit includes a pre-wired power supply unit Input: 220Vac; output: 12Vdc 3A

---

Issued by:

Siemens Switzerland Ltd  
Building Technologies Division  
International Headquarters  
Gubelstrasse 22  
CH-6301 Zug  
Tel. +41 41-724 24 24  
[www.siemens.com/buildingtechnologies](http://www.siemens.com/buildingtechnologies)

© 2015 Copyright by  
Siemens Switzerland Ltd

Data and design subject to change without notice.  
Supply subject to availability.