


Meter/Load Center Combinations


FEATURES

- UL Listed only for use as service entrance equipment
- Overhead and underground feed
- Side hinged door, only one screw required to remove door
- Captive deadfront screw
- 22K AIC rating
- Meter socket jaw guides provided on ringless devices
- Ring and ringless versions available
- 5th jaw option available
- Surface mount
- NEMA Type 3R enclosure with painted, G90 galvanized steel Alstan[®] tin-plated aluminum bus bars
- Horn bypass available
- Uses Type RX hubs



Knockout Code

- | | |
|---|----------------------------------|
| A | = 1/2" |
| B | = 1/2", 3/4", 1" |
| C | = 3/4", 1", 1-1/4" |
| D | = 1, 1-1/4", 1-1/2" |
| E | = 1-1/2", 2", 2-1/2" |
| F | = 1", 1-1/4", 1-1/2", 2", 2-1/2" |
| G | = 1-1/4", 1-1/2", 2", 2-1/2", 3" |



| Meter Socket Ampere Rating | Catalog Number | Max. 1" Spaces | Max. Circuits | Phase | Main Ampere Rating | Number of Jaws | Type of Bypass | Type of Cover |
|----------------------------|----------------|----------------|---------------|--------|--------------------|----------------|----------------|---------------|
| 200 | MC2040B1150R | 20 | 40 | Single | 150 | 4 | None | Ringless |
| 200 | MC2040B1200R | 20 | 40 | Single | 200 | 4 | None | Ringless |
| 200 | MC2040B1150 | 20 | 40 | Single | 150 | 4 | None | Ring |
| 200 | MC2040B1200 | 20 | 40 | Single | 200 | 4 | None | Ring |

Family Type J

fastfax

SIEMENS

Siemens Energy & Automation, Inc. • 3333 Old Milton Parkway, Alpharetta, GA 30005 • 1-800-964-4114 • www.sea.siemens.com/reselec

©2004 Siemens Energy & Automation, Inc. All Rights Reserved.

Siemens is a registered trademark of Siemens AG. Product names mentioned may be trademarks or registered trademarks of their respective companies. Specifications are subject to change without notice