



**SIEMENS**  
*Ingenuity for life*

# Medium-voltage air-insulated switchgear



## GM-SG, non-arc-resistant, 5 kV-15 kV, up to 63 kA drawout, metal-clad

### Features and benefits:

- One-high or two-high construction
- Up to 100 full-fault interruptions
- Universal spare circuit breaker for 50 kA and lower ratings
- Universal spare circuit breaker for 63 kA ratings
- Interlocks permit insertion of higher rated vacuum circuit breaker into lower rated cell but not vice versa
- Closed door racking
- Front accessible circuit breaker operating mechanism for ease of maintenance
- Floor rollout circuit breaker in lower cell without a dolly
- Visible secondary disconnect
- Circuit breaker ships inside of cell, thus reducing installation cost and transit damage
- Pair with Siemens protective relays to match any typical application
- Horizontal drawout type MSGG vacuum circuit breaker with type 3AH3 operating mechanism
- Uses the latest developments in vacuum interrupter technology
- Highly reliable vacuum interrupters - MTTF over 50,000 years
- Common type 3AH3 operator platform for all ratings
- Over 120,000 type 3AH3 operators produced since 1998
- Generator circuit breakers (to IEEE C37.013 optionally available)
- 10,000 operations to overhaul
- Three-cycle interrupting time (optional)
- SIERS integrated electrical-racking system available (optional)
- Optional Sm@rtGear™ functionality provides predictive diagnostics, continuous monitoring, and control from a remote location
- Meets or exceeds the latest ANSI, IEEE and NEMA standards
- UL or C-UL Listing available.

### Type GM-SG switchgear available as:


- Indoor (type GM-SG)
- Outdoor walk-in Shelter-Clad NEMA 3R (type SGM-SG)
  - Single-aisle (factory-assembled aisle)
  - Factory insulated and assembled aisle (optional)
- Outdoor walk-in Shelter-Clad+ factory-assembled switchgear and aisle on common base with power equipment center type options (type S+GM-SG)
- Outdoor, aisleless non-walk-in (type OGM-SG).

Type GMSG circuit breaker ratings constant kA basis - ANSI/IEEE C37.06-2009

Maximum design voltage kV	Rated interrupting rating kA	Maximum interrupting and short time kA	Voltage range factor	Continuous current <sup>1</sup> A rms	Withstand voltage levels		Closing and latching (momentary)	
					Power frequency kV rms	Lightning Impulse (BIL) kV peak	Asymmetrical (1.55 x I) kA rms	Peak (2.6 x I) kA peak
4.76	40	40	1.0	1,200, 2,000, 3,000	19	60	62	104
4.76	50	50	1.0	1,200, 2,000, 3,000	19	60	78	130
4.76	63	63	1.0	1,200, 2,000, 3,000	19	60	98	164
8.25	40	40	1.0	1,200, 2,000, 3,000	36	95	62	104
15.0	25	25	1.0	1,200, 2,000	36	95	39	65
15.0	40	40	1.0	1,200, 2,000, 3,000	36	95	62	104
15.0	50	50	1.0	1,200, 2,000, 3,000	36	95	78	130
15.0	63	63	1.0	1,200, 2,000, 3,000	36	95	98	164

Dimensions in inches (mm)

Type	Height (H)	Width (W)	Depth (D)	Drawout aisle (DA)
GM-SG	95.3 (2,419)	36.0 (914)	98.7 (2,507) <sup>4</sup>	72.0 (1,829) recommended <sup>6</sup>
SGM-SG <sup>7</sup>	114.8 (2,915)	36.0 (914) <sup>2</sup>	173.4 (4,404) <sup>5</sup>	72.0 (1,829) included
OGM-SG	113.6 (2,886)	36.0 (914) <sup>2</sup>	101.9 (2,588) <sup>5</sup>	72.0 (1,829) recommended <sup>6</sup>



Footnotes:

1. 4,000 A fan-cooled rating available using a 3,000 A circuit breaker together with a modified switchgear structure incorporating fan-cooling equipment.
2. Add 6" (152 mm) to each end of lineup for aisle extension 12" (304 mm) total.
3. Dimensions are approximate size of floor footprint. For outdoor equipment, enclosure overhangs floor frame. Refer to Footnote 5.
4. If indoor switchgear is installed on a raised housekeeping pad, the pad must not extend further than 3" (75 mm) from the front of the switchgear to avoid interference with the use of the portable lift truck.

<sup>5</sup>. Add for roof and enclosure overhang:

- Rear:
- Non-walk-in: 3.6" (92 mm)
  - Shelter-Clad: 3.6" (92 mm).
- Front (drawout aisle):
- Non-walk-in: 3.7" (94 mm)
  - Shelter-Clad: 1.7" (43 mm).
- <sup>6</sup>. 72.0" (1,829 mm) aisle space recommended and allows room for interchange of circuit breakers. Minimum aisle space required for handling circuit breakers with lift truck is 65" (1,651 mm). Minimum aisle space required if all circuit breakers are at floor level is 55" (1,397 mm).

<sup>7</sup>. Shelter-Clad+ switchgear assemblies (type S+GM-SG) are built in partnership with Siemens-qualified vendors, who provide detailed drawings of each custom assembly which include dimensions and weights.

Published by Siemens Industry, Inc. 2017.

Siemens Industry  
7000 Siemens Road  
Wendell, North Carolina 27591

For more information, please contact our Customer Support Center.  
Phone: +1 (800) 333-7421

[www.usa.siemens.com/mvswitchgear](http://www.usa.siemens.com/mvswitchgear)

Article No. EMMS-B40095-00-4AUS

Printed in U.S.A.

© 2017 Siemens Industry, Inc.

The technical data presented in this document is based on an actual case or on as-designed parameters, and therefore should not be relied upon for any specific application and does not constitute a performance guarantee for any projects. Actual results are dependent on variable conditions. Accordingly, Siemens does not make representations, warranties, or assurances as to the accuracy, currency or completeness of the content contained herein. If requested, we will provide specific technical data or specifications with respect to any customer's particular applications. Our company is constantly involved in engineering and development. For that reason, we reserve the right to modify, at any time, the technology and product specifications contained herein.