



**TIME-CURRENT CHARACTERISTIC CURVE  
I-T-E® CIRCUIT BREAKER**

**TYPE BQCH** **2 & 3 POLES**

For application and coordination purposes only. Based on 40°C ambient cold start. Connected with four (4) feet of rated wire (60/75°C) per terminal. Tested in open air with current in all poles.

**MAXIMUM VOLTS**

| BREAKER TYPE | AC VOLTS         |
|--------------|------------------|
| BQCH         | 60 Hz<br>277/480 |

**BREAKER RATING**

| CONTINUOUS AMPERES | INSTANTANEOUS TRIP, AMPERES |
|--------------------|-----------------------------|
| 15-100             | See Curve                   |

**INTERRUPTING RATING (UL Listed)**

| BREAKER TYPE | SYMMETRICAL RMS AMPERES |               |
|--------------|-------------------------|---------------|
|              | 240 VOLTS               | 277/480 VOLTS |
| BQCH         | 65,000                  | 14,000        |