


NOTES:

1. PEDESTAL IS FABRICATED FROM 14 GAUGE GALVANIZED STEEL
2. PANELBOARD ENCLOSURE IS FABRICATED FROM 16 GAUGE GALVANIZED STEEL
3. PAINT: GRAY
4. BREAKER COMPARTMENT COVER IS HINGED AT TOP AND LOCKS INTO OPEN POSITION
5. 120/240 VAC, 200 AMP, 1 PHASE, 3 WIRE
6. LOAD TERMINALS ARE RATED FOR 60° C OR 75° C CONDUCTOR
7. SIEMENS ACCEPTABLE BREAKER TYPES:
15-100A "QP"
8. ORDER MPEXT FOR DIRECT BURIAL KIT.
ORDER MPFLANGE FOR PAD MOUNTING KIT.



UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES

TOLERANCES:
.XX
.XXX
HOLE DIAMETER
ANGULAR
UNDIMENSIONED 90° ANGLES

-CONFIDENTIAL-PROPERTY OF
Siemens Industry Inc.
Building technologies division

SKT/BKR/PED 200A 1P

DWN	MAF	DATE 5/24/2011
CHK		DATE
APVD		DATE

SIZE B	ISSUE RELEASE NO.	DWG NO. MP0406B1200RB	REV
SCALE	DO NOT SCALE DRAWING	SHEET 1 OF 1	

4/10/2013	REVISED PER 2013-015	RB
2/10/2012	REVISED PER 2011-023	KP