



TEL (915) 590-8500
FAX (915) 590-8510

6.125"

.125" rcr
X4

SIEMENS

Cat. No. HNF661J Non-Fusible 6 Pole Heavy Duty Safety Switch Type VB II
30 Amps Maximum 600 Volts AC (V~) Maximum 250 Volts DC (V---) Maximum
Type 3R / 3S / 12 / 13 Dust-Tight

For 3R / 3S service, remove drain plug from enclosure bottom and tilt 1/2 to 1 degree towards drain.

Horsepower Ratings	240 VAC ¹ 1Ø	240 VAC 3Ø	480 VAC ¹ 1Ø	480 VAC 3Ø	600 VAC ¹ 1Ø	600 VAC 3Ø	250 VDC ¹
Max. HP	5	10	7½	20	10	30	5

Suitable for use as service equipment in the U.S.A. when neutral kit **HN612** or ground lug kit **HG61234** is installed.

Fuse and Short Circuit Information

This switch is suitable for use on a circuit capable of delivering not more than 200,000 amperes, RMS symmetrical, 600 volts maximum when protected by class J, R or T fuses rated 30 amperes maximum.

Danger – Unless Type NEB or NGB circuit breakers or Class J, R or T fuses are used to protect this switch, it may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes, RMS symmetrical.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, RMS symmetrical, 600 volts maximum, when protected by Class K fuses, Class H fuses or a UL Listed Circuit Breaker rated for 10,000 amperes, RMS symmetrical, 600 volts maximum.

This switch is suitable for use on a circuit capable of delivering not more than 18,000 amperes, rms symmetrical up to 480 VAC, when protected by Type NEB or NGB circuit breakers rated 30 amperes maximum.

This switch is suitable for use on a circuit capable of delivering not more than 10,000 amperes, 250 volts DC maximum, when protected by fuses marked with an interrupting rating of 10,000 amperes, 250 volts DC.

Danger – Unless fuses marked for an interrupting rating of 10,000 amperes at 250 volts DC are used to protect this switch, this switch may present a risk of fire and injury to persons if installed on circuits capable of delivering more than 10,000 amperes.

⚠ DANGER

Hazardous voltage.
Will cause death or serious injury.

- Disconnect and lock out power supplying this switch before working on this switch.
- Turn off switch before removing or installing fuses if so equipped.
- Always use a properly rated voltage sensing device on all fuse clips (Fusible) or all load side terminals (Non-Fusible) to confirm switch is off.
- Close or replace cover before turning power on.

11.375"

Terminal & Wire Information

USE 60°C / 75°C COPPER OR ALUMINUM WIRE

Terminal & Wire Information			
Description	Wire Range	Wire Tightening Torque ⁵	Lug Mounting Torque ⁵
Line, Load & Main Neutral	14-6 AWG	35 lb-ins. 14-10 AWG / 40lb-ins. 8 AWG 45 lb-ins. 6-4 AWG	24 lb-ins.
Ground	14-4 AWG	35 lb-ins. 14-10 AWG / 40lb-ins. 8 AWG 45 lb-ins. 6-4 AWG	24 lb-ins.

UL Listed Compression Lugs (Refer to manufacturers instructions for proper installation)⁶

Wire Size (AWG OR kcmil)	Burndy		Thomas & Betts		IlSCO	
	Cu Only	Cu / Al	Cu Only	Cu / Al	Cu Only	Cu / Al
14 - 10				60096 60097		
8	YA8C-L Box YA8C-L1 Box		54104 54130	60101 60102 61102	CRA-8	ACL - 8 ACN - 8
6				61107		

Inspection record number:

Accessories

Aux. Switch (1NO - 1NC)	HA161234	Compression Lug Neutral Barrier Kit	HCL612	Isolated Ground Lug Kit	HG261234
Aux. Switch (2NO - 2NC)	HA261234	Neutral	HN612	Wire Grip Kit (CU)	HLC612
Low Voltage Aux. Sw. (1NO - 1NC)	HA361234	Ground Lug Kit (Wire Range 14-4 AWG)	HG61234	Hub Kits	SSH100 (1")

Replacement Parts

Line Base	HNB612	Wire Grip Kit (Al)	HL612	Handle / Handle Guard	HH461234
Load Base		Mechanism		Door	HNF661JDOOR

Protected by one or more of the following US Patents: 6,134,979, 6,356,460, 5,945,650, 5,990,439.

¹ Use outer two poles.

⁵ When tightening or replacing connectors, refer to lug mounting torque in Terminal & Wire Information Table.

⁶ If compression lugs are used for the neutral, order compression lug neutral barrier kit **HCL612**.

For questions on this device please call 1-800-241-4453

Siemens Industry, Inc.
 Norcross, GA 30092 USA
<http://www.usa.siemens.com/powerdistribution>
 Assembled in Mexico

Pc. No. 500448AF04
0904

COMPANY NAME

SIEMENS INDUSTRY, INC.

JOB WILL NOT BE PRINTED UNLESS APPROVED BY CUSTOMER.

THIS DOCUMENT IS THE PROPERTY OF LABELTECH, INC. IT'S USE IS AUTHORIZED ONLY FOR RESPONDING TO A REQUEST FOR QUOTATION OR FOR THE PERFORMANCE OF WORK REQUESTED FROM LABELTECH, INC. ALL QUESTIONS MUST BE REFERRED TO THE LABELTECH, INC. PRODUCTION DEPARTMENT.

MATERIAL

Synthetic Paper

INK COLORS

BLACK

185 RED

SIZE

WIDTH

6.125"

LENGTH

11.375"

ROUND CORNER RADIUS

.125"

OK TO PRINT AS IS

MAKE CORRECTIONS, RESUBMIT CORRECTED PROOF

OK TO PRINT WITH CORRECTIONS AS MARKED

PART NO.

500448AF04

DESCRIPTION:

Label

AUTHORIZED BY

DATE

REVISION LEVEL 38P

DESIGNER

Gibran Camacho

CHECKED BY

DATE

08/09/11