

FOR USE ON SERIES 5 OR 6 DISTRIBUTION SECTIONS, CDP-5, CDP-6, VB-5, VB-6, FCI, FCII, SB1, SB2 & SB3.


31-1153-01 Rev. 3

Apvd SH 5-17-88	ITEM	DESCRIPTION	PC. NO.	QTY.			
	1	E2-4-6 AC-PHASE BRANCH BUS	11-7140-01	2			
	2	E2-4-6 B-PHASE BRANCH BUS	11-7141-01	1			
	3	E2-4-6 LINE CONNECTOR	11-7138-01	3			
	4	INTERPHASE BARRIER	15-7505-01	2			
	5	E2-4-6 MOUNTING BRACKET	15-B-3016-02	2			
	6	3.750 E2-4-6 COVER PLATE	12-6024-01	1			
	7	CIRCUIT I. D. CARD	11-7505-01	2			
	8	CARD HOLDER	11-7506-01	2			
	9	1/4-20 X 3/8 SHWHSW	11-1553-02	6			
	▲ 10	STRAP BUS HARDWARE KIT	11-B-2022-05	1			
	11	10-24 X 5/8 ISHOWSW	11-1576-07	12			
	12	8-32 X 4-3/16 SRHSW	11-1510-15	6			
	13	1/4-20 X 5/8 SHWHSW	11-1553-06	4			
	14	NEUTRAL LUG ASSEMBLY	12-B-2105-02	1			
	15						
	16	BLANK FILLER	12-5531-09	2			
	17						
	18						
	19						
	20						
	21						
	22						
	23						
	24						
	25						
	26						
	27	SERIES 5 CONVERSION KIT	11-5570-01	1			
	28	INSTRUCTION SHEET	31-1153-01	1			
	29	CARTON LABEL	15-A-1027-01	1			
	30	CARTON	48001056	1			
	31						
	32						
	33						
	34						
	35						
	36	THIS ASSY. USED ON STRAP KIT NO. 6CLE2					
	37	FOR TYPE CLE, CLE-A, CEd6 BREAKERS ▲					
	38	15-125 AMPERE					
	39						
	40						
	41						
	42						
	43						
	44	MERCHANDISE KIT NO. CEd6					
Revisions 0: 1B-908 1: 1C-831A 4-12-04 2: 1C-831B 7-25-06 3: 1E-166B 12-11-09	Chk SH 5-17-89	By RAW 5-17-89	Confidential - property of Siemens Industry, Inc. Norcross, GA	CED6 BRANCH BREAKER MOUNTING SERIES 5 & 6 COPPER BRANCH BUS	11-5068-05 Dwg No.	Sht. 1 Of 1	3 Rev.

IF EXISTING EQUIPMENT IS TYPE CDP-5, VB-5, OR FC20 THE VERTICAL BUS WILL BE PRE-PUNCHED WITH .406 DIAMETER HOLES, IN THESE CASES USE SERIES 5 ADAPTOR KIT FURNISHED WITH THIS KIT. SEE REVERSE SIDE FOR INSTRUCTIONS.

Siemens Industry, Inc.
Norcross, GA

CAT. NO. **6CLE2**



FOR USE WITH CLE-6 FRAME ON SERIES 5 OR 6 DISTRIBUTION SECTIONS, CDP-5, CDP-6, VB-5, VB-6, FCI, FCII, SB1, SB2 & SB3.

Apvd DSH 6-15-92	ITEM	DESCRIPTION	PC. NO.	QTY.			
	1	5/16 INSERT	11-1620-04	6			
	2	5/16 FLAT WASHER	11-1615-06	6			
	3	5/16 LOCK WASHER	11-1618-04	6			
	4	5/16-18 X 1 1/4 HHMS	11-1566-07	6			
	5	FAST LATCH SCREW BAG	11-A-1821-01	1			
	6 ▲	ID CARD	31-1160-01	1			
	7						
	8						
	9						
	10						
	11						
	12						
	13						
	14						
	15						
	16						
	17						
	18						
	19						
	20						
	21						
	22						
	23						
	24						
	25						
	26						
	27						
	28						
	29						
	30						
	31						
	32						
	33						
	34						
	35	For use in adapting Series 6 Mounting Kits to be used in Series 5 type panel construction.					
	36						
	37	Series 5 construction has .406 dia. holes in interior horizontal bus.					
	38						
	39						
	40	(1) Use 5/16-18 insert in bus being certain that flange on insert is pulled up flush with back of bus bar.					
	41						
	42						
	43	(2) Drill out appropriate holes in branch bus minimum of .344 dia. to accommodate 5/16-18 bolts.					
	44						
Revisions 0: 681 1: 1B-362 6-5-92 2: 1B-359 11-11-92 3: 1C-286 4-19-99	Chk DSH 6-5-92	By RM 6-15-83	Confidential - property of Siemens Industry, Inc. Norcross, GA	SERIES 5 ADAPTOR KIT	11-5570-01 Dwg No.	Sht. 1 Of 1	3 Rev.

IF EXISTING EQUIPMENT IS TYPE CDP-6, VB-6, FCI OR FCII THE VERTICAL BUS WILL BE PRE-PUNCHED WITH .228 DIAMETER HOLES. IN THESE CASES USE SERIES 6 BRANCH BUS PARTS LIST ON REVERSE SIDE.

CAT. NO. **6CLE2**